



SOCKETS

**Phenolic Sockets
with Paper Shell Covers**





**REPLACEMENT
PAPER SHELL**
22552
CANDELABRA BASE
FOR SOCKETS RATED
75 WATTS
125 VOLTS
HEIGHT - 1 1/2"





CANDELABRA BASE 
22125 
1/8-IP HICKEY
75 WATTS
125 VOLTS
HEIGHT - 1 1/2"



CANDELABRA BASE 
22126 
1/8-IP HICKEY
75 WATTS
125 VOLTS
HEIGHT - 2"



CANDELABRA BASE 
22127 
1/8-IP HICKEY
75 WATTS
125 VOLTS
HEIGHT ADJUSTABLE
FROM 3 3/8" - 4 3/4"



KEYLESS
22135
STANDARD BASE
1/8-IP HICKEY
660 WATTS
250 VOLTS
HEIGHT - 2"



ADJUSTABLE TURN KNOB
22118 - REMOVABLE KNOB
STANDARD BASE
1/8-IP HICKEY
250 WATTS
250 VOLTS
HEIGHT ADJUSTABLE
FROM 4" - 5 1/4"



KEYLESS
22136
STANDARD BASE
1/8-IP HICKEY
660 WATTS
250 VOLTS
HEIGHT - 3"



**ADJUSTABLE
KEYLESS**
22138
STANDARD BASE
1/8-IP HICKEY
660 WATTS
250 VOLTS
HEIGHT ADJUSTABLE
FROM 4" - 5 5/8"