

Drywall Screws Phillips Bugle Head Fine Thread - Black Oxide - PC 4260



- Drywall Screws
- Bugle Head
- Phillips
- Fine Thread
- Black Oxide
- Invincibox™ Up To 2"

Fine thread Bugle head drywall screws are self piercing and are used for wood, drywall and aluminum. Length is determined from the top of the fastener head.

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
DWSBX61	58100	6 x 1	100	500	4000	0.35#	C
DWSBX6118	58102	6 x 1-1/8	100	500	4000	0.36#	C
DWSBX6114	58104	#6 6 x 1-1/4	100	500	4000	0.40#	C
DWSBX6158	58106	6 x 1-5/8	100	500	4000	0.64#	C
DWSBX62	58108	6 x 2	100	500	3000	0.64#	C
DWSBX6214	58110	6 x 2-1/4	100		3000	0.69#	C
DWSBX8212	58112	#8 8 x 2-1/2	100		1000	1.04#	C
DWSBX83	58114	8 x 3	100		1000	1.30#	C
DWT61	58120	6 x 1	500		3000	1.64#	C
DWT6118	58122	#6 Tuff Pack 6 x 1-1/8	500		3000	1.82#	C
DWT6114	58124	6 x 1-1/4	500		3000	1.93#	C
DWT6158	58126	6 x 1-5/8	500		3000	2.39#	C
DWT62	58128	6 x 2	300		1800	1.68#	C
DWSBK61	58050	6 x 1	10000		10000	35.00#	C
DWSBK6118	58052	6 x 1-1/8	10000		10000	36.00#	C
DWSBK6114	58054	#6 Bulk Pack 6 x 1-1/4	8000		8000	28.80#	C
DWSBK6158	58056	6 x 1-5/8	5000		5000	20.00#	C
DWSBK62	58058	6 x 2	3500		3500	22.40#	C
DWSBK6214	58060	6 x 2-1/4	3000		3000	20.40#	C
DWSBK8212	58062	#8 Bulk Pack 8 x 2-1/2	2500		2500	26.00#	C
DWSBK83	58064	8 x 3	2000		2000	26.00#	C

Drywall Screws Phillips Bugle Head Coarse Thread Wood Rockets - Yellow Zinc - PC 4260



- Wood Rockets
- Bugle Head
- Phillips
- Coarse Thread
- Yellow Zinc
- Invincibox™ Up To 2"

Coarse thread Bugle head drywall screws (Wood Rockets) are self piercing and are used for drywall, particle board and wood. The coarse threads provide for a quicker installation.

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
WR61	16200	6 x 1	100	500	4000	0.35#	C
WR6118	16202	6 x 1-1/8	100	500	4000	0.38#	C
WR6114	16204	#6 6 x 1-1/4	100	500	4000	0.40#	C
WR6158	16206	6 x 1-5/8	100	500	4000	0.54#	C
WR62	16208	6 x 2	100	500	3000	0.64#	C
WR6214	16210	6 x 2-1/4	100		3000	0.68#	C
WR8212	16209	#8 8 x 2-1/2	100		1000	1.04#	C
WR83	16211	8 x 3	100		1000	1.30#	C
WRT61	16212	6 x 1	500		3000	1.58#	C
WRT6118	16214	#6 Tuff Pack 6 x 1-1/8	500		3000	1.79#	C
WRT6114	16216	6 x 1-1/4	500		3000	2.00#	C
WRT6158	16215	6 x 1-5/8	500		3000	2.46#	C
WRT62	16217	6 x 2	300		1800	1.81#	C
WRBK61	16218	6 x 1	10000		10000	35.00#	C
WRBK6118	16220	#6 Bulk Pack 6 x 1-1/8	10000		10000	38.00#	C
WRBK6114	16222	6 x 1-1/4	8000		8000	43.20#	C
WRBK6158	16224	6 x 1-5/8	5000		5000	20.00#	C
WRBK62	16226	6 x 2	3500		3500	22.40#	C
WRBK6214	16228	6 x 2-1/4	3000		3000	20.40#	C
WRBK8212	16230	#8 Bulk Pack 8 x 2-1/2	2500		2500	26.00#	C
WRBK83	16232	8 x 3	2000		2000	26.00#	C