

Pass & Seymour



Switches TradeMaster® Decorator Combination Switches



Unique "Up/Down" switches match the look and feel of standard Decorator switches.

Easy-to-use oversized main switch for primary load.

Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds. See Page A-20 for details.

Identification modules (sold separately) identifies each switch — light, fan, heat lamp. See Page A-20 for details.



TM8113-WCC
Shown with Snap-In Light Module TM8LMCC.

Fully rounded back body protects wires from being damaged by sharp edges.

Ground screw position under the end of the strap minimizes the risk of contact.

Impact-resistant face and body.



Full wraparound metal strap, commercial grade with lock-in tabs.

All screws are tri-drive.

Patented split circuit tab — easily accessible, and can be reinstalled without a tool.

External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.

Adding a Snap-In Light Module



Switches

TradeMaster® Decorator Combination Switches


15A, 120VAC

Pass & Seymour




Features


- Impact-resistant face and body.
- Fully rounded back body protects wires from being damaged by sharp edges.
- Clear identification of circuits.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Full wraparound metal strap with lock-in tabs.
- Patented split circuit tab – easily accessible, and can be reinstalled without a tool.
- Unique “Up/Down” switches match the look and feel of standard Decorator switches.
- Largest breadth of 15 amp offering.
- All screws are tri-drive.
- Patented Snap-In Light and Identification Modules (sold separately). See Page A-20 for details.



TM811-WCC



TM8111-WCC




TM81111-WCC


All devices listed on this page conform to NEMA WD-1 and WD-6.

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			 UL20	 cULus
Two Single Pole Switches				
TM811-ICC	15 120	Ivory	•	•
TM811-WCC	15 120	White	•	•
TM811-CC	15 120	Brown	•	•
TM811-BKCC	15 120	Black	•	•
TM811-LACC	15 120	Light Almond	•	•
Two Single Pole Switches with Pilot Light				
TM811-PLICC	15 120	Ivory	•	•
TM811-PLWCC	15 120	White	•	•
TM811-PLBKCC	15 120	Black	•	•
TM811-PLLACC	15 120	Light Almond	•	•
Single Pole Switch & Three-Way Switch				
TM813-ICC	15 120	Ivory	•	•
TM813-WCC	15 120	White	•	•
TM813-CC	15 120	Brown	•	•
TM813-BKCC	15 120	Black	•	•
TM813-LACC	15 120	Light Almond	•	•
Single Pole Switch with Pilot Light & Three-Way Switch				
TM813-PLICC	15 120	Ivory	•	•
TM813-PLWCC	15 120	White	•	•
TM813-PLBKCC	15 120	Black	•	•
TM813-PLLACC	15 120	Light Almond	•	•
Two Three-Way Switches				
TM833-ICC	15 120	Ivory	•	•
TM833-WCC	15 120	White	•	•
TM833-CC	15 120	Brown	•	•
TM833-BKCC	15 120	Black	•	•
TM833-LACC	15 120	Light Almond	•	•
Three Single Pole Switches				
TM8111-ICC	15 120	Ivory	•	•
TM8111-WCC	15 120	White	•	•
TM8111-CC	15 120	Brown	•	•
TM8111-BKCC	15 120	Black	•	•
TM8111-LACC	15 120	Light Almond	•	•
Two Single Pole Switches & Three-Way Switch				
TM8113-ICC	15 120	Ivory	•	•
TM8113-WCC	15 120	White	•	•
TM8113-CC	15 120	Brown	•	•
TM8113-BKCC	15 120	Black	•	•
TM8113-LACC	15 120	Light Almond	•	•
Four Single Pole Switches				
TM81111-ICC	15 120	Ivory	•	•
TM81111-WCC	15 120	White	•	•
TM81111-CC	15 120	Brown	•	•
TM81111-BKCC	15 120	Black	•	•
TM81111-LACC	15 120	Light Almond	•	•

Pass & Seymour



TM818-WCC



TM8118-WCC



TM8LMCC



TM8ID-WCC

Switches

TradeMaster® Decorator Combination Switches

15A, 120/125VAC

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL20	 UL498	 cULus
Single Pole Switch & Single Receptacle						
TM818-ICC	15 120/125	Ivory	5-15R	•	•	•
TM818-WCC	15 120/125	White	5-15R	•	•	•
TM818-CC	15 120/125	Brown	5-15R	•	•	•
TM818-BKCC	15 120/125	Black	5-15R	•	•	•
TM818-LACC	15 120/125	Light Almond	5-15R	•	•	•
Single Pole Switch & Single Receptacle with Pilot Light						
TM818-PLICC	15 120/125	Ivory	5-15R	•	•	•
TM818-PLWCC	15 120/125	White	5-15R	•	•	•
TM818-PLBKCC	15 120/125	Black	5-15R	•	•	•
TM818-PLLACC	15 120/125	Light Almond	5-15R	•	•	•
Three-Way Switch & Single Receptacle						
TM838-ICC	15 120/125	Ivory	5-15R	•	•	•
TM838-WCC	15 120/125	White	5-15R	•	•	•
TM838-CC	15 120/125	Brown	5-15R	•	•	•
TM838-BKCC	15 120/125	Black	5-15R	•	•	•
TM838-LACC	15 120/125	Light Almond	5-15R	•	•	•
Two Single Pole Switches & Single Receptacle						
TM8118-ICC	15 120/125	Ivory	5-15R	•	•	•
TM8118-WCC	15 120/125	White	5-15R	•	•	•
TM8118-CC	15 120/125	Brown	5-15R	•	•	•
TM8118-BKCC	15 120/125	Black	5-15R	•	•	•
TM8118-LACC	15 120/125	Light Almond	5-15R	•	•	•
Single Pole Switch & Pilot Light						
TM81-PLICC	15 120/125	Ivory		•	•	•
TM81-PLWCC	15 120/125	White		•	•	•
TM81-PLBKCC	15 120/125	Black		•	•	•
TM81-PLLACC	15 120/125	Light Almond		•	•	•
Three-Way Switch & Pilot Light						
TM83-PLICC	15 120/125	Ivory		•	•	•
TM83-PLWCC	15 120/125	White		•	•	•
TM83-PLBKCC	15 120/125	Black		•	•	•
TM83-PLLACC	15 120/125	Light Almond		•	•	•

Features

- Module simply snaps-in for easy installation.
- Can be installed with the following devices: TM811, TM813, TM833, TM818, TM838, TM8111, TM8113, TM81111, TM8118 and the LS Series of Dimmers & Fan Speed Controls (see Pages M-8 and M-17).

Snap-In Light Module:

- Lights when OFF.
- Uses energy-efficient 1/4 watt LED light.
- LED light will not generate heat and will last on average 47 years.

Catalog Number	Rating A. VAC	Color	3rd Party Compliance
			
Snap-In Light Module			
TM8LMCC	15 120/125	Clear	•
Identification Modules			
TM8ID-ICC	— —	Ivory	
TM8ID-WCC	— —	White	
TM8ID-CC	— —	Brown	
TM8ID-BKCC	— —	Black	
TM8ID-LACC	— —	Light Almond	

For Decorator Hallway Lights and Combination Devices, see Pages D-14, D-17, and D-19.

All devices listed on this page conform to NEMA WD-1 and WD-6.