

Bulb Shape	Base	Watts	Order Code	Description	Volts	Case Qty	Filament Design	MOL (in)	LCL (in)	Rated Life (hrs)	Lumens Initial	Color Temp K	CBCP	Beam Spread	Warning and Caution Notices	Reduced Wattage	Additional Information
Incandescent Lamps (continued)																	
200 Watts																	
A21	Med	200	16069	200A/CL-1 12PK	120	12	CC-8	5.37	4.06	750	3980						Crystal
		200	11585	200A/W-1 12PK	120	12	CC-8	5.37	4.06	750	3910						Soft-White
		200	44534	200A/W-PK6	120.1		CC-8	5.37	4.06	750	3910						Soft-White
		200	89371	200A/RVL-TP1/6	120	30	CC-8	5.37	4.06	750	2800						Reveal® Soft-White
		200/177	25936	200A21/99/IF	130/120	60	CC-8	5.37	4.06	2500/6800	3250/2500						I.F.-Extended Service (Ratings @ 120 volts)
PAR46	Med Sid Pr	200	20115	200PAR46/3NSP	120	12	CC-13	4		2000	2270	2750	31000		1a,2a,5b,5c,9n		Narrow Reflector
		200	20138	200PAR46/3MFL	120	12	CC-13	4		2000	2270	2750	11500		1a,2a,5b,5c,9n		Medium Flood
		200	20117	200PAR46/3NSP	130	12	CC-13	4		2000	2270	2750	31000		1a,2a,5b,5c,9n		Narrow Reflector
		200	20140	200PAR46/3MFL	130	12	CC-13	4		2000	2270	2750	11500		1a,2a,5b,5c,9n		Medium Flood
PAR56	Scrw Term	200	20122	200PAR	30	12	CC-8	4.5		350			230000				Locomotive Headlight
	Mog End Pr	200	49889	200PAR56/MFL	120	12	CC-13	5		2000	2270	2750	15000		1a,2a,5b,5c,9n		Medium Flood
PS30	Med	200/177	72548	200PS30RS/23/STG	130/120	60	C-9	8.06	6.00	1000/2600	3240/2495				2a, 5e		Saf-T-Guard®
240 Watts																	
PAR56	Scrw Term	240	20575	240PAR56/VNSP	12	12	C-6	4.5		2000		2800	140000		1a,2a,5b,5c,9n		Very Narrow Reflector
		240	20576	240PAR56/MFL	12	12	C-6	4.5		2000		2800	46000		1a,2a,5b,5c,9n		Medium Flood
		240	20577	240PAR56/WFL	12	12	C-6	4.5		2000		2800	13000		1a,2a,5b,5c,9n		Wide Flood
250 Watts																	
R40	Med	250	37770	250R40/1 6PK	120	30	C-9	6.56		5000	2200				2a, 2b, 3b, 5e, 6a		Reflector-Warm Up Infrared Heat Lamp-Clear Face
		250	37771	250R40/10 6PK	120	30	C-9	6.56		5000					2a, 2b, 3b, 5e, 6a		Reflector-Chill Chaser Infrared Heat Lamp. Red, HRG
		250	46881	250R40/1/CVG	120	30	C-9	6.56		5000	2150				2a, 2b, 3b, 5e, 6a		Clear-covRguard®, Food Warming, Reflector-Infrared
R40	Med Skirt	250	20724	250R40/4	120	24	C-9	7.43		5000				2a, 2b, 3b, 5e, 6a		Reflector Infrared Industrial-Light I.F., BB	
R40	Med	250	47724	250R40/1/STG PQ6	120	30	C-9	6.56		5000	2150				2a, 2b, 3a, 3b, 6a		Heat Lamp Saf-T-Gard® - Shatter-Resistant
		250	23423	21A/R40/FL	12	24	C-2V	6.68		1000	2850		1600		2b, 5a, 5e		Reflector Flood
300 Watts																	
PS25	Med	300/266	20863	300M	130/120	60	CC-8	6.93	5.18	750/1950	6120/4170						Clear
		300/266	20917	300M/IF	130/120	60	CC-8	6.93	5.18	750/1950	6120/4170						Inside Frost
PS35	Mog Screw	300	21025	300	130	24	C-9	9.37	7.00	1000	5820						Clear
		300	21079	300/IF	130	24	C-9	9.37	7.00	1000	5820						Inside Frost
R40	Med	300	21197	300R/SP	120	24	CC-2V	6.56		2000	3700		9000		2a, 2b, 5b, 9e		Reflector-Light I.F. HORIZ
		300	21213	300R/FL	120	24	CC-2V	6.56		2000	3700		2500		2a, 2b, 5b, 9e		Reflector-Flood I.F. HORIZ
		300	21229	300R/FL/1	120	24	CC-2V	6.75		2000	3000		4400		2a, 2b, 5b, 9e		Reflector-Flood-I.F. BB, HRG
		300/266	21215	300R/FL	130/120	24	CC-2V	6.56		2000/5400	3465/2670		2500		2a, 2b, 5b, 9e		Reflector Flood-I.F. HORIZ (Ratings @ 120 volts)
R40	Mog Screw	300	21254	300R/3FL	120	24	CC-2V	7.25		2000	3000		4500		2a, 2b, 5b, 9e		Reflector Flood-I.F.1BB

Cross-Reference

GE Description	Osram/Sylvania Description	Philips Description
Order This GE Lamp	If you currently use these lamps	
Incandescent Lamps		
3S6/5 130V	3S6/5 130V	3S6/5 120-130V
4C7	4C7/BL/2PK	BC-4C7
4C7/W	4C7/W/2PK 120V	BC4C7/W
10S11N	10S11N/CL	10S11N
10S11N/F	10S11/F	10S11N/F
15S14/GR/CL 130V	15S14/CL 130V	—
40S11N/1/F	40S11/N/CF 120V	40S11N/F 120V
40R14/N/CD	40R14/N/RP	40R14/N
40T6 1/2	40T6.5/CL	40T6-1/2 120V
40T8	40T8	40T8
40T10	40T10	40T10
60T10F/CD	60T10/CF	60T10/641F
38A 130V		
38A 130V	38A/CVP 130V	38A 120V
38A/CL 130V	not available in 130V	38A/CL 130V
40A15	40A15	40A15
40A 48PK	40A/CVP 130V	40A 130V
50A19/RS/SH		
50A19/RS/SH	50A/RS/SL	50A/RS/TF 120V
50/150	50/150A/W	50/150T/SW
57A 130V		
57A 130V	57A/CVP 130V	57A 130V
57A/CL 130V	57A/CL 130V	57A/CL 130V
60A15	60A15	60A15
60A 48PK	60A/CVP 130V	60A19/35
60A/RS 130V	60A/RS/2/RP 130V	—
60A/RS/STG	60A/RS/SL/RP 120V	—
60A/PL	60A/GRO	60A/AGRO
65R30FL/LL		
65R30FL/LL	—	65BR30/FL/LL
65R30/SP/LL	—	65BR30/SP/LL
71A 130V		
71A 130V	71A/CVP 130V	71A 120V
71A/CL 130V	not available in 130V	71A/CL 130V
75A 48PK	75A/CVP 130V	75A
75A/RS/130	75A/RS/2/RP 130V	—
75A/RS/STG	75A21/RS/SL/RP 130V	75A/RH/TG 120-130V
95A 130V		
95A 130V	95A/CVP 130V	95A 120V
95A/CL 130V	not available in 130V	95A/CL 130V
100A 48PK	100A/CVP 130V	100A 130V
100A/RS 130V	100A/RS/2/RP 130V	—
100A/RS/STG	100A/RS/SL/RP 120V	100A/RS/VS/BR/TG 120-130V
100A23	100A23 12V	100A 12V
150A21/RS		
150A21/RS	150A23/RS 130V	—
150A21/RS/STG	—	150A/35/RS/BR/TG 120-130V
150PS25/RS/STG	150PS25/RS/SL 120V	—
200PS30/RS/23/STG	200PS/RS/SL 120V	200PS30/RS/TF 120V
250R40/10	250R40/10	250R40/HR
300M	300M/CL	300-120V CLR PS30
300M/IF	300M/IF	300M/PS30IF 130V
15BC	15B10C/T	15BA9C
15FC	15FC	15F10C
25B10C/T		
25BC	25B10C/T	25B10-1/2C
25BM	25B10	25B13
25CAC	25B10C	25BA9C/CL
25CAC/F	25B10C/W	25BA9C/F
25CAC/L	25B10C/DL	25BA9C/4M
25CAM	—	25BA9-1/2

GE Description	Osram/Sylvania Description	Philips Description
Order This GE Lamp	If you currently use these lamps	
Incandescent Lamps (continued)		
25FM/CF	—	—
25GC	25G16.5C	25G16-1/2C
25GM	25G16.5	25G16-1/2
25G25	25G25	25G25
40B10C/T		
40BC	40B10C/T	40B10-1/2C
40BM	40B10	40B13
40CAC	40B10C	40BA9C/CL
40CAC/F	40B10C/F	40BA9C/F
40CAC/L	—	40BA9C/4M
40CAM	—	40BA9-1/2
40CAM/L	—	40BA9-1/2/LL
40FM/CF	—	—
40GC	40G16.5C	40G16-1/2C
40GM	40G16.5	40G16-1/2
40G25	40G25	40G25
60B10C/T		
60BC	60B10C/T	60B10-1/2C
60BM	60B10	60B13
60CAC	60B10C	60BA9C/CL
60CAC/F	60B10C/F	60BA9C/F
60CAM	—	60BA9-1/2
60FM/CF	—	—
60GC	60G16.5C	60G16-1/2C
60GM	60G16.5	60G16-1/2
60G25	60G25	60G25