

Hangers / Hanging Systems

Deck Hanger And Punch

Features

- 1/4" or 3/8" square section nut or 3/8" (10 mm) clearance hole
- Maximum trapeze width 2" (50 mm)
- Minimum roof decking sheet thickness 24 gauge



Fig. #1

Part Number	Fig. #	Description	Standard Packaging Quantity
TDH	1	3/8" Plain Hole	50
TDHT4	2	1/4 - 20 Nut	50
TDHT6	2	3/8 - 16 Nut	50



Fig. #2

Features

- Decking hole punch tool
- Easy one-step operation
- Preset dimensions
- No secondary power sources needed

Part Number	Fig. #	Description	Standard Packaging Quantity
TDHP2	3	Deck Hanger Punch	1
TDHP2PR10	4	Replacement Punch (requires 2 per punch)	1



Fig. #3

Roof Decking Thickness				
in	mm	gauge	lbs.	kN.
0.025-0.0276	0.63-0.70	24	130	0.60
0.0276-0.0315	0.70-0.80	23	150	0.70
0.0315-0.0394	0.80-1.00	22	180	0.80
0.0394	1.00	19	200	0.90
0.0516	1.20	18	240	1.07



Fig. #4

