

# CI6

## 6" Incandescent Cylinder

### Specifications/Features

#### Fixture

6" diameter extruded aluminum construction for indoor commercial and industrial applications.

Three mounting options available: ceiling mount, pendant mount or wall mount.

Pendant mount fixtures feature a sloped ceiling canopy (select stem kits separately below).

Flexible cable mount fixtures are supplied with 120" field adjustable cable.

Wall mount bracket provides easy, one handed installation.

Safety chain connects the cylinder to the lid (ceiling mount and pendant mount).

#### Lamp/Electrical

150W PAR38, E26 Medium Base, max lamp (ceiling mount and pendant mount), 120-130V.

300W R40 or 150W PAR38, E26 Medium Base, max lamp (wall mount) 120-130V.

100W R40 or 100W PAR38, E26 Medium Base, max lamp (flexible cable mount), 120-130V.

#### Mounting






Ceiling mount, pendant mount or wall mount (hardware included for mounting to octagonal or rectangular switch junction box).

#### Warranty

This fixture is covered by ConTech's full one year replacement guarantee after date of purchase.

#### Labels/Usage

cCSAus Certified. Suitable for damp locations.



### Ordering Information

Example Order:  -

Fixture	Mounting	Baffle/Reflector	Finish
<input type="text" value="CI6"/>	<input type="text" value="C"/>	<input type="text" value="B"/>	<input type="text" value="B"/>

**CI6**

**C** - Ceiling Mount  
**FC** - Flexible Cable  
**P** - Pendant Mount  
**W** - Wall Mount

**B** - Black Baffle  
**C** - Clear Reflector

**B** - Black  
**P** - White  
**S** - Silver

Stem Kit - Pendant Mount Only

<input type="text" value="CSK12-B"/>
--------------------------------------

**CSK6-(B,P,S)** - 6" Stem Kit  
**CSK12-(B,P,S)** - 12" Stem Kit  
**CSK18-(B,P,S)** - 18" Stem Kit  
**CSK24-(B,P,S)** - 24" Stem Kit  
**CSK30-(B,P,S)** - 30" Stem Kit  
**CSK36-(B,P,S)** - 36" Stem Kit  
**CSK48-(B,P,S)** - 48" Stem Kit