

ILSCO

connections
matter

www.ilsco.com




TYPE PED-Z

Features

- Available in two, four, six, or eight conductor configurations in four wire ranges
- Manufactured from high strength 6061-T6 aluminum alloy
- Compact size
- Rated for 600 volts, 90° C

Benefits

- Provides multiple conductor installation for a wide range of conductors
- Suitable for use with either copper or aluminum conductors
- Suitable for pedestal applications



Catalog Number	Connector Design	Number Of Ports	Wire Range	Dimensions			Hex Size
				L	W	H	
PED-2-2/0-Z		2	2/0-14	2.09	.56	.73	3/16
PED-4-2/0-Z		4	2/0-14	3.78	.56	.73	3/16
PED-6-2/0-Z		6	2/0-14	5.46	.56	.73	3/16
PED-8-2/0-Z		8	2/0-14	7.15	.56	.73	3/16
PED-2-4/0-Z		2	4/0-6	1.78	.75	1.00	5/16
PED-4-4/0-Z		4	4/0-6	3.64	.75	1.00	5/16
PED-6-4/0-Z		6	4/0-6	5.50	.75	1.00	5/16
PED-8-4/0-Z		8	4/0-6	7.36	.75	1.00	5/16
PED-2-350-Z		2	350kcmil-6	2.22	1.00	1.25	5/16
PED-4-350-Z		4	350kcmil-6	4.53	1.00	1.25	5/16
PED-6-350-Z		6	350kcmil-6	6.84	1.00	1.25	5/16
PED-8-350-Z		8	350kcmil-6	9.15	1.00	1.25	5/16
PED-2-600-Z		2	600kcmil-4	2.47	1.25	1.63	3/8
PED-4-600-Z		4	600kcmil-4	5.03	1.25	1.63	3/8
PED-6-600-Z		6	600kcmil-4	7.59	1.25	1.63	3/8
PED-8-600-Z		8	600kcmil-4	10.16	1.25	1.63	3/8

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)
Covers not available. DE-OX Inhibitor is recommended for all aluminum terminations.