

**LED**

25,000 Hours average rated life, 120Volts

### Applications:

Ideal for decorative dimming applications. Suitable for outdoor fixtures. Also perfect for applications with hard to reach areas, vibration, and frequent starts.

#### Accent and decorative lighting including:

- + Chandeliers
- + Ceiling Fans
- + Decorative
- + Indoor Fixtures
- + Outdoor Fixtures




Light output equivalent to 25W.


### Features and Benefits

- Long Life: 25,000 hours – no more bulb replacements!
- Fully dimmable, brilliant LED light.
- Excellent white color consistency from bulb to bulb
- UL approved for dry and damp locations.
- Available in E12 and E26 base.

\* Three or more lamps per dimming circuit is recommended fo optimal dimming.



LED4E26G1627K



LED4E12G1627K



LED4E12B1127K



LED4E26B1127K




LED4E26G1627K



LED4E12G1627K



LED4E12B1127K



LED4E26B1127K

Catalog Number

Notes

Type



### Specifications ( at full brightness )

Input Line Voltage:	120VAC
Input Line Frequency	60HZ
Lamp Life (Rated)	25,000 hrs
Minimum Starting Temp	-30°C
Maximum Operating Temp	40°C
UL/cUL Listed	Yes
Power Factor	92%
CRI	82

Warranties and Certifications:	Item #	Description	Voltage	Wattage	Wattage Equivalent	M.O.L. (inches)	Diameter (inches)	Lumens	LPW	CCT	CRI
3 YEAR WARRANTY	LED5E12B1127K	LED 5W DIMMABLE CANDELABRA BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	300	60	2700K	82
	LED5E26B1127K	LED 5W DIMMABLE BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	300	60	2700K	82
	LED5E12B1127KF	LED 5W DIMMABLE CANDELABRA FROSTED BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	300	60	2700K	82
	LED5E26B1127KF	LED 5W DIMMABLE FROSTED BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	300	60	2700K	82
	LED5E12G1627K	LED 5W DIMMABLE CANDELABRA G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	300	60	2700K	82
	LED5E26G1627K	LED 5W DIMMABLE G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	300	60	2700K	82
	LED5E12G1627K	LED 5W DIMMABLE CANDELABRA FROSTED G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	300	60	2700K	82
	LED5E26G1627K	LED 5W DIMMABLE FROSTED G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	300	60	2700K	82
	LED4E12B1127K	LED 4W DIMMABLE CANDELABRA BLUNT TIP - 2700K	120	3.7	25W	3.8	1.4	200	50	2700K	82
	LED4E26B1127K	LED 4W DIMMABLE BLUNT TIP - 2700K	120	3.7	25W	3.8	1.4	200	50	2700K	82
	LED4E12B1127KF	LED 4W DIMMABLE CANDELABRA FROSTED BLUNT TIP - 2700K	120	3.7	25W	3.8	1.4	200	50	2700K	82
	LED4E26B1127KF	LED 4W DIMMABLE FROSTED BLUNT TIP - 2700K	120	3.7	25W	3.8	1.4	200	50	2700K	82
	LED4E12G1627K	LED 4W DIMMABLE CANDELABRA G16 GLOBE - 2700K	120	3.7	25W	3.5	2.0	200	50	2700K	82
	LED4E26G1627K	LED 4W DIMMABLE G16 GLOBE - 2700K	120	3.7	25W	3.5	2.0	200	50	2700K	82
LED4E12G1627K	LED 4W DIMMABLE CANDELABRA FROSTED G16 GLOBE - 2700K	120	3.7	25W	3.5	2.0	200	50	2700K	82	
LED4E26G1627K	LED 4W DIMMABLE FROSTED G16 GLOBE - 2700K	120	3.7	25W	3.5	2.0	200	50	2700K	82	