



**A15**  
Medium Base  
(130 Volt)

- S3720** 40 Watt Clear
- S3721** 40 Watt Frosted
- S3739** 60 Watt Clear
- S3740** 60 Watt Frosted

Packing: 1 Bulb/Card  
240 Cards/Master,  
20 Cards/Inner



**7C7 & 4C7**  
Candelabra Base  
(130 Volt)

**Two Packs**

- S3797** 4 Watt Clear
- S3791** 7 Watt Clear
- S3792** 7 Watt White

Packing: 2 Bulbs/Card  
400 Cards/Master,  
20 Cards/Inner

**Four Packs**

- S4724** 4 Watt Clear
- S4725** 7 Watt Clear
- S4726** 7 Watt White

Packing: 4 Bulbs/Card  
48 Cards/Master,  
12 Cards/Inner



carded lamps

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
4	C7	Cand.	<b>S3797</b>	4C7	Clear	120V	3000	16	C-7A	2 1/8"	Card/2	400/20
4	C7	Cand.	<b>S4724</b>	4C7	Clear	120V	3000	16	C-7A	2 1/8"	Card/4	48/12
7	C7	Cand.	<b>S3791</b>	7C7	Clear	120V	3000	35	C-7A	2 1/8"	Card/2	400/20
7	C7	Cand.	<b>S3792</b>	7C7/W	White	120V	3000	20	C-7A	2 1/8"	Card/2	400/20
7	C7	Cand.	<b>S4725</b>	7C7	Clear	120V	3000	35	C-7A	2 1/8"	Card/4	48/12
7	C7	Cand.	<b>S4726</b>	7C7/W	White	120V	3000	20	C-7A	2 1/8"	Card/4	48/12
40	A15	Med.	<b>S3720</b>	40A15	Clear	130V	2500	290	C-9	3 1/2"	Card/1	240/20
40	A15	Med.	<b>S3721</b>	40A15/F	Frosted	130V	2500	280	C-9	3 1/2"	Card/1	240/20
60	A15	Med.	<b>S3739</b>	60A15	Clear	130V	2500	580	C-9	3 1/2"	Card/1	240/20
60	A15	Med.	<b>S3740</b>	60A15/F	Frosted	130V	2500	530	C-9	3 1/2"	Card/1	240/20