

Deluxe Cord Grips

Aluminum Fittings, Stainless Steel Mesh, Liquidtight for Insulated Cables.

IMPORTANT:

Read all safety and technical data relating to this product.

Refer to pages X-61 through X-68.

Straight Female Thread

NPT Thread Size Inches	Grip Diameter Range Inches (cm)		Form Size	Catalog Number
½	.375"-.500"	(.95-1.27)	F2	07401043
	.500"-.625"	(1.27-1.59)		07401045
¾	.500"-.625"	(1.27-1.59)	F2	07401052
¾	.625"-.750"	(1.59-1.90)	F4	07401053

90° Male Thread

NPT Thread Size Inches	Grip Diameter Range Inches (cm)		Form Size	Catalog Number
¾	.250"-.312"	(.63-.79)	F1	07401071
	.312"-.375"	(.79-.95)		07401072
	.375"-.437"	(.95-1.11)		07401073
½	.187"-.250"	(.47-.63)	F2	07401074
	.250"-.375"	(.63-.95)		07401076
	.375"-.500"	(.95-1.27)		07401078
¾	.500"-.625"	(1.27-1.59)	F3	07401080*
	.375"-.500"	(.95-1.27)		07401081
	.500"-.625"	(1.27-1.59)		07401083
1	.625"-.750"	(1.59-1.90)	F4	07401084*
	.750"-.875"	(1.90-2.22)		07401085
	.875"-.1.000"	(2.22-2.54)		07401087
1½	1.000"-.1.125"	(2.54-2.86)	F5	07401089
	.750"-.875"	(1.90-2.22)		07401091*
	.875"-.1.000"	(2.22-2.54)		07401099*
2	1.125"-.1.250"	(2.86-3.17)	F6	074011229*
	1.000"-.1.125"	(2.54-2.86)		074011230
	1.125"-.1.250"	(2.86-3.17)		074011231
1¼	1.250"-.1.375"	(3.17-3.49)	F5	074011232
	1.000"-.1.125"	(2.54-2.86)		074011233
	1.125"-.1.250"	(2.86-3.17)		074011234*
1½	1.250"-.1.375"	(3.17-3.49)	F5	074011045
	1.000"-.1.125"	(2.54-2.86)		074011046
	1.125"-.1.250"	(2.86-3.17)		074011047
2	1.312"-.1.437"	(3.33-3.65)	F6	074011048
	1.437"-.1.562"	(3.65-3.97)		074011049
	1.687"-.1.812"	(4.28-4.60)		074011050
1¼	1.750"-.1.875"	(4.44-4.76)	F5	074011240
	1.500"-.1.625"	(3.81-4.13)		074011241
	1.625"-.1.750"	(4.13-4.45)		074011242

45° Male Thread

NPT Thread Size Inches	Grip Diameter Range Inches (cm)		Form Size	Catalog Number
½	.250"-.375"	(.63-.95)	F2	074011236
	.375"-.500"	(.95-1.27)		074011021
	.500"-.625"	(1.27-1.59)		074011237*
¾	.500"-.625"	(1.27-1.59)	F3	074011049
	.625"-.750"	(1.59-1.90)		074011051*
	.750"-.875"	(1.90-2.22)		074011239*
1	.625"-.750"	(1.59-1.90)	F4	074011055
	.750"-.875"	(1.90-2.22)		074011057
	.875"-.1.000"	(2.22-2.54)		074011199*
1¼	1.000"-.1.125"	(2.54-2.86)	F5	074011059
	1.125"-.1.250"	(2.86-3.17)		074011060

Note: Kellems® Deluxe Cord Grips are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 of the National Electric Code Sections 501.10(b)(2), 502.10(a)(2), 502.10(b)(2), 503.10(a)(2) and 503.10(b).

*Cable jacket may have to be stripped to pass through connector body.



Dimensions in Inches (mm)