



**ALLIED
MOULDED
PRODUCTS, Inc.**



ADDITIONAL LAMP HOLDERS



LH-21WP



LH-22WP

Allied Moulded Product's lampholder line has been expanded to include two new **GU24 2-pin base** models. These products were developed for the electrical contractor looking for basic and cost effective lampholders.

Lampholder Features

- Listed per UL® 496
- Mounting slots accept 3-1/2" or 4" outlet boxes
- Lampholder rated 75 Watts, 250 Volts
- Made of UV and heat resistant polycarbonate material
- For use in non-corrosive, residential lighting applications as permitted by local code
- All models are individually polybagged
- Will accept industry standard lamps with GU24 pin design (*see below)
- Title 24 compliant for installation of lampholders in California

GU24 Lampholders




Catalog Number	Component Description	Outside Diameter	UPC# 85399	Pkg. Qty.	Std. Pkg. Wt. (lb.)
LH-21WP	GU24 Keyless lampholder with wire leads, 75W/250V (mounting screws included)	4-7/8	99583	48	13
LH-22WP	GU24 pull chain lampholder with wire leads, 75W/250V, 3' pull cord (mounting screws included)	4-7/8	99584	48	13

* Not intended for use with GU24/incandescent bulb adapter designs

Designed in the USA
Made in China

COMPACT FLUORESCENT LUMINAIRE PRODUCTS:

CF Luminaire	Lamp Wattage	Catalog Number	Component Description	Base Dia.	Asm. Height	UPC# 85339	Pkg. Qty.	Pkg. Wt. (lbs.)
	13 W	LH-CFL1	Compact fluorescent luminaire with wire leads (mounting screws included)	5.06"	3.04"	87005	12	9
	13 W	LH-CFL2	Compact fluorescent luminaire with wire leads and pull chain (mounting screws included)	5.06"	3.82"	87006	12	11
	13 W	33213SSP	Squat or low-profile compact fluorescent lamp, GU24 base replacement lamp	-----	2.3" (M.O.L)	see note	6	2

Note: UPC# 762148091735

Replacement Lamp Part Numbers:

MaxLite: MLS13FUSWW, 13 Watt, GU24 fixture base, M.O.L. = 2.52"

TCP: 33213SSP, 13 Watt, GU24 fixture base, M.O.L. = 2.3"

Golo: GU241327, 13 Watt, GU24 fixture base, M.O.L. = 2.36"


US PAT. # D652,979
Designed in the USA
Made in China



INCANDESCENT LAMPHOLDER PRODUCTS:

Keyless Medium Base	Catalog Number	Component Description	Outside Diameter	UPC# 85399	Pkg. Qty.	Std. Pkg. Wt. (lb.)
	LH-11P**	Keyless lampholder, 660W/250V, 4 terminal screws (mounting screws included)	4-9/16	87000	48	13
	LH-11WP	Keyless lampholder with wire leads, 660W/250V (mounting screws included)	4-9/16	87001	48	13

Pull Chain	Catalog Number	Component Description	Outside Diameter	UPC# 85399	Pkg. Qty.	Std. Pkg. Wt. (lb.)
	LH-12P**	Lampholder, 660W/250V, 3' pull cord, 2 terminal screws (mounting screws included)	4-9/16	87002	48	14
	LH-12WP	Lampholder with wire leads, 660W/250V, 3' pull cord (mounting screws included)	4-9/16	87003	48	15

Pull Chain with Grounded Outlet	Catalog Number	Component Description	Outside Diameter	UPC# 85399	Pkg. Qty.	Std. Pkg. Wt. (lb.)
	LH-13P**	Lampholder, 660W/125V, 3' pull cord, grounded outlet (125VAC/15A) (mounting screws included)	4-9/16	87004	48	15

** Indicates model shown in picture

Designed in the USA
Made in China

