



# OccuSwitch

## Classic wired occupancy sensors

OccuSwitch classic wall switch and low voltage occupancy sensors. The Philips OccuSwitch classic line of devices is a complete portfolio of wired occupancy sensors. The wide selection includes solutions for nearly every application. To maximize energy savings and improve the working environment, Philips offers the classic product to meet the basic needs for lighting control and energy conservation.

### Sensor technology

- PIR—Passive infrared
- Multi-Technology (PIR and Ultra-Sonic)

### Sensor types

- Wall Switch Replacement for small areas
- Low Voltage Ceiling and Wall Sensors with remote Power Pack for large areas
- Self-Powered sensors for High-Bay spaces

### Applications

- Educational facilities
- Commercial buildings
- Industrial operations
- Health care
- Retail



LRS2225/00



LRM2255/00



LRM2265/00



LCA2285/00

Order number	Description	Voltage
<b>Wall switch devices</b>		
LRS2210/00	Wall Switch Sensor - PIR, Single Switch, White	120/277 VAC
LRS2210/01	Wall Switch Sensor - PIR, Single Switch, Ivory	120/277 VAC
LRS2215/00	Wall Switch Sensor - PIR, Dual Switch, White	120/277 VAC
LRS2215/01	Wall Switch Sensor - PIR, Dual Switch, Ivory	120/277 VAC
LRS2220/00	Wall Switch Sensor - Multi-tech, Single Switch, White	120/277 VAC
LRS2220/01	Wall Switch Sensor - Multi-tech, Single Switch, Ivory	120/277 VAC
LRS2225/00	Wall Switch Sensor - Multi-tech, Dual Switch, White	120/277 VAC
LRS2225/01	Wall Switch Sensor - Multi-tech, Dual Switch, Ivory	120/277 VAC
LRS2230/00	Wall Switch Sensor - PIR Single Night Light, White	120/277 VAC
LRS2230/01	Wall Switch Sensor - PIR Single Night Light, Ivory	120/277 VAC
<b>Low voltage sensors</b>		
LRM2250/00	PIR - Ceiling Mount, Low voltage, 1500 sq.ft.	24 VDC
LRM2255/00	Multi-tech - Ceiling Mount, Low voltage, 2000 sq.ft.	24 VDC
LRM2260/00	Multi-tech - Ceiling Mount, Low voltage, 500 sq.ft.	24 VDC
LRM2265/00	Multi-tech - Wall Mount, Low voltage, 1200 sq.ft.	24 VDC
LRM2270/00	PIR - Wall Mount, Low Voltage, 2500 sq.ft.	24 VDC
LRM2275/00	PIR - Wall Mount, Low Voltage, High-Bay 55'x7'	24 VDC
LRM2280/00	PIR - Wall Mount, Low Voltage, Long Range 100'x14'	24 VDC
<b>Power relay packs</b>		
LCA2285/00	PowerPack - 120-230-277 volt	120 - 277 VAC
LCA2287/00	PowerPack - 120-230-277 volt, with HVAC Dry Contacts	120 - 277 VAC
LCA2290/00	PowerPack - 347 volt	347 VAC
LCA2292/00	PowerPack - 120-230-277 volt, Manual-ON, Auto-OFF, Title 24	120 - 277 VAC