

## BBP®31 Sign & Label Printer

The Way Label Making Should Be.



[www.BradyID.com/bbp31](http://www.BradyID.com/bbp31)

So simple,  
your whole team  
can use it.  
Just type and  
print – it's really  
that easy.



### Fast, Simple And Powerfully Versatile.

The BBP®31 Sign & Label Printer is exactly how a printer is supposed to be. It's easy to use. It's packed with functionality. And best of all, it's got so many material options that this one printer can handle all of the labeling needs in your facility.

#### Seriously simple operation.

This printer is so simple, your whole team can use it. Just type and print – it's really that easy.

- Large touch-screen display with “touch and drag” moving and sizing
- 2-touch printing – just walk up and print!
- Drop, lock and print smart chip supplies for automatic label formatting
- Full size fold-down keyboard
- Stand alone or PC-connect operation

#### Chock-full of capabilities.

This one printer can take on all the different labeling needs of your facility. There are so many options packed into this printer, your applications are endless.

- Prints labels from ½” to 4” wide
- 192 built-in graphics, with quick import options for graphics and fonts
- Wizard-style apps for pipe ID, arc flash, and RTK chemical labels
- Templates for common label styles such as signs with headers and a library of 266 pre-made “pick and print” signs and labels

#### Hundreds of material options.

The BBP®31 Sign & Label Printer can print on continuous supplies, pre-cut labels and even pre-printed sign headers and chemical labels. Choose from:

- Indoor/Outdoor Grade Vinyl (12 colors)
- Low-Halide Polyester (16 colors)
- Pre-printed ANSI/OSHA Safety Signs
- Pre-printed Right-to-Know Labels
- Repositionable Vinyl
- Cold Temperature Labels
- Magnetic Labels
- Glow-in-the-Dark Tape
- Reflective Tape
- Raised Profile Engraved Plate Substitute Labels
- Self-Laminating Wire Markers
- Tag Stock
- Tamper Evident Labels
- And more!

**SAMPLE PACK & ONLINE DEMO VIDEOS**  
[www.BradyID.com/bbp31](http://www.BradyID.com/bbp31)

# BBP<sup>®</sup>31 SIGN & LABEL PRINTER

Part Number	Description
BBP31	BBP31 Sign & Label Printer*
BBP31-360B	BBP31 Printer w/Brady 360 <sup>®</sup> Basic plan
BBP31-360P	BBP31 Printer w/Brady 360 <sup>®</sup> Preferred plan
BBP31-360B-MWS	BBP31 Printer w/Brady 360 <sup>®</sup> Basic plan and MarkWare™ Std software
BBP31-360P-MWS	BBP31 Printer w/Brady 360 <sup>®</sup> Preferred plan and MarkWare™ Std software

\*BBP31 Sign & Label Printer ships with printer, power cord, USB cable, drivers CD, stylus, cleaning kit, cutter cleaning tool, quick start guide and documentation holder.

\*\*Current MarkWare owners: Markware v3.8.1 required for use with BBP31. MarkWare v3.7 or higher required to upgrade to v3.8.1. Both upgrades are free and available at [www.BradyID.com](http://www.BradyID.com).

## Indoor/Outdoor Vinyl (B-595)

- 8-10 year outdoor durability with our most aggressive adhesive
- Conforms to irregular, rough and "difficult" surfaces such as painted cinder blocks and blow-molded equipment cases



		Catalog Number				
		4"x100'	3"x100'	2.25"x100'	1.125"x100'	0.5"x100'
White		B30C-4000-595-WT	B30C-3000-595-WT	B30C-2250-595-WT	B30C-1125-595-WT	B30C-500-595-WT
Yellow		B30C-4000-595-YL	B30C-3000-595-YL	B30C-2250-595-YL	B30C-1125-595-YL	B30C-500-595-YL
Red		B30C-4000-595-RD	-	B30C-2250-595-RD	B30C-1125-595-RD	B30C-500-595-RD
Blue		B30C-4000-595-BL	-	B30C-2250-595-BL	B30C-1125-595-BL	B30C-500-595-BL
Green		B30C-4000-595-GN	-	B30C-2250-595-GN	B30C-1125-595-GN	B30C-500-595-GN
Orange		B30C-4000-595-OR	-	B30C-2250-595-OR	B30C-1125-595-OR	B30C-500-595-OR

6 other colors in 4 sizes each can be found at [www.BradyID.com/bbp31](http://www.BradyID.com/bbp31)

## Additional Materials

- The BBP<sup>®</sup>31 Sign & Label Printer can print on 13 different types of materials with 260 total label parts to choose from!

	Catalog Number	Size	Labels Per Roll
<b>Pre-print Sign Header and RTK Chemical Supplies</b>			
	B30-25-595-ANSICA	4" x 6"	175
	B30-25-595-ANSIDA	4" x 6"	175
	B30-25-595-ANSIWA	4" x 6"	175
	B30-243-595-NFPA	4" x 6.25"	170
	B30-243-595-CB	4" x 6.25"	170
<b>BBP31 Printer Ribbons</b>			
	B30-R10000	Printer Ribbon - Black	
	B30-R10000-WT	Printer Ribbon - White	



BradyGlo™  
Photoluminescent Tape  
B30C-4000-526



Printable Magnetic  
B30C-4250-509-WT



Retro Reflective Tape  
B30C-4000-584-YL



Non-Adhesive Tag Stock  
B30C-4250-551-WT



Self-Laminating  
Cable Labels



Engraved Plate  
Substitute Labels

Over 220 additional parts for BBP<sup>®</sup>31 Sign & Label Printer can be viewed at [www.BradyID.com/bbp31](http://www.BradyID.com/bbp31)

## Tape Starter Kits

- Get started fast with the best materials packaged for your most common applications

### 5S Visual Workplace Supply Kit

Catalog Number: B30KIT-LEANVW  
Contents:

- (1) 4" B595 WHITE
- (1) 2.2" B595 WHITE
- (1) 4" B595 YELLOW
- (1) 2.2" B595 YELLOW
- (1) 2.2" REPOS WHITE
- (1) 1.1" REPOS WHITE
- (1) 2.2" MAGNETIC WHITE
- (1) BLANK VALVE TAGS - VARIETY PACK - LG
- (1) LG DIE CUT LBLS FOR VALVE TAGS
- (1) 4" X 6" B595 CAUTION HDR
- (2) BLACK RIBBON
- (1) RED RIBBON
- (1) GREEN RIBBON
- (1) BLUE RIBBON

### Pipe ID Supply Kit (Available April 2011)

Catalog Number: B30KIT-PIPE  
Contents:

- (1) 4" B595 YELLOW
- (1) 2.2" B595 YELLOW
- (1) 1.1" B595 YELLOW
- (1) 4" B595 GREEN
- (1) 2.2" B595 GREEN
- (1) 1.1" B595 GREEN
- (1) 1.1" B595 BLUE
- (1) 2.2" B595 RED
- (1) 1.1" B595 RED
- (1) 1" X 4" B593 BLACK
- (1) BLANK VALVE TAGS - VARIETY PACK - SM
- (1) SM DIE CUT LBLS FOR VALVE TAGS
- (3) BLACK RIBBON
- (2) WHITE RIBBON

### Arc Flash Warning Supply Kit (Available April 2011)

Catalog Number: B30KIT-ARCFASH-W Contents:

- (2) 4" X 6" B595 ANSI WARNING HDR
- (1) 2" X 3" B595 ANSI WARNING HDR
- (3) BLACK RIBBON
- (1) 1" X 4" B593 WHITE
- (1) 2.2" B595 ORANGE

USA  
1-888-272-3946  
[www.BradyID.com](http://www.BradyID.com)

Canada  
1-800-263-6179  
[www.BradyCanada.ca](http://www.BradyCanada.ca)

Mexico  
1-800-262-7777  
[www.BradyLatinAmerica.com](http://www.BradyLatinAmerica.com)



Order & Install with Compsee  
West Coast: 800-852-3282  
East Coast: 800-628-3888  
[sales@compsee.com](mailto:sales@compsee.com)

