

# STANDARD CONDUIT LOCKNUTS

FOR THREADED RIGID CONDUIT AND IMC

## APPLICATION

Used with bushings to bond threaded rigid conduit and IMC to boxes, cabinets or other enclosures where locknut is exposed.

## STANDARD MATERIALS


Steel

## STANDARD FINISH

Zinc Plated



## Grounding Locknuts



## TYPE GL75

CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	MASTER PACK	LBS. / 100 PCS.	UPC #
GL70	1/2"	1.250	0.220	100	1000	3	17704
GL71	3/4"	1.450	0.260	100	1000	4	17714
GL72	1"	1.720	0.245	50	500	5	17724
GL73	1-1/4"	2.020	0.240	50	500	6	17734
GL74	1-1/2"	2.535	0.250	50	500	8	17744
GL75	2"	2.950	0.250	25	250	13	17754
GL76	2-1/2"	3.570	0.280	10	100	19	17764
GL77	3"	4.330	0.295	10	100	21	17774
GL78	3-1/2"	4.810	0.310	10	100	38	17784
GL79	4"	5.395	0.300	10	100	40	17794
GL80	5"	6.487	0.525	-	10	76	17804
GL81	6"	7.830	0.525	-	10	87	17814

## APPLICATION

Used with a fixture nipple to hang fixtures.

## STANDARD MATERIALS

Steel

## STANDARD FINISH

Zinc Plated

## Conduit Oversize Locknuts



## TYPE 705X

CATALOG NUMBER	TRADE SIZE	DIM ACROSS CORNERS	DIM ACROSS FLATS	UNIT PACK	MASTER PACK	LBS. / 100 PCS.	UPC #
705X	3/8"	1.038	1.006	-	250	1	17052