



PVC COATED RIGID CONDUIT

Item Number	Trade Size	Size Metric (mm)	Wall Thickness (in.)	Outside Dia. w/ Coating	Inside Diameter	Weight Per 100 Feet	Feet Per Bundle	Aluminum Item Number
PV0510CT00	1/2"	16	0.104	0.920	0.632	90	1000	PA0510CT00
PV0710CT00	3/4"	21	0.107	1.130	0.836	119	900	PA0710CT00
PV1010CT00	1"	27	0.126	1.395	1.063	175	750	PA1010CT00
PV1210CT00	1-1/4"	35	0.133	1.740	1.394	237	420	PA1210CT00
PV1510CT00	1-1/2"	41	0.138	1.980	1.624	281	380	PA1510CT00
PV2010CT00	2"	53	0.146	2.455	2.083	376	300	PA2010CT00
PV2510CT00	2-1/2"	63	0.193	2.955	2.489	593	170	PA2510CT00
PV3010CT00	3"	78	0.205	3.580	3.090	772	140	PA3010CT00
PV3510CT00	3-1/2"	91	0.215	4.080	3.570	922	110	PA3510CT00
PV4010CT00	4"	103	0.225	4.580	4.050	1089	110	PA4010CT00
PV5010CT00	5"	129	0.245	5.643	5.073	1488	80	PA5010CT00
PV6010CT00	6"	155	0.266	6.705	6.093	1998	50	PA6010CT00



PVC COATED RIGID COUPLINGS

Item Number	Trade Size	Size Metric (mm)	Length of Metal	Threads Per Inch	Weight Per 100 (lbs)	Box Qty	Aluminum Item Number
PV0500CP00	1/2"	16	1.500	14	19	100	PA0500CP00
PV0700CP00	3/4"	21	1.532	14	32	90	PA0700CP00
PV1000CP00	1"	27	1.906	11-1/2	40	75	PA1000CP00
PV1200CP00	1-1/4"	35	1.906	11-1/2	50	42	PA1200CP00
PV1500CP00	1-1/2"	41	1.906	11-1/2	69	38	PA1500CP00
PV2000CP00	2"	53	1.937	11-1/2	93	30	PA2000CP00
PV2500CP00	2-1/2"	63	2.878	8	123	17	PA2500CP00
PV3000CP00	3"	78	3.031	8	217	14	PA3000CP00
PV3500CP00	3-1/2"	91	3.094	8	422	11	PA3500CP00
PV4000CP00	4"	103	3.188	8	391	11	PA4000CP00
PV5000CP00	5"	129	3.374	8	550	8	PA5000CP00
PV6000CP00	6"	155	3.437	8	884	5	PA6000CP00



PVC COATED 90° STANDARD ELBOWS

Item Number	Trade Size	Size Metric (mm)	Weight Per 100 (lbs)	Standard Radius A	Offset B	Tangent T	Aluminum Item Number
PV0590EL00	1/2"	16	70	4.25	6.0	1.7	PA0590EL00
PV0790EL00	3/4"	21	100	4.50	6.7	2.2	PA0790EL00
PV1090EL00	1"	27	190	5.75	8.0	2.4	PA1090EL00
PV1290EL00	1-1/4"	35	310	7.25	9.6	2.8	PA1290EL00
PV1590EL00	1-1/2"	41	400	8.25	10.6	2.6	PA1590EL00
PV2090EL00	2"	53	640	9.50	12.0	3.5	PA2090EL00
PV2590EL00	2-1/2"	63	1210	10.50	14.8	4.7	PA2590EL00
PV3090EL00	3"	78	1950	13.00	17.0	5.3	PA3090EL00
PV3590EL00	3-1/2"	91	2630	15.00	20.9	6.1	PA3590EL00
PV4090EL00	4"	103	3280	16.00	21.0	6.5	PA4090EL00
PV5090EL00	5"	129	6750	24.00	32.0	11.2	PA5090EL00
PV6090EL00	6"	155	10510	30.00	41.0	12.1	PA6090EL00

