

Panasonic

WhisperGreenSelect*


FV-05-11VKS1, FV-05-11VK1, FV-11-15VK1



FV-05-11VKSL1, FV-05-11VKL1, FV-11-15VKL1



- Customizable, all-in-one fan and fan/LED light combinations
- Pick-A-Flow speed selector one fan, you choose the CFM
- Unique Plug 'N Play modules provide up to three value-added features
- Revolutionary DC motor with SmartFlow[™] technology ensures optimal CFM output
- Replaceable, GU24 base LED lamps provide warm, energy efficient illumination
- Flex-Z Fast™ bracket provides flexible, fast and easy installation
- Can be used to comply with ASHRAE 62.2, LEED, CALGreen and ENERGY STAR for Homes 3.0





- Integrated dual 4" or 6" duct adaptor (up to 110 CFM models)
- Built-in metal flange provides blocking for penetrations through drywall as an air barrier, and assists with the decrease in leakage in the building envelope during blower door testing
- Fits in 2 x 8 construction
- Protected by UL Class 2 Power Unit
- UL listed for tub/shower enclosure when used with a GFCI protected circuit
- 6 year warranty on DC motor, 5 years on LED, 3 years on parts







The all-purpose, customizable IAQ solution for virtually any application

WhisperGreen Select™ is a ground-breaking IAQ solution that is revolutionizing the ventilation fan industry with a new set of features that enable customization and easier installation. To the builder and professional installer, Panasonic continues to be the innovation leader with high performance ventilation solutions that are built to last. WhisperGreen Select's unique design and superior energy efficiency are achieved through engineering expertise, provided by a company who sets the standard for quality and value.

WHISPERGREEN SELECT™ IS AS EASY AS 1-2-3!

Step 1: Select a Base Fan Model -

Select a base model to start building the perfect IAQ solution that satisfies your ventilation design requirements.

Fan	Fan/Light
FV-05-11VKS1: 30 to 110 CFM integrated multi-speed	FV-05-11VKSL1: 30 to 110 CFM integrated multi-speed + LED Light
FV-05-11VK1: 50-80-110 CFM single speed	FV-05-11VKL1: 50-80-110 CFM single speed + LED Light
FV-11-15VK1: 110-130-150 CFM single speed	FV-11-15VKL1: 110-130-150 CFM single speed + LED Light

Pick-A-Flow™ Speed Technology

Built-in Pick-A-Flow™ speed selector – one fan, you choose the CFM. Provides the unique ability to select your required airflow (50-80-110 and 110-130-150 CFM models) with the simple flip of a switch.

Step 2: Select Value Added Features*-

WhisperGreen Select™ offers a unique set of Four* patented modules that allow you to further customize your fan:



Multi-Speed with Time Delay (FV-VS15VK1) – Allows you to select the proper CFM settings to satisfy ASHRAE 62.2 continuous ventilation requirements. The fan runs continuously at a pre-set lower level, then elevates to a maximum level of operation when the wall switch is turned on, or when the SmartAction® motion sensor or condensation sensor module is activated. A high/Low delay timer returns the fan to the pre-set CFM level after a period of time set by the user.



SmartAction® Motion Sensor (FV-MSVK1) - Automatically activates when someone enters the room. Once the settings have been applied, the fan becomes truly automatic, making it ideal for people with disabilities and assisted living environments such as nursing homes and retirement communities. This module also activates an automatic 20 minute delay off timer for the fan.



Condensation Sensor (FV-CSVK1) – Helps control bathroom condensation to prevent mold and mildew. Advanced sensor technology detects relative humidity and temperature to anticipate dew point, automatically turning the fan on to control humidity. Built-in Relative Humidity(RH) sensitivity adjustment enables fine tuning for moist conditions and for satisfying CALGreen requirements. When the condensation sensor is used in conjunction with multi-speed functionality, the fan will kick up to high speed when the condensation sensor detects moisture in the room. This module also activates an automatic 20 minute delay off timer for the fan.



NiteGlow™ LED Night Light (FV-NLVK1) - A specialized photocell feature automatically turns on the 1 watt LED night light when darkness is sensed in the room. Hi/Low brightness switch enables you to fine tune the photo cell to work in conjunction with the darkness level of your bathroom. This module also activates an automatic 20 minute delay off timer for the fan.

Step 3: Install Your Ideal Fan with the New! Flex-Z Fast™ Installation System



Fold up articulating joints to easily position bracket in between the joist and/or through ceiling hole.

Fold articulating joints back down in preparation for installation



Extend bracket to desired length

Ingeniously designed installation bracket provides flexible, fast and easy installation for all your new construction or renovation projects.


Installed Performance and Quiet Operation at 0.25" w.g. Static Pressure


ASHRAE, ENERGY STAR®, LEED for Homes, and HVI have set the industry standard for performance measurement at 0.25" w.g. WhisperGreen Select™ fans not only provide powerful CFM output at 0.25" w.g., but our sones have also been certified at 0.25" w.g. so they are quiet under pressure and after installation.

^{*}Select up to 3 value added features.

WhisperGreenSelect*-







				W	hispe	rGree	n Sele	lect (Fan Only Models)						WhisperGreen Select (Fan Only Models)								
							Base	Fan						Base Fan with Integrated Multi-Speed								
SF	PECIFICATIONS			FV-05	-11VK	1			F	V-11-	15VK	1					/-05-1			Ť		
	Static Pressure in inches w.g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	
	Air Volume (CFM)	110	113	80	82	50	53	150	151	130	130	110	110	110	113	100	106	90	95	80	82	
	Noise (sones)	<0.3	0.8	<0.3	0.4	<0.3	0.3	<0.3	0.7	<0.3	0.5	<0.3	<0.3	<0.3	0.8	<0.3	0.7	<0.3	0.6	<0.3	0.4	
Observatoristica	Power Consumption (watts)	9.8	16.1	5.5	10.2	3.5	7.0	13.0	22.0	10.0	17.0	7.0	13.5	9.8	16.1	8.0	14.0	6.5	11.7	5.5	10.2	
Characteristics (HVI tested data	Energy Efficiency (CFM/Watt)	11.5	7.2	15.3	8.4	15.1	8.1	11.5	6.8	13.1	7.8	15.7	8.2	11.5	7.2	13.0	7.9	14.5	8.5	15.3	8.4	
for 0.1" S.P.)	Speed (RPM)	931	1205	814	1131	747	1072	664	904	635	891	616	889	931	1205	895	1179	852	1146	814	1131	
	Current (amps)	0.10 0.16 0.06 0.10 0.04 0.0					0.07	0.13	0.21	0.10	0.17	0.07	0.13	0.10	0.16	0.09	0.14	0.07	0.12	0.06	0.10	
	MAX. Current (amps)			0.	27			0.33										0.27				
	Power Rating (V/Hz)	120/60						120/60						120/60								
	Motor Type	DC						DC						DC								
	Type of Motor Bearing	Ball						Ball					Ball									
Specifications	Thermal Fuse Protection	Yes								Ye	es			Yes								
	Blower Wheel Type		-	Sire	occo					Sirc	оссо							Sirocco				
	ENERGY STAR Qualified	Yes								Ye	es							Yes				
	Duct Diameter (Inches)	4 & 6								(3							4 & 6				
Installation	Mounting Opening (Inches sq.)	10-1/2						10-1/2										10-1/2				
	Grille Size (Inches sq.)	13						13						13								
	Lamp Watts			N	/A			N/A					N/A									
	Lumens (Im)			N	/A			N/A					N/A									
	Lumens Per Watt (LPW)			N	/A			N/A						N/A								
	Color Rendering Index			N	/A			N/A										N/A				
Light Specifications	Color Temperature (Kelvin)			N	/A					N	/A							N/A				
	Rated Life (hours)			N	/A					N	/A							N/A				
	Lamp Model #			N	/A					N	/A							N/A				
	Type of Lamp Socket			N	/A					N	/A							N/A				
Night Light Specs	Night Light Watts			N.	/A*					N/	'A*							N/A*				
Shipping	Gross Weight (lbs)	11.90				13.45										11.90						
	UL tub/Shower Enclosure			Υ	es					Ye	es			Yes								
Approved Code/Standard/	Washington VIAQ Code	Yes					Yes				Yes											
Regulation	California Title 24 Compliant			Y	es			Yes				Yes										
	Mfg in ISO 9001 Certified Facility			Υ	es			Yes					Yes									


^{*}Light specs may change. **Night Glo™ LED Night Light module is available.

NOTE: 0.25" w.g. = Installed Performance




DC Motor with SmartFlow™ Technology

WhisperGreen Select™ features the same revolutionary DC motor that comes with our WhisperGreen line of products. With built-in SmartFlow™ technology, WhisperGreen Select™ is designed to perform as rated. When the fan senses static pressure, its speed is automatically increased to ensure optimal CFM output. This feature provides peace of mind, as the installer doesn't have to worry about compromising the fan's performance.







	Wh	isper(Green	Selec	t (Fai	ı Only	Mod	els)					
	В	ase Fa	n wit	h Inte	grated	Multi	i-Spec	ed					
			F	V-05-	11VK	S1							
0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25				
70	71	60	66	50	53	40	43	30	33				
<0.3	0.4	<0.3	0.3	<0.3	0.3	<0.3	<0.3	<0.3	<0.3				
4.3	8.6	3.6	7.8	3.5	7.0	2.7	5.7	2.4	5.0				
17.2	8.7	17.5	8.8	15.1	8.1	16.3	8.2	14.2	7.6				
772	1112	750	1107	747	1072	731	1073	718	1062				
0.05	0.09	0.04	0.08	0.04	0.07	0.08	0.06	0.03	0.06				
					0.27								
					120/60)							
DC													
Ball													
					Yes								
					Sirocco)							
					Yes								
					4 & 6								
					10-1/2	2							
					13								
					N/A								
					N/A								
					N/A								
					N/A								
					N/A								
					N/A								
					N/A								
					N/A								
					N/A*								
					11.90								
					Yes								
					Yes								
					Yes								
					Yes								

	WhisperGreen Select (Fan Only Models) Base Fan with Multi-Speed Plug 'N Play Module																		
						Base F	an wi	th Mu	lti-Sp	eed Pi	ug 'N	Play I	Modul	е					
							FV	-11-1	5VK1	+ FV-\	/S15V	K1							
0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25
150	151	130	130	120	121	110	110	100	102	90	96	80	84	70	72	60	62	50	51
<0.3	0.7	<0.3	0.5	<0.3	0.4	<0.3	<0.3	<0.3	<0.3	<0.3	<0.3	<0.3	0.4	<0.3	0.4	<0.3	0.4	<0.3	0.4
13.0	22.0	10.0	17.0	7.4	14.1	7.0	13.5	5.6	11.3	4.9	10.7	4.4	9.6	3.8	8.6	3.6	7.7	3.1	6.8
11.5	6.8	13.1	7.8	16.2	8.6	15.7	8.2	17.9	9.0	18.6	9.0	18.2	8.8	18.4	8.4	16.7	8.1	16.1	7.5
664	904	635	891	615	884	616	889	603	886	595	891	604	911	602	918	622	919	616	928
0.13	0.21	0.10	0.17	0.08	0.14	0.07	0.13	0.06	0.11	0.06	0.11	0.05	0.10	0.05	0.09	0.04	0.08	0.04	0.07
									0.	33									
	120/60																		
DC Pall																			
Ball																			
Yes																			
Sirocco																			
									Y										
																			
									10-										
										3									
										/A									
										/A									
										/A									
										/A /A									
										/A /A									
										/A									
										/A									
									N/										
									13										
									Yı										
									Y										
									Y										
									Y										





LED Lighting

WhisperGreen Select™ fan/light models feature a contemporary flush mount grille that incorporates Two replaceable, ENERGY STAR rated, 7W GU24 base LED lamps. Panasonic's advanced LED technology lasts 4 times longer than compact fluorescent lamps and does not contribute to mercury waste when disposed.

WhisperGreenSelect -










				Wh	isper(Green	Selec	t (Fa	n/LED	Light	Mode	els)		
ODE	OLEIGATIONO					Base F	an wi	th LE	D Ligh	t				
SPE	CIFICATIONS		F	V-05-	11VKL	1			F	V-11-	15VKL	1	ı	
	Static Pressure in inches w.g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	
	Air Volume (CFM)	110	114	80	86	50	53	150	143	130	131	110	111	
	Noise (sones)	0.4	0.9	<0.3	0.6	<0.3	<0.3	0.6	0.9	<0.3	0.8	<0.3	0.6	
Characteristics	Power Consumption (watts)	11.1	18.0	6.0	11.1	4.0	7.0	16.5	24.0	12.0	21.0	8.5	16.0	
(HVI tested data	Energy Efficiency (CFM/Watt)	9.9	6.3	13.3	7.7	12.8	7.7	9.2	6.0	10.9	6.3	13.1	7.1	
for 0.1" S.P.)	Speed (RPM)	960	1237	837	1157	740	1081	730	941	679	926	652	914	
	Current (amps)	0.12	0.17	0.07	0.12	0.04	0.07	0.16	0.22	0.12	0.19	0.08	0.15	
	MAX. Current (amps)			0.	42					0.	48			
	Power Rating (V/Hz)			120	0/60			120/60						
	Motor Type	DC							DC					
	Type of Motor Bearing			В	all		Ball							
Specifications	Thermal Fuse Protection			Y	es					Y	es			
	Blower Wheel Type			Sirc	оссо					Sirc	оссо			
	ENERGY STAR Qualified			Y	es					Y	es			
	Duct Diameter (Inches)	4 & 6								(6			
Installation	Mounting Opening (Inches sq.)	10-1/2								10-	-1/2			
	Grille Size (Inches sq.)	13							13					
	Lamp Watts	2 x 7W						2 x 7W						
	Lumens (Im)			550lm p	er lamp*			550lm per lamp*						
	Lumens Per Watt (LPW)			80L	PW*			80LPW*						
Light Charifications	Color Rendering Index			>	80					>	80			
Light Specifications	Color Temperature (Kelvin)			30	00K					30	00K			
	Rated Life (hours)			40,	000					40,	000			
	Lamp Model #			LPI	HT7					LPI	HT7			
	Type of Lamp Socket			GL	124					GL	J24			
Night Light Specs	Night Light Watts			N/	A**					N/	A**			
Shipping	Gross Weight (lbs)	14.55 14.77												
	UL tub/Shower Enclosure			Y	es					Y	es			
Approved Code/Standard/	Washington VIAQ Code			Y	es			Yes						
Regulation	California Title 24 Compliant			Y	es			Yes						
	Mfg in ISO 9001 Certified Facility	Yes Yes												

Wh	isper	Green	Selec	et (Fa	n/LED	Light	Mod	els)					
Bas	se Fan	with L	ED Ligh	nt and	Integra	ited Mi	ulti-Sp	eed					
			FV-05	-11VK	SL1								
0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1					
110	114	100	105	90	94	80	86	70					
0.4	0.9	<0.3	0.8	<0.3	0.6	<0.3	0.6	<0.3					
11.1	18.0	8.7	15.0	7.0	12.8	6.0	11.1	4.7					
9.9	6.3	11.6	7.1	13.1	7.5	13.3	7.7	15.3					
960	1237	926	1213	872	1184	837	1157	796					
0.12	0.17	0.09	0.15	0.08	0.13	0.07	0.12	0.05					
				0.42	2								
120/60													
DC													
	Ball												
	Yes												
				Siroc	СО								
				Yes	;								
				4 &	6								
				10-1	/2								
				13									
				2 x 7	W								
			5	50lm pe	r lamp*								
				80LP	W*								
				>80									
				3000									
				40,0									
				LPH ⁻									
				GU2									
				N/A									
				14.3									
				Yes									
				Yes									
				Yes									







Wh	WhisperGreen Select (Fan/LED Light Models) Base Fan with LED Light and Integrated Multi-Speed													
Bas	se Fan	with LI	D Ligh	t and l	ntegrat	ed Mul	ti-Spee	d						
			FV-05	-11VK	SL1									
0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25						
71	60	62	50	53	40	43	30	35						
0.4	<0.3	0.3	<0.3	<0.3	<0.3	<0.3	<0.3	<0.3						
8.9	3.9	7.6	4.0	7.0	2.8	5.7	2.5	5.0						
8.2	15.9	8.4	12.8	7.7	14.6	7.7	12.8	7.4						
1119	769	1102	740	1081	739	1077	731	1058						
0.09	0.05	0.08	0.04	0.07	0.04	0.06	0.03	0.06						
0.42														
120/60														
DC														
	Ball													
Yes														
Sirocco														
				Yes										
				4 & 6										
				10-1/2										
				13										
				2 x 7W										
			550lr	n per lan	1p*									
			8	80LPW*										
				>80										
			:	3000K										
			-	40,000										
				LPHT7										
				GU24										
				N/A**										
				14.33										
				Yes										
				Yes										
				Yes										

	WhisperGreen Select (Fan/LED Light Models)																		
				Ba	se Fa	n with	LED	Light :	and M	ulti-S	peed I	Plug 'l	N Play	Modu	ıle				
							FV-	11-15	VKL1	+ FV-	VS15\	/K1							
0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25
150	143	130	131	120	122	110	111	100	102	90	90	80	82	70	71	60	62	50	52
0.6	0.9	<0.3	0.8	<0.3	0.6	<0.3	0.6	<0.3	0.5	<0.3	0.4	<0.3	0.4	<0.3	0.3	<0.3	0.3	<0.3	0.4
16.5	24.0	12.0	21.0	9.5	16.9	8.5	16.0	6.9	13.5	5.7	11.6	5.0	10.4	4.3	8.8	4.0	7.9	3.2	7.2
9.2	6.0	10.9	6.3	12.8	7.3	13.1	7.1	14.8	7.7	16.0	7.8	16.0	7.9	16.3	8.1	15.5	8.1	16.3	7.5
730	941	679	926	669	917	652	914	644	923	631	917	633	918	624	904	634	910	607	928
0.16	0.22	0.12	0.19	0.10	0.17	0.08	0.15	0.07	0.14	0.06	0.12	0.06	0.11	0.05	0.09	0.05	0.08	0.04	0.08
0.48																			
120/60																			
DC																			
Ball																			
Yes																			
Sirocco																			
Yes 6																			
									10-										
										3									
									2 x										
									550lm p										
									80L										
									>										
									300	00K									
									40,	000									
									LPI	łT7									
									GU	24									
									N/A	4**									
									14	.77									
									Ye	es									
									Ye	es									
									Ye	es									
									Ye	es									







Panasonic Eco Solutions of North America Eco Products Division

Two Riverfront Plaza Newark, NJ 07102

us.panasonic.com/ventfans

For Order Information

PHONE: 866-292-7299 FAX: 888-553-0723

ventfans@us.panasonic.com