



Service Entrance Fittings

Size (in.)	Part Number	Product Code
1/2	MH05	078302
3/4	MH07	078303
1	MH10	078304
1-1/4	MH12	078305
1-1/2	MH15	078306
2	MH20	078307
2-1/2	MH25	078308
3	MH30	078309
3-1/2	MH35	078310
4	MH40	078311



Offset Terminal Adapters

Size S x H (in)	Part Number	Product Code	OL (in)
1-1/4	MO12	078351	4.240
2	MO20	078352	4.360

Pull Elbow

Size (in.)	Part Number	Product Code
1/2 & 3/4	PULEL0705	078386



Nonmetallic Strain Relief Connectors

Kraloy's Nonmetallic Strain Relief Connectors are supplied with all the components you need for a complete connection. The connector body, a selection of grommets and compression rings accepting a range of cord dimensions, a sealing 'O' ring and metallic locknut are all supplied in one package. Available in 1/2" and 3/4" threaded hub and 3/4" PVC socket solvent weld configurations to accommodate a variety of applications.



Threaded Strain Relief Connector

Size (in.)	Part Number	Product Code
1/2	TSRCU05	278100
3/4	TSRCU07	278101

Strain Relief Connector

Size (in.)	Part Number	Product Code
3/4	SRCU07	278102



c/w 4 Grommets -
3/4" solvent weld
male end

Strain Relief Connector

Size (in.)	Part Number	Product Code
3/4	SRC15	077985

c/w 6 Grommets -
3/4" solvent weld
male end

Grommet Dimensions

Grommet	from	to	Grommet	from	to
	$\emptyset = .240"$	$\emptyset = .315"$		$\emptyset = .420"$	$\emptyset = .515"$
	$\emptyset = .320"$	$\emptyset = .415"$		$\emptyset = .520"$	$\emptyset = .615"$

Note: All four grommets and corresponding compression rings are supplied with TSRCU05, TSRCU07 & SRCU07.