




CAT#	A	B	C
ELB1	4.295	2.150	1.330
ELB2	5.090	2.430	1.540
ELB3	5.915	2.765	1.740
ELB4	7.894	3.665	2.490
ELB5	7.894	3.665	2.490
ELB6	10.134	4.275	3.100
ELB7	12.500	5.437	4.450
ELB8	12.500	5.657	4.450
ELB9	15.500	6.922	5.500
ELB10	15.500	6.922	5.500



CAT#	A	B	C
ET1	4.720	1.370	2.030
ET2	5.570	1.625	2.335
ET3	6.460	1.900	2.705
ET4	8.528	2.770	3.630
ET5	8.528	2.770	3.630
ET6	10.831	3.335	3.980
ET7	13.500	4.060	5.825
ET8	13.50	4.685	5.825
ET9	15.937	5.450	7.060
ET10	15.937	5.450	7.060



CAT#	A	B	C
ELR1/ELL1	4.295	1.370	2.030
ELR2/ELL2	5.090	1.625	2.330
ELR3/ELL3	5.915	1.900	2.650
ELR4/ELL4	7.894	2.770	3.385
ELR5/ELL5	7.894	2.770	3.385
ELR6/ELL6	10.134	3.335	3.810
ELR7/ELL7	12.500	5.437	4.450
ELR8/ELL8	12.500	5.657	4.450
ELR9/ELL9	15.500	6.922	5.500
ELR10/ELL10	15.500	6.922	5.500



CAT#	A	B	C
EC1	4.720	1.370	1.330
EC2	5.570	1.625	1.540
EC3	6.460	1.900	1.740
EC4	8.528	2.770	2.490
EC5	8.528	2.770	2.490
EC6	10.831	3.335	3.100
EC7	13.00	4.063	5.709
EC8	12.50	4.682	5.506
EC9	15.50	5.452	6.171
EC10	15.50	5.452	6.171

CONDUIT BODIES

EMT SET SCREW TYPE

COPPER FREE ALUMINUM

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
EMT LB TYPE					
ELB1	20470	1/2"	10	100	28
ELB2	20480	3/4"	10	50	19
ELB3	20490	1"	5	25	20
ELB4	20500	1 1/4"	2	10	13
ELB5	20510	1 1/2"	2	10	14
ELB6	20520	2"	1	5	13
ELB7	20530	2 1/2"	—	1	6
ELB8	20540	3"	—	1	6
ELB9	20550	3 1/2"	—	1	8
ELB10	20560	4"	—	1	8

EMT T TYPE

ET1	20690	1/2"	10	100	32
ET2	20700	3/4"	10	50	30
ET3	20710	1"	5	25	15
ET4	20720	1 1/4"	2	10	17
ET5	20730	1 1/2"	2	10	19
ET6	20740	2"	—	2	5
ET7	20781	2 1/2"	—	1	7
ET8	20782	3"	—	1	7
ET9	20783	3 1/2"	—	1	9
ET10	20784	4"	—	1	9

EMT LR TYPE

ELR1	20630	1/2"	10	100	30
ELR2	20640	3/4"	10	50	24
ELR3	20650	1"	5	25	16
ELR4	20660	1 1/4"	2	10	14
ELR5	20670	1 1/2"	2	10	17
ELR6	20680	2"	1	5	14
ELR7	20681	2 1/2"	—	1	6
ELR8	20682	3"	—	1	6
ELR9	20683	3 1/2"	—	1	8
ELR10	20684	4"	—	1	8

EMT LL TYPE

ELL1	20570	1/2"	10	100	30
ELL2	20580	3/4"	10	50	23
ELL3	20590	1"	5	25	18
ELL4	20600	1 1/4"	2	10	14
ELL5	20610	1 1/2"	2	10	16
ELL6	20620	2"	1	5	14
ELL7	20621	2 1/2"	—	1	6
ELL8	20622	3"	—	1	6
ELL9	20623	3 1/2"	—	1	8
ELL10	20624	4"	—	1	8

EMT C TYPE

EC1	20410	1/2"	10	100	24
EC2	20420	3/4"	10	50	21
EC3	20430	1"	5	25	25
EC4	20440	1 1/4"	2	10	15
EC5	20450	1 1/2"	2	10	17
EC6	20460	2"	1	5	13
EC7	20461	2 1/2"	—	1	6
EC8	20462	3"	—	1	7
EC9	20463	3 1/2"	—	1	8
EC10	20464	4"	—	1	8



E170258



E170258



E170258



E170258

