

Dimmers & Fan Speed Controls Rotary Fan Speed Controls

Pass & Seymour



No-Noise De-Hummers

Since the development of variable fan speed controls, many fans have made an annoying humming noise when their speed was reduced. Through the use of specially designed capacitive circuitry, these units can control fans at 3 or 4-speed levels in slide, rotary and dual styles with virtually no fan motor noise.

Catalog Number	Description	Ratings	Color
1.5A Max. Specification Grade Rotary Fan Speed Controls – No-Noise De-Hummers, RFI Protected*			
94003-I 94003-W 94003-LA	3-Speed, Low-Medium-High	1.5A max.	Ivory White Light Almond
94004-CL 94004-I 94004-W 94004-LA	4-Speed, Low-High	1.5A max.	Clear Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94003-LAV.

Dual Control Features	
<ul style="list-style-type: none"> Fits one gang box. Controls both fan speed and light level. 	<ul style="list-style-type: none"> Decorator styling.

Catalog Number	Description	Ratings	Color
1.5A/300W Max. Specification Grade Dual Controls – No-Noise De-Hummers*			
94315-I 94315-W 94315-LA	3-Speed Fan Control and 2-Level Hi/Low Dimmer	1.5A/300W max.	Ivory White Light Almond
94215-I 94215-W 94215-LA	4-Speed Fan Control and 2-Level Hi/Low Dimmer	1.5A/300W max.	Ivory White Light Almond


Requires 3 wire installation.

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94315-LAV.

Catalog Number	Description	Ratings	Color
3A/300W Max. Specification Grade Dual Controls*			
94331-I 542-433	Dial Speed Control and Dimmer	3A/300W max.	Ivory White

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94331-IV.


Catalog Number	Description	Color
Accessories for Dual Controls		
109-019V 109-020V 109-018V	Adapter Kit for Dual Fan/Light Controls	Ivory White Light Almond




Dual Control Connection Diagram

Note: All controls on this page may be ganged without de-rating.

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.



94004
94003



94215
94315
94331
542-433