



Turnlok® Devices Receptacles, Connectors, Plugs, Inlets


4 Wire Grounded 50A, 125/250V; 50A 3ø, 250V; 50A, 250VDC 600VAC




Corrosion Resistant Receptacle



Corrosion Resistant Connector



Corrosion Resistant Plug




Corrosion Resistant Flanged Inlet

Catalog Number	Rating A. V.	Description	Cord Diameter	3rd Party Compliance		
				UL498	FSUL WC596	CSA
Receptacles						
CR6369	50 125/250	Corrosion Resistant		•		•
CS6369	50 125/250	California Standard		•		•
CS8369	50 3ø, 250	California Standard		•		•
CS8169	50 3ø, 480	California Standard		•		•
3769	50 250VDC, 600VAC	Corrosion Resistant		•		•
*7379	50 250VDC, 600VAC	Corrosion Resistant		•		•
Connectors						
CR6364	50 125/250	Corrosion Resistant	.680"-1.125"	•		•
CS6364	50 125/250	California Standard	.680"-1.125"	•		•
CS8364	50 3ø, 250	California Standard	.680"-1.125"	•		•
CS8164	50 3ø, 480	California Standard	.680"-1.125"	•		•
3764	50 250VDC, 600VAC	Corrosion Resistant	.680"-1.125"	•		•
*7764	50 250VDC, 600VAC	Corrosion Resistant	.680"-1.125"	•		•
Plugs						
CR6365	50 125/250	Corrosion Resistant	.680"-1.125"	•		•
CS6365	50 125/250	California Standard	.680"-1.125"	•		•
CS8365	50 3ø, 250	California Standard	.680"-1.125"	•		•
CS8165	50 3ø, 480	California Standard	.680"-1.125"	•		•
3765	50 250VDC, 600VAC	Corrosion Resistant	.680"-1.125"	•		•
*7765	50 250VDC, 600VAC	Corrosion Resistant	.680"-1.125"	•		•
Flanged Inlets						
CR6375	50 125/250	Corrosion Resistant		•		•
CS6375	50 125/250	California Standard		•		•
CS8375	50 3ø, 250	California Standard		•		•
CS8175	50 3ø, 480	California Standard		•		•
3775	50 250VDC, 600VAC	Corrosion Resistant		•		•
*7958	50 250VDC, 600VAC	Corrosion Resistant		•		•

*Devices for replacement use only in existing installations.

Catalog Number	Description
Accessories	
7770	Weatherproof Cover for 50A Locking Receptacles, Thermoplastic
CR7716-N	Weatherproof Boot, 50A Locking Connector
CR7717-N	Weatherproof Boot, 50A Locking Plug
S750	Stainless Steel Plate for 50A Locking Receptacle (style 97)
PSLD	Lockout Device



Turnlok® Devices Plugs & Connectors Product Specifications & Performance



50 Amp Locking Plugs & Connectors

	Corrosion Resistant	California Standard
Plugs		
Plug Shroud	Zytel Supertough Nylon	Zytel Supertough Nylon
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Nylon	Nylon
Cord Clamp	Nylon	Nylon
Blades	Nickel-Plated Brass	Brass
Terminal Clamp	Nickel-Plated Brass	Brass
Terminal Screws	Nickel-Plated Brass	Brass
Ground Screw	Nickel-Plated Brass	Brass
Assembly Screws	Stainless Steel	Stainless Steel
Connectors		
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Nylon	Nylon
Cord Clamp	Nylon	Nylon
Contacts	Nickel-Plated Brass	Brass
Terminal Clamp	Nickel-Plated Brass	Brass
Terminal Screws	Nickel-Plated Brass	Brass
Ground Screw	Nickel-Plated Brass	Brass
Assembly Screws	Stainless Steel	Stainless Steel
Performance		
Electrical		
Dielectric Withstand Voltage	3000V minimum	
Maximum Working Voltage	600VAC	
Current Interrupting	Certified for current interrupting at full rated current	
Temperature Rise	30°C maximum after 50 cycles at 150% rated current	
Mechanical		
Cord Accommodations	Round portable service cords of diameters in accordance with the device rating as defined in UL62	
Cord Grip Accommodations	.680"-1.125" diameter	
Terminal Identification	Color Coded Terminal Screws	
Terminal Accommodation	#10 AWG min.-#4 AWG max.	
Product Identification	Amperage/Voltage hot stamped on device	
Environmental		
Flammability	UL94 HB or better	
Operating Temperature	Maximum Continuous: 75°C Minimum: -40°C without impact	