

# SOCKETS

## Porcelain Sockets



### KEYLESS TWIN

**22275**

STANDARD BASE  
STRAPPED TO  
PREVENT ROTATION  
BUSHING 1/8-IP WITH  
SET SCREW  
660 WATTS  
250 VOLTS  
HEIGHT - 3"



### FIXTURE

**22281 - 3-WAY**

MOGUL BASE  
REMOVABLE KNOB  
BUSHING 1/4-IP  
750 WATTS  
250 VOLTS  
HEIGHT - 4 1/4"



### FIXTURE

**22267**

STANDARD BASE  
1/8-IP HICKEY  
660 WATTS  
250 VOLTS  
HEIGHT - 2"



### FIXTURE

**22282**

MOGUL BASE  
750 WATTS  
250 VOLTS  
HEIGHT - 2 5/8"



### KEYLESS TWIN

**22274**

STANDARD BASE  
BUSHING 1/8-IP  
WITH SET SCREW  
660 WATTS  
250 VOLTS  
HEIGHT - 2 1/8"



### FIXTURE

**22371**

STANDARD BASE  
1/4-IP HICKEY  
660 WATTS  
250 VOLTS  
HEIGHT - 2"



### TWO-PIECE

**22266 - SIGN RECEPTACLE**

STANDARD BASE  
660 WATTS  
250 VOLTS  
HEIGHT - 1 1/2"



### KEYLESS

**22269**

STANDARD BASE  
BUSHING 1/8-IP  
WITH SET SCREW  
660 WATTS  
250 VOLTS  
HEIGHT - 2"



### THREADED

**22272**

STANDARD BASE  
BUSHING 1/8-IP WITH  
SET SCREW  
RING SIZE - 2 5/8"  
660 WATTS  
250 VOLTS  
HEIGHT - 2 1/8"