



10128 ICSN, WSOI
 9-Light Chandelier
 32"W x 31.5"H
 9 x 100w MB Bulbs



10122 ICSN, WSOI
 3-Light Chandelier
 19"W x 17"H
 3 x 100w MB Bulbs



10125 ICSN, WSOI
 5-Light Chandelier
 26"W x 22.5"H
 5 x 100w MB Bulbs

Conversion Kits

Conversion Kits are available to convert specified semi-flush mounts to invert bowl pendants. Included in the kit is a canopy, chain and extra loop to screw to the top of the semi-flush mount, all in matching finish.

CKT001AC Conversion Kit
Acorn
Compatible with 5843MRAC

CKT001PE Conversion Kit
Pewter
Compatible with 5833FTPE, 5843MRPE

CKT001CS Conversion Kit
Country Stone
Compatible with 5843MRCS

CKT001SN Conversion Kit
Satin Nickel
Compatible with 5833FTSN, 5843MRSN & 10120ICSN

CKT001OI Conversion Kit
Oil Rubbed Bronze
Compatible with 5833FTOI, 5843MROI, 5843WSOI & 10120WSOI

Diffusers

Diffusers are used to conceal light clusters in pendants and wall sconces. Many of Maxim Lighting's invert bowl pendants have diffusers built in or included. Optional diffusers are also available.



DIF001WT Diffuser
White
Compatible with 8025MRAC, 8025MRBK, 8025MRKB, 8025MRSN and 8025WSKB



DIF002WT Diffuser
White
Compatible with 8026MRSN

Finishes

AC Acorn	EG Etruscan Gold	MW Matte White	SST Stainless Steel
AD Auburn Dusk	FF French Floral	NI Natural Iron	SV Silver
AF Auburn Florentine	FL Filbert	OI Oil Rubbed Bronze	TT Textured Terra
AP Antique Pecan	FN Florentine	PB Polished Brass	TW Textured White
BC Bali Collection	GA Golden Auburn	PBPC Polished Brass/Chrome	VC Vintage Copper
BG Black Gold	GB Greek Bronze	PC Polished Chrome	VI Vienna Ivory
BK Black	GC Grand Canyon	PD Platinum Dusk	WB Windsor Bronze
BM Brushed Metal	GF Golden Fawn	PE Pewter	WC Weathered Copper
BN Brighton	HA Honey Auburn	PS Plated Silver	WR Weathered Russet
BZ Bronze	HB Heirloom Brass	PT Pine Tree	WT White
CH Chocolate	KB Kentucky Bronze	RB Rustic Burnished	
CR Canyon Rock	LG Light Gold	RC Roasted Chestnut	
CS Country Stone	MA Mahogany	RE Rustic Ebony	
CU Colonial Umber	MB Metallic Bronze	SA Satin Aluminum	
DB Desert Bronze	MD Modello	SN Satin Nickel	

Glass

AI	Amber Ice	EF	Early Frost	JF	Java Fog	SV	Soft Vanilla
AV	Amber Vanilla	EM	Ember	KL	Karmel	TC	Textured Clear
BL	Burnished Lichen	EV	Embossed Vanilla	LT	Latte	VA	Vintage Amber
CD	Seedy	FI	Frosted Ivory	MC	Mocha Cloud	VS	Vanilla Swirl
CF	Cafe	FL	Frost Lichen	MR	Marble	WH	Wheat
CI	Clear Ice	FT	Frosted	SA	Screen Amber	WI	White Ice
CL	Clear	IC	Ice	SC	Stone Candle	WS	Wilshire
CY	Crystal	JA	Java Swirl	SI	Screen Ivory	WT	White

Shades

BI	Burnt Ivory	CH	Champagne	KB	Kentucky Bronze	VN	Vanilla
BL	Beige Linen	GR	Grass Reed	PD	Ponderosa	WH	Wheat
BT	Black Tie	GS	Golden Sheen	RT	Rattan	WT	White
CC	Country Cottage	GT	Golden Taupe	TN	Tan		



Catalog Legend



Energy Star
Certified

Installing new ENERGY STAR qualified light fixtures is a smart way to save energy and money. Maxim Lighting is proud to be a ENERGY STAR partner. Look for this ENERGY STAR logo to find Maxim Lighting fixtures that use 1/4 of the energy of traditional incandescent fixtures and last up to 10 times longer. More information on ENERGY STAR can be found on the ENERGY STAR web site at energystar.gov.



California
Title 24

All new homes, additions, alterations and most commercial buildings in California must meet minimum energy efficiency standards contained in Title 24, Part 6 of the California Code of Regulations. When you see the California Title 24 symbol next to a Maxim Lighting fixtures, you can be assured that the fixtures complies. More information on California Title 24 can be found on the California Energy Commission web site at energy.ca.gov/title24.



Installs
Up or Down



Installs
on Slope
Ceiling

















Diffuser
Available



Conversion
Kit

Lamping Guide

Code	Description	Type	Code	Description	Type
 R20	R Shape Medium Base 2.5" W	Incandescent	 R30	R Shape Medium Base 3.75" W	Incandescent
 CA	Candelabra Base	Incandescent	 T5	Tubular Mini Bipin Base .625" W	Fluorescent
 G9	T Shape Bi-Pin (G9) Base .5" W	Xenon	 T8	Tubular Medium Bipin Base 1" W	Fluorescent
 GU24	CFL GU24 Bi-Pin Base	Fluorescent	 Circline T9	Tubular Circline 4 Pin Base 1.125" W	Fluorescent
 MB	Medium Base	Incandescent	 Circline T5	Tubular Circline 2GX13 Base .625" W	Fluorescent
 MBT10	T Shape Medium Base 1.25" W	Incandescent	 G8	T4 Bi-Pin (G8) Base	Xenon
 PAR30	PAR Shape Short Neck Medium Base 3.75" W	Halogen	 Wedge	T5 Mini Wedge Base	Xenon