

2016 EXPANDED

LED Program

...see what's new inside!



Westinghouse

INNOVATION YOU CAN BE SURE OF



Energy Saving



**Environmentally
Conscious**



Long Life

60+

NEW LED Lamps!

Making the switch to LED lamps provides significant energy savings by using less energy to produce the same light output over incandescent, halogen and fluorescent alternatives. On average, LED lamps last much longer and consume 80% less energy when compared to incandescent lamps. They do not contain harmful mercury, making them the ideal choice for many applications.



DECORATIVE LED LAMPS

20+ NEW

Decorative LED lamps are an energy-saving choice for various applications in your home, like chandeliers, sconces and ceiling fans. Our globe lamps provide ample illumination in pendants and vanity fixtures.



FILAMENT LED LAMPS

NEW AMBER OPTIONS

Use LED filament lamps for a traditional look. Filament LEDs are aesthetically designed to look like traditional incandescent lamps, making them ideal for fixtures with visible lamps. Available in amber and clear finishes for two distinct looks.



All LED lamps in this brochure are approved for use in damp locations.

GENERAL PURPOSE LED LAMPS

20+ NEW

LED technology has evolved, and now there is a general purpose lamp for any application, from table lamps to ceiling fans. Maximize your energy savings with 25,000 or 12,000 hour lamps, available in a variety of finishes, color temperatures and lumens.



REFLECTOR LED LAMPS

15+ NEW

Upgrade your track or recessed lighting with energy-saving LED reflectors. Recessed LED downlights are ideal for renovations and new construction. Outdoor flood lamps, available in clear and festive colors, provide security at night or add a decorative touch.



SPECIALTY LED LAMPS

NEW DIMMABLE OPTIONS

Westinghouse offers a complete assortment of specialty LED lamps, including halogen alternatives. From night lights to landscape lighting, there is an LED lamp that provides longer life and energy savings for any specialty application.



DECORATIVE LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
DECORATIVE														
03211	3	Cand.	3B10/LED/DIM/CL/CB/30 1CD	Card	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.85"
33045	3	Cand.	3B10/LED/DIM/CL/CB/30	Hanging Box	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.85"
03212	3	Med.	3B10/LED/DIM/CL/30 1CD	Card	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.67"
33046	3	Med.	3B10/LED/DIM/CL/30	Hanging Box	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.67"
33204	5	Cand.	5B11/LED/DIM/CL/CB/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.78"
33141	5	Cand.	5B11/LED/DIM/CL/CB/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.86"
33205	5	Med.	5B11/LED/DIM/CL/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.82"
33144	5	Med.	5B11/LED/DIM/CL/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.82"
05121	5	Med.	5C11/LED/SW/27 2CD	Card (2)	40	Warm White	Soft White	2700	80	300	12000	10.9	\$0.60	4.01"
05122	5	Cand.	5C11/LED/SW/CB/27 2CD	Card (2)	40	Warm White	Soft White	2700	80	300	12000	10.9	\$0.60	4.01"
05123	5	Med.	5C11/LED/CL/27 2CD	Card (2)	40	Warm White	Clear	2700	80	300	12000	10.9	\$0.60	4.01"
05124	5	Cand.	5C11/LED/CL/CB/27 2CD	Card (2)	40	Warm White	Clear	2700	80	300	12000	10.9	\$0.60	4.01"
33206	5	Cand.	5CA11/LED/DIM/CL/CB/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.98"
33145	5	Cand.	5CA11/LED/DIM/CL/CB/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.98"
33207	5	Med.	5CA11/LED/DIM/CL/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.94"
33146	5	Med.	5CA11/LED/DIM/CL/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.94"
33200	7	Cand.	7B13/LED/DIM/CL/CB/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.25"
33130	7	Cand.	7B13/LED/DIM/CL/CB/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.25"
33201	7	Med.	7B13/LED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.25"
33132	7	Med.	7B13/LED/DIM/CL/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.25"
05125	7	Med.	7C13/LED/SW/27 2CD	Card (2)	60	Warm White	Soft White	2700	80	500	12000	10.9	\$0.84	4.48"
05127	7	Cand.	7C13/LED/SW/CB/27 2CD	Card (2)	60	Warm White	Soft White	2700	80	500	12000	10.9	\$0.84	4.48"
05128	7	Med.	7C13/LED/CL/27 2CD	Card (2)	60	Warm White	Clear	2700	80	500	12000	10.9	\$0.84	4.48"
05129	7	Cand.	7C13/LED/CL/CB/27 2CD	Card (2)	60	Warm White	Clear	2700	80	500	12000	10.9	\$0.84	4.48"
33202	7	Cand.	7CA13/LED/DIM/CL/CB/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.49"
33138	7	Cand.	7CA13/LED/DIM/CL/CB/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.49"
33203	7	Med.	7CA13/LED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.45"
33139	7	Med.	7CA13/LED/DIM/CL/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.45"
GLOBE														
33213	7	Cand.	7G16.5/LED/DIM/CL/CB/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	2.99"
33128	7	Cand.	7G16.5/LED/DIM/CL/CB/27	Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	2.99"
33214	7	Med.	7G16.5/LED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	2.93"
33129	7	Med.	7G16.5/LED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	2.93"
05131	7	Cand.	7G16.5/LED/DIM/SW/CB/27 1CD	Card	60	Warm White	Soft White	2700	80	500	25000	22.8	\$0.84	2.97"
05130	7	Med.	7G16.5/LED/DIM/SW/27 1CD	Card	60	Warm White	Soft White	2700	80	500	25000	22.8	\$0.84	2.97"
03192	7	Med.	7G19/LED/DIM/SW/27 1CD	Card	60	Warm White	Soft White	2700	80	500	25000	22.8	\$0.84	3.52"
53011 ▲	6	Med.	6G25/LED/DIM/SW/30	Box	60	Warm White	Soft White	3000	80	500	25000	22.8	\$0.72	4.33"
05149	7	Med.	7G25/LED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.42"

◆ Wet Location Approved

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh

▲ Approved for use in totally enclosed fixtures

GENERAL PURPOSE LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
OMNI A15														
05134 ▲	4.5	Med.	4.5OMNIA15/LED/SW/27 1CD	Card	40	Warm White	Soft White	2700	80	350	12000	10.9	\$0.54	3.55"
05136 ▲	6	Med.	6OMNIA15/LED/SW/27 1CD	Card	60	Warm White	Soft White	2700	80	600	12000	10.9	\$0.72	3.55"
05135	7	Med.	7OMNIA15/LED/CL/27 1CD	Card	40	Warm White	Clear	2700	80	450	12000	10.9	\$0.84	3.50"
03191	7	Med.	7OMNIA15/LED/DIM/SW/27 1CD	Card	40	Warm White	Soft White	2700	80	450	25000	22.8	\$0.84	3.48"
A19														
03798 ▲	14	Med.	14A19/LED/SW/30	Box	100	Warm White	Soft White	3000	80	1500	12000	10.9	\$1.69	4.33"
05158 ▲	14	Med.	14A19/LED/SW/30 2PK	Box (2)	100	Warm White	Soft White	3000	80	1500	12000	10.9	\$1.69	4.33"
05142 ▲	14	Med.	14A19/LED/SW/50	Box	100	Daylight	Soft White	5000	80	1550	12000	10.9	\$1.69	4.33"
OMNI A19														
33425 ▲	5.5	Med.	5.5OMNIA19/LED/DIM/SW/27	Box	40	Warm White	Soft White	2700	80	450	25000	22.8	\$0.66	4.33"
43098 ▲	5.5	Med.	5.5OMNIA19/LED/DIM/SW/30	Box	40	Warm White	Soft White	3000	80	470	25000	22.8	\$0.66	4.33"
33464 ▲	6	Med.	6OMNIA19/LED/SW/27	Box	40	Warm White	Soft White	2700	80	450	25000	22.8	\$0.72	4.33"
33189 ▲	6	Med.	6OMNIA19/LED/SW/30	Box	40	Warm White	Soft White	3000	80	450	12000	10.9	\$0.72	4.33"
05156 ▲	6	Med.	6OMNIA19/LED/SW/30 4PK	Box (4)	40	Warm White	Soft White	3000	80	450	12000	10.9	\$0.72	4.33"
05138 ▲	6	Med.	6OMNIA19/LED/SW/50	Box	40	Daylight	Soft White	5000	80	470	12000	10.9	\$0.72	4.33"
05144 ▲	6	Med.	6OMNIA19/LED/DIM/SW/50	Box	40	Daylight	Soft White	5000	80	470	25000	22.8	\$0.72	4.33"
05137	7	Med.	7OMNIA19/LED/CL/27	Box	40	Warm White	Clear	2700	80	480	12000	10.9	\$0.84	4.41"
05143	7	Med.	7OMNIA19/LED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	480	25000	22.8	\$0.84	4.41"
33697 ▲	9	Med.	9OMNIA19/LED/SW/27	Box	60	Warm White	Soft White	2700	80	800	25000	22.8	\$1.08	4.33"
03697 ▲	9	Med.	9OMNIA19/LED/SW/27	Box	60	Warm White	Soft White	2700	80	790	40000	36.5	\$1.08	4.33"
33696 ▲	9	Med.	9OMNIA19/LED/DIM/SW/27	Box	60	Warm White	Soft White	2700	80	800	25000	22.8	\$1.08	4.33"
33440 ▲	9	Med.	9OMNIA19/LED/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	800	25000	22.8	\$1.08	4.33"
03440 ▲	9	Med.	9OMNIA19/LED/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	800	40000	36.5	\$1.08	4.33"
33127 ▲	9	Med.	9OMNIA19/LED/SW/30	Box	60	Warm White	Soft White	3000	80	800	12000	10.9	\$1.08	4.33"
05160 ▲	9	Med.	9OMNIA19/LED/SW/30 4PK	Box (4)	60	Warm White	Soft White	3000	80	800	12000	10.9	\$1.08	4.33"
33439 ▲	9	Med.	9OMNIA19/LED/DIM/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	830	25000	22.8	\$1.08	4.33"
43094 ▲	9	Med.	9OMNIA19/LED/DIM/SW/30	Box	60	Warm White	Soft White	3000	80	830	25000	22.8	\$1.08	4.33"
05140 ▲	9	Med.	9OMNIA19/LED/SW/50	Box	60	Daylight	Soft White	5000	80	800	12000	10.9	\$1.08	4.33"
43097 ▲	9	Med.	9OMNIA19/LED/DIM/SW/50	Box	60	Daylight	Soft White	5000	80	900	25000	22.8	\$1.08	4.33"
33158 ▲	9	GU24	9OMNIA19/LED/DIM/SW/GU24/27	Box	60	Warm White	Soft White	2700	80	800	25000	22.8	\$1.08	4.33"
05139	10	Med.	10OMNIA19/LED/CL/27	Box	60	Warm White	Clear	2700	80	800	12000	10.9	\$1.20	4.41"
03696 ▲	10	Med.	10OMNIA19/LED/DIM/SW/27	Box	60	Warm White	Soft White	2700	80	790	40000	36.5	\$1.20	4.33"
03439 ▲	10	Med.	10OMNIA19/LED/DIM/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	800	40000	36.5	\$1.20	4.33"
43053 ▲	11	Med.	11OMNIA19/LED/DIM/SW/30	Box	75	Warm White	Soft White	3000	80	1100	25000	22.8	\$1.32	4.33"
33190 ▲	11	Med.	11OMNIA19/LED/SW/30	Box	75	Warm White	Soft White	3000	80	1100	12000	10.9	\$1.32	4.33"
05157 ▲	11	Med.	11OMNIA19/LED/SW/30 2PK	Box (2)	75	Warm White	Soft White	3000	80	1100	12000	10.9	\$1.32	4.33"
05141 ▲	11	Med.	11OMNIA19/LED/SW/50	Box	75	Daylight	Soft White	5000	80	1150	12000	10.9	\$1.20	4.33"
05145 ▲	11	Med.	11OMNIA19/LED/DIM/SW/50	Box	75	Daylight	Soft White	5000	80	1150	25000	22.8	\$1.20	4.33"
OMNI A21														
33136	15	Med.	15OMNIA21/LED/DIM/SW/27	Box	100	Warm White	Soft White	2700	80	1600	25000	22.8	\$1.81	5.28"
33140	3/ 9/ 17	Med.	3/9/17OMNIA21/LED/3WAY/SW/27	Box	30/ 60/ 100	Warm White	Soft White	2700	80	350/ 810/ 1600	25000	22.8	\$2.05	5.28"
SPECIALTY - COLOR OMNI A19														
03153 ◆▲	5	Med.	5OMNIA19/LED/R	Box	40	—	Red	—	—	—	25000	22.8	\$0.60	4.33"
03154 ◆▲	6	Med.	6OMNIA19/LED/B	Box	40	—	Blue	—	—	—	25000	22.8	\$0.72	4.33"
03152 ◆▲	6	Med.	6OMNIA19/LED/G	Box	40	—	Green	—	—	—	25000	22.8	\$0.72	4.33"

◆ Wet Location Approved

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh

▲ Approved for use in totally enclosed fixtures

NEW!

Visit www.westinghouselighting.com for our latest energy-saving LED products and dimmer compatibilities.

REFLECTOR LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
MR11														
05152	4	GU4	4MR11/LED/FL/GU4/30 1CD	Card	30	Warm White	White	3000	80	250	25000	22.8	\$0.48	1.52"
05153	4	GU10	4MR11/LED/DIM/FL/GU10/30 1CD	Card	25	Warm White	White	3000	80	250	25000	22.8	\$0.48	1.89"
MR16														
03209 ▲	5	GU5.3	5MR16/LED/DIM/FL/30 1CD	Card	35	Warm White	Clear	3000	80	370	25000	22.8	\$0.60	1.85"
03638 ▲	5	GU5.3	5MR16/LED/DIM/FL/30	Hanging Box	35	Warm White	Clear	3000	80	370	25000	22.8	\$0.60	1.85"
03208 ▲	7	GU5.3	7MR16/LED/DIM/FL/30 1CD	Card	50	Warm White	Clear	3000	80	520	25000	22.8	\$0.84	1.85"
03491 ▲	7	GU5.3	7MR16/LED/DIM/FL/30	Hanging Box	50	Warm White	Clear	3000	80	520	25000	22.8	\$0.84	1.85"
03210	7	GU10	7MR16/LED/DIM/NFL/GU10/30 1CD	Card	50	Warm White	Clear	3000	80	500	25000	22.8	\$0.84	2.2"
33032	7	GU10	7MR16/LED/DIM/NFL/GU10/30	Hanging Box	50	Warm White	Clear	3000	80	500	25000	22.8	\$0.84	2.2"
REFLECTOR														
05154	4	Inter.	4R14/LED/DIM/FL/1IN/27 1CD	Card	25	Warm White	Frost	2700	80	250	25000	22.8	\$0.48	2.17"
05155	6	Med.	6R16/LED/DIM/FL/27 1CD	Card	45	Warm White	Frost	2700	80	450	25000	22.8	\$0.72	3.23"
43050	7	Med.	7R20/LED/DIM/FL/27	Box	50	Warm White	Frost	2700	80	550	25000	22.8	\$0.84	3.82"
33161	7	Med.	7R20/LED/DIM/FL/30	Box	50	Warm White	Frost	3000	80	550	25000	22.8	\$0.84	3.82"
53000	8	Med.	8R30/LED/DIM/FL/27	Box	65	Warm White	Frost	2700	80	650	25000	22.8	\$0.96	5.16"
03159	8.5	GU24	8.5R30/LED/DIM/FL/GU24/27	Box	65	Warm White	Frost	2700	80	650	25000	22.8	\$1.02	4.96"
53055 ▲	9	Med.	9BR30/LED/DIM/FL/27	Box	65	Warm White	Frost	2700	80	750	25000	22.8	\$1.08	5.24"
53010 ▲	9	Med.	9BR30/LED/DIM/FL/30	Box	65	Warm White	Frost	3000	80	750	25000	22.8	\$1.08	5.24"
05148 ▲	9	Med.	9BR30/LED/DIM/FL/50	Box	65	Daylight	Frost	5000	80	780	25000	22.8	\$1.08	5.16"
43063	11.5	Med.	11.5R40/LED/DIM/FL/27	Box	75	Warm White	Frost	2700	80	940	25000	22.8	\$1.39	6.46"
33162	11.5	Med.	11.5R40/LED/DIM/FL/30	Box	75	Warm White	Frost	3000	80	970	25000	22.8	\$1.39	6.46"
33163	16.5	Med.	16.5R40/LED/DIM/FL/27	Box	85	Warm White	Frost	2700	80	1200	25000	22.8	\$1.99	6.46"
43064	16.5	Med.	16.5R40/LED/DIM/FL/30	Box	85	Warm White	Frost	3000	80	1230	25000	22.8	\$1.99	6.46"
PAR16 REFLECTOR														
33067 ▲	6	Med.	6PAR16/LED/DIM/FL/30	Box	45	Warm White	Clear	3000	80	470	25000	22.8	\$0.72	3.50"
PAR20 REFLECTOR														
43012 ▲	7	Med.	7PAR20/LED/DIM/FL/30	Box	50	Warm White	Clear	3000	80	470	25000	22.8	\$0.84	3.50"
PAR30 REFLECTOR														
43160 ▲	10	Med.	10PAR30S/LED/DIM/FL/30	Box	75	Warm White	Clear	3000	80	840	25000	22.8	\$1.20	3.58"
53013 ▲	10	Med.	10PAR30/LED/DIM/FL/30	Box	75	Warm White	Clear	3000	80	840	25000	22.8	\$1.20	4.57"
PAR38 REFLECTOR														
03110 ▲▲	15	Med.	15PAR38/LED/OutdoorFL/30	Box	90	Warm White	Clear	3000	80	1310	25000	22.8	\$1.81	5.32"
03114 ▲▲	15	Med.	15PAR38/LED/OutdoorFL/30 2PK	Box (2)	90	Warm White	Clear	3000	80	1310	25000	22.8	\$1.81	5.32"
53014 ▲	15	Med.	15PAR38/LED/DIM/FL/30	Box	90	Warm White	Clear	3000	80	1350	25000	22.8	\$1.81	5.24"
SPECIALTY - COLOR PAR38 REFLECTOR														
03147 ▲▲	11	Med.	11PAR38/LED/FL/R	Box	100	—	Red	—	—	—	25000	22.8	\$1.32	5.32"
03149 ▲▲	15	Med.	15PAR38/LED/FL/G	Box	100	—	Green	—	—	—	25000	22.8	\$1.81	5.32"
03151 ▲▲	15	Med.	15PAR38/LED/FL/B	Box	100	—	Blue	—	—	—	25000	22.8	\$1.81	5.32"

◆ Wet Location Approved

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh

▲ Approved for use in totally enclosed fixtures

FILAMENT LAMPS

LAMPS SHOWN UNLIT



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
A TYPE														
03166 ▲	5	Med.	5A15/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	3.19"
03164 ▲	5	Med.	5A19/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	3.97"
05151 ▲	5	Med.	5A19/FilamentLED/DIM/A/20 1CD	Card	40	Warm White	Amber	2000	80	420	15000	13.6	\$0.60	3.97"
03165 ▲	7.5	Med.	7.5A19/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	806	15000	13.6	\$0.90	3.97"
BT15														
03167 ▲	5	Med.	5BT15/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	4.05"
B11 DECORATIVE														
03168 ▲	5	Cand.	5B11/FilamentLED/DIM/CL/CB/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	4.13"
03169 ▲	5	Med.	5B11/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	3.58"
CA10 DECORATIVE														
03170 ▲	5	Cand.	5CA10/FilamentLED/DIM/CL/CB/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	4.52"
03171 ▲	5	Med.	5CA10/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	3.93"
05132 ▲	5	Cand.	5CA10/FIILED/DIM/A/CB/20 1CD	Card	40	Warm White	Amber	2000	80	400	15000	13.6	\$0.60	4.52"
F15														
03193 ▲	2.5	Med.	2.5F15/FIILED/DIM/CL/27 1CD	Card	25	Warm White	Clear	2700	80	250	15000	13.6	\$0.30	4.33"
03195 ▲	2.5	Med.	2.5F15/FilaLED/DIM/A/20 1CD	Card	25	Warm White	Amber	2000	80	190	15000	13.6	\$0.30	4.33"
03194 ▲	5	Med.	5F15/FilamentLED/DIM/CL/27 1CD	Card	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	4.33"
03196 ▲	5	Med.	5F15/FilamentLED/DIM/A/20 1CD	Card	40	Warm White	Amber	2000	80	400	15000	13.6	\$0.60	4.33"
G25 GLOBE														
03172 ▲	5	Med.	5G25/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	4.65"
03173 ▲	7.5	Med.	7.5G25/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	806	15000	13.6	\$0.90	4.65"
G40 GLOBE														
03174 ▲	5	Med.	5G40/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	6.73"
03175 ▲	7.5	Med.	7.5G40/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	806	15000	13.6	\$0.90	6.73"
ST20														
03176 ▲	2.5	Med.	2.5ST20/FilamentLED/DIM/A/20	Box	25	Warm White	Amber	2000	80	190	15000	13.6	\$0.30	5.31"
03177 ▲	5	Med.	5ST20/FilamentLED/DIM/A/20	Box	40	Warm White	Amber	2000	80	420	15000	13.6	\$0.60	5.31"
03178 ▲	7.5	Med.	7.5ST20/FilamentLED/DIM/A/20	Box	60	Warm White	Amber	2000	80	600	15000	13.6	\$0.90	5.31"
05133 ▲	5	Med.	5ST20/FilamentLED/DIM/A/20 1CD	Card	40	Warm White	Amber	2000	80	400	15000	13.6	\$0.60	5.39"

▲ Approved for use in totally enclosed fixtures

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh



Add a touch of nostalgia with LED filament lamps, designed to look just like traditional incandescent lamps. Filament LEDs light up instantly and are compatible with most dimmers, making them an ideal choice for use in pendant fixtures, table and floor lamps, vanity fixtures, ceiling fixtures and ceiling fans.

See the Westinghouse Lighting Catalog for more retro style light fixtures and pendants.

NEW!

Visit www.westinghouselighting.com for our latest energy-saving LED products and dimmer compatibilities.

GENERAL PURPOSE SPECIALTY LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
C7														
05108	0.6	Cand.	0.6C7/LED/F/CB/27 2CD	Card (2)	4	Warm White	Frost	2700	80	20	12000	10.9	\$0.07	2.05"
05110	0.6	Cand.	0.6C7/LED/CL/CB/27 2CD	Card (2)	4	Warm White	Clear	2700	80	20	12000	10.9	\$0.07	2.05"
05109	1	Cand.	1C7/LED/F/CB/27 2CD	Card (2)	7	Warm White	Frost	2700	80	50	12000	10.9	\$0.12	2.05"
05111	1	Cand.	1C7/LED/CL/CB/27 2CD	Card (2)	7	Warm White	Clear	2700	80	50	12000	10.9	\$0.12	2.05"
S6														
05117	0.6	Cand.	0.6S6/LED/CL/CB/27 1CD	Card	6	Warm White	Clear	2700	80	32	12000	10.9	\$0.07	1.77"
S11														
05113	1	Med.	1S11/LED/CL/27 1CD	Card	7.5	Warm White	Clear	2700	80	50	12000	10.9	\$0.12	1.99"
05112	1	Med.	1S11/LED/W/27 1CD	Card	7.5	Warm White	White	2700	80	40	12000	10.9	\$0.12	1.99"
05114	1.5	Inter.	1.5S11/LED/CL/IN/27 1CD	Card	10	Warm White	Clear	2700	80	80	12000	10.9	\$0.18	2.09"
S14														
05115	1	Med.	1S14/LED/F/27 1CD	Card	11	Warm White	Frost	2700	80	60	12000	10.9	\$0.12	3.23"
05116	1	Med.	1S14/LED/CL/27 1CD	Card	11	Warm White	Clear	2700	80	65	12000	10.9	\$0.12	3.23"
T7														
05118	1	Cand.	1T7/LED/CL/CB/27 1CD	Card	10	Warm White	Clear	2700	80	50	12000	10.9	\$0.12	2.09"
05119	1.5	Inter.	1.5T7/LED/CL/IN/27 1CD	Card	15	Warm White	Clear	2700	80	80	12000	10.9	\$0.18	2.09"
05120	1.5	D.C. Bay.	1.5T7/LED/CL/DC/27 1CD	Card	15	Warm White	Clear	2700	80	80	12000	10.9	\$0.18	2.09"
03199 ▲	8	Med.	8T7/LED/F/30 1CD	Card	60	Warm White	Frost	3000	80	800	12000	10.9	\$0.96	4.22"
05161 ▲	8	Med.	8T7/LED/DIM/F/30 1CD	Card	60	Warm White	Frost	3000	80	800	25000	22.8	\$0.96	4.22"
UTILITY														
03197 ▲	15	Med.	15DLR46E26/LED/F/27	Box	75	Warm White	Frost	2700	80	1200	25000	22.8	\$1.81	4.41"
03198 ▲	20	Med.	20DLR64E26/LED/F/27	Box	100	Warm White	Frost	2700	80	1800	25000	22.8	\$2.41	6.06"

▲ Approved for use in totally enclosed fixtures.

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh

HALOGEN ALTERNATIVE SPECIALTY LAMPS




Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Volt	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
JC															
03184 ▲	1.3	G4	1.3G4/LED/F/30 1CD	12	Card	10	Warm White	Frost	3000	80	100	25000	22.8	\$0.16	1.46"
JCD															
03185 ▲	2.5	G9	2.5G9/LED/F/30 1CD	120	Card	25	Warm White	Frost	3000	80	220	25000	22.8	\$0.30	2.05"
DOUBLE-ENDED SHORT															
03186 ▲	5	RSC	5R7S/LED/CL/27 1CD	120	Card	40	Warm White	Clear	2700	80	450	25000	22.8	\$0.60	3.07"
DOUBLE-ENDED LONG															
03187 ▲	9	RSC	9R7S/LED/CL/27 1CD	120	Card	75	Warm White	Clear	2700	80	900	25000	22.8	\$1.08	4.65"
03188 ▲	25	RSC	25R7S/LED/CL/27	120	Box	150	Warm White	Clear	2700	80	2500	25000	22.8	\$3.01	4.65"

▲ Approved for use in totally enclosed fixtures.

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh



LINEAR LAMPS

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Lamp Type Replacement	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	MOL
T5 (DesignLights Consortium® qualified product)												
03788 †▲■	22	Mini BiPin	LED 22T5/46"/40 Direct Install	Sleeve	T5	Cool White	Frost	4000	82	2800	50000	45.8"
03789 †▲■	22	Mini BiPin	LED 22T5/46"/50 Direct Install	Sleeve	T5	Daylight	Frost	5000	82	2800	50000	45.8"
T8 (DesignLights Consortium® qualified product)												
03739 †▲	14	Med. BiPin	LED 14T8/48"/40 Direct Install	Sleeve	T8	Cool White	Frost	4000	82	1800	50000	47.78"
33652 †▲	17	Med. BiPin	LED 17T8/48"/35 Direct Install	Sleeve	T8	Cool White	Frost	3500	82	2200	50000	47.78"
33653 †▲	17	Med. BiPin	LED 17T8/48"/40 Direct Install	Sleeve	T8	Cool White	Frost	4000	82	2200	50000	47.78"
33655 †▲	17	Med. BiPin	LED 17T8/48"/50 Direct Install	Sleeve	T8	Daylight	Frost	5000	82	2200	50000	47.78"
33660 †▲	18	Med. BiPin	LED 18T8/48"/35 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	3500	82	2200	50000	47.78"
33672 †▲	18	Med. BiPin	LED 18T8/48"/40 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	4000	82	2200	50000	47.78"
33676 †▲	18	Med. BiPin	LED 18T8/48"/50 Ballast Bypass	Sleeve	T8 & T12	Daylight	Frost	5000	82	2200	50000	47.78"

- Replace any 4 foot T8 or T12 linear fluorescent with a medium bipin base. Direct Install lamps replacing T12 lamps require a ballast change.
- † Dimmable when used with applicable ballast. See individual product specification sheets for dimmer compatibility on www.westinghouselighting.com.
- ▲ Approved for use in totally enclosed fixtures.
- Replace F54T5HO linear fluorescent lamps.



RECESSED DOWNLIGHTS

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL	MOD
STEP BAFFLE															
41047 ◊	10	Med.	10R/4"/LED/DIM/FL/30	Retail Box	65	Warm White	Frost	3000	80	650	35000	31.9	\$1.20	3.43"	5.35"
41048 ◊	10	Med.	10R/5-6"/LED/DIM/FL/30	Retail Box	65	Warm White	Frost	3000	80	750	35000	31.9	\$1.20	4.61"	7.48"
SMOOTH BAFFLE															
31043 †◊	8	Med.	8R/4"/LED/DIM/FL/27	Contractor Box	65	Warm White	Frost	2700	80	650	50000	45.6	\$0.96	3.50"	5.04"
31041 †◊	8	Med.	8R/4"/LED/DIM/FL/30	Contractor Box	65	Warm White	Frost	3000	80	650	50000	45.6	\$0.96	3.50"	5.04"
31040 †◊	14	Med.	14R/5"/LED/DIM/FL/27	Contractor Box	80	Warm White	Frost	2700	80	1000	50000	45.6	\$1.69	3.54"	6.30"
31044 †◊	14	Med.	14R/5"/LED/DIM/FL/30	Contractor Box	80	Warm White	Frost	3000	80	1000	50000	45.6	\$1.69	3.54"	6.30"
31045 †◊	14	Med.	14R/6"/LED/DIM/FL/27	Contractor Box	80	Warm White	Frost	2700	80	1000	50000	45.6	\$1.69	3.40"	7.24"
31046 †◊	14	Med.	14R/6"/LED/DIM/FL/30	Contractor Box	80	Warm White	Frost	3000	80	1000	50000	45.6	\$1.69	3.40"	7.24"

+ Optional accessory GU24 base adapter sold separately (Item # 22000)

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh

◊ UL Listed Only

See individual product specification sheets for dimmer compatibility on www.westinghouselighting.com.

NEW!

Visit www.westinghouselighting.com for our latest energy-saving LED products and dimmer compatibilities.

LEDs for every lighting application!

Recessed LED Downlights

Easily replace standard recessed housings with more efficient LED downlights. Convenient one-piece kits are the perfect replacements when remodeling residential or commercial applications.



Recessed Lighting

Perfect for providing overhead lighting in residential or commercial applications. Available in a range of beam spreads.



Track Lighting

Ideal for highlighting architectural spaces. Provides ambient and directional lighting utilizing a range of beam spreads for both residential and commercial applications.




Pendant Fixtures

Perfect for balancing function and design, as well as creating a personalized style in the home or workplace.



Retro Fixtures

Amber-tinted filament LEDs are perfect for creating a vintage look in popular retro-style fixtures with an exposed lamp.



Decorative Fixtures

Use in both residential and commercial applications where ambience is desired. Provide ample downward illumination for dining rooms, bedrooms, and home entertainment areas.



Ceiling Fans

Ideal for use in ceiling fans in both residential and commercial applications. Provide ample downward illumination for added ambience in dining rooms, bedrooms, and home entertainment areas.



Vanity Fixtures

Perfect in bathrooms and powder rooms where task lighting is important.



Night Lights

Essential for avoiding obstacles in the dark as well as providing a sense of security at night.



Table and Floor Lamps

Fulfills general purpose lighting needs, especially in areas where various levels of brightness are required for reading or relaxing.



Specialty General Purpose

Ideal for various applications, such as utility, general purpose, accent, automotive and landscape lighting.



Specialty Halogen Alternative

Ideal for under cabinet accent lighting and outdoor security lighting in commercial and residential applications.



Outdoor Lighting

Perfect for transforming outdoor areas into inviting spaces, as well as illuminating areas to ensure safety.



Specialty Color Lighting

Perfect for commercial or residential outdoor accent lighting. Ideal for holiday lighting, parties and special events. Weatherproof for indoor and outdoor use.



Office & Work Area Lighting

Ideal for both residential and commercial applications. Easily replace any 4 foot linear fluorescent lamp with energy-saving LED alternatives. Dimmable options available.




Visit www.westinghouselighting.com for our complete assortment of LED lamps, light fixtures, ceiling fans and accessories.

Packaging

Westinghouse LED lamp packaging is attractive and informative, providing all the facts you need to make the right lighting choice.

BOXED



Incandescent Equivalent Wattage

Energy Used (Watts)

ENERGY STAR[®] (where Applicable)

Kelvin Temperature Scale

Kelvin Temperature Appearance

Suggested Applications

Caution & Warranty

Brightness (Lumens)

Estimated Yearly Energy Cost

Product Features

CARDED



Incandescent Equivalent Wattage

Energy Used (Watts)

ENERGY STAR[®] (where Applicable)

Brightness (Lumens)

Estimated Yearly Energy Cost

Kelvin Temperature Scale

Kelvin Temperature Appearance

Suggested Applications

Lighting Facts Label

ENERGY STAR[®] (where Applicable)

Caution

Certifications

Warranty

Lamp Base (shown in actual size)



Call 1-800-999-2226 or visit www.westinghouselighting.com.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

Contact your Westinghouse Sales Representative for more information.