

Designed for an array of interior applications, **SkyTrim™** is a luminous decorative accent that can be mounted directly on the light guide of a SkyRidge™ fixture. A co-extruded high-grade optical acrylic strip, less than 0.5" deep, the SkyTrim provides a simple means of applying color to an existing or new fixture. It is ideal for spaces where color is necessary to provide visual cues, emphasize brand identity, directional awareness or simply as an artistic expression. The result is a unique and easy accessory for addressing a wealth of application needs with seven color choices and hundreds more with custom color options.

Features and Benefits

- Flexible use of color for identification, awareness or artistic purpose in space
- Seven standard color choices with custom color options
 - Tahitian Blue
 - Primary Green
 - Storaro Orange
 - Pearl
 - Belladonna Rose
 - Medium Red
 - Straw
- Offered in both 2' and 4' lengths
- Factory or field installable
- Simple installation; no hardware or tools required
- High-grade optical acrylic
- Minimal 0.45" depth

Suggested Applications

- Healthcare: wayfinding, paths of egress
- Education: school colors, space identification, pathways
- Sport Venues: team colors, zone/activity identification
- Retail: highlight merchandise, traffic influencer, customer checkout/service area identification
- Corporate Facilities: department identifiers, campus coding, branding, awareness
- Hospitality / Event: color coordination by activity, customer colors or holidays

Ordering Information (with fixture)

Sample Number: 22SR-LD1-29-C-UNV-L835-CD1-TB-U

Rating	Series ¹¹	Air	Lamp Type	LED Lumens Output				Reflector
[Blank]=Standard ATW-SW4=Chicago Rated ¹⁰	22SR=2' x 2' SkyRidge 24SR=2' x 4' SkyRidge 14SR=1' x 4' SkyRidge 12SR=1' x 2' SkyRidge	[Blank]=Standard A=Air Vented ^{9,16}	LD1=LED 1.0	2' x 2' Stock 20=2000 Lumens 29=2900 Lumens MTO ³ 25=2500 Lumens	2' x 4' Stock 39=3900 Lumens 48=4800 Lumens MTO ³ 29=2900 Lumens ² 34=3400 Lumens 45=4500 Lumens 53=5300 Lumens 59=5900 Lumens 64=6400 Lumens	1' x 4' MTO ³ 15=1500 Lumens 20=2000 Lumens 25=2500 Lumens 30=3000 Lumens 35=3500 Lumens 41=4100 Lumens 45=4500 Lumens	1' x 2' MTO ³ 9=900 Lumens 12=1200 Lumens 16=1600 Lumens 20=2000 Lumens	C=Curved (Standard) S=Straight
Optics	Voltage ⁴	Options		CCT	Options	Driver Type ⁷		
[Blank]=Standard	347V=347 Volt UNV=Universal Voltage 120-277	Emergency EL=Emergency Installed, 700 Lumens ^{1,5} EL14=Emergency Installed, 1400 Lumens ^{1,5} EL10W=Emergency Installed, 10 Watts ^{5,12}		CCT L830=3000K L835=3500K L840=4000K L850=5000K	Flex⁶ Flex=Multiple Configurations Available	CD=0-10V Dimming Driver (Standard) SD=Step-Dim Driver ^{8,13} 5LTD=Fifth Light (DALI) Driver		
Number of Drivers	SkyTrim ¹⁴	Packaging		Accessories				
1=1 Driver	TB=Tahitian Blue PG=Primary Green SO=Storaro Orange PL=Pearl	BR=Belladonna Rose MR=Medium Red ST=Straw CC=Custom ¹⁵	U=Unit Pack PALC=Job Pack, in Carton	(Order Separately) T3A END E.Q. BRACKET PARTS BAG=(Standard with Fixture) DF-22-W=2' x 2' Drywall Frame Kit DF-24-W=2' x 4' Drywall Frame Kit SK-22-WT=2' x 2' Surface Mount Kit, Tall SK-24-WT=2' x 4' Surface Mount Kit, Tall				

NOTES: 1. Must specify voltage (120V or 277V) when selecting EL option. 2. 2900 lumen option is not available with Step-Dim or Fifth Light (DALI) driver. 3. Made-to-order (MTO) requires four week lead time. 4. Products also available in non-US voltage and frequencies for international markets. 5. Test switch and indicator are remote mounted. 6. Flex does not include dimming leads. Control leads provided by others. 7. Call factory for step-dimming options. 8. 5300, 5900 and 6400 lumen packages are not available with Step-Dim driver. For a complete listing of Fifth Light Technology products and other solutions from Cooper Controls, visit www.coopercontrol.com. 9. Air version is vented but does not meet air handling requirements. 10. Chicago rated version does not allow for row mounting. 11. DesignLights Consortium@ Qualified (all lumen packages except 5300, 5900 and 6400). Refer to www.designlights.org Qualified Products List under Family Models for details. 12. For delivered lumens, take lumens per watt of desired fixture and multiply by 10 watts (100 lp/W x 10 = 1000 lumens delivered). 13. 2' x 2' not offered with Step-dim driver. 14. Fixtures using factory installed SkyTrim option do not meet DLC qualifications. 15. Custom colors must list Roscolux numeric color specification code. 16. Air vented version not available with 1' x 2' and 1' x 4'.

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.

Field Installed Ordering Information

Color Choice	2' Kit Catalog Number	4' Kit Catalog Number	Kit Quantity
Tahitian Blue	STK-2-TB-10PK	STK-4-TB-10PK	10
Primary Green	STK-2-PG-10PK	STK-4-PG-10PK	10
Storaro Orange	STK-2-SO-10PK	STK-4-SO-10PK	10
Pearl	STK-2-PL-10PK	STK-4-PL-10PK	10
Belladonna Rose	STK-2-BR-10PK	STK-4-BR-10PK	10
Medium Red	STK-2-MR-10PK	STK-4-MR-10PK	10
Straw	STK-2-ST-10PK	STK-4-ST-10PK	10
Custom Color	STK-2-CC-*-10PK	STK-4-CC-*-10PK	10

* Custom color requires Roscolux numeric specification color code.

NOTE: Chosen color will be matched on acrylic but will appear lighter once applied to lit light guide.

Custom Color Specification

Add Custom Color number to order code

CC


Color Reference

CC = Custom

Roscolux

Numeric Color Specification

Up to a four-digit number – must be obtained from Rosco.





Eaton's Cooper Lighting Business

Headquarters
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales

5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

Our Lighting Product Brands

Halo
Halo Commercial
Portfolio
IRiS
RSA
Metalux
Corelite
Neo-Ray
Fail-Safe
MWS
Ametrix
Shaper
io
Lumark
McGraw-Edison
Invue
Lumière
Streetworks
AtLite
Sure-Lites

Our Controls Product Brands

Greengate
iLumin
Zero 88
Fifth Light Technology
iLight (International Only)