



*** 22264**
Receptacle
 Candelabra Base
 75 Watts Max., 125 Volts
 Height - 7/8"




*** 22273**
One-Piece Receptacle
 Medium Base
 600 Watts Max., 250 Volts
 Height - 1 1/2"
 180° C Maximum Temp.



*** 22150**
70364
Socket Extender
 Medium Base
 660 Watts Max., 250 Volts
 Extension - 1/4"
 Overall Length - 2 1/4"



*** 22218**
Keyless Socket
1 Screw Surface Mount
 Medium Base
 7" Wire Leads
 660 Watts Max., 250 Volts
 105° Leads
 Leads Height - 1 5/8"



*** 22372**
Socket
 Medium Base
 9" Wire Leads
 Fits 3/8" x 1/4" Hole
 18 Gauge, 105° Leads
 660 Watts Max., 250 Volts
 Height - 2"



*** 22276**
Snap-In
Porcelain Socket
 660 Watts Max., 250 Volts
 Height - 1 3/4"



*** 22739**
Phenolic Adapter
Ivory Socket
 Medium Base
 Polarized 660 Watts Max.
 15A, 125 Volts



*** 22281**
Mogul Base Socket
 3-Way
 Removable Knob
 Bushing 1/4-IP
 750 Watts Max., 250 Volts
 Height - 4 1/4"



*** 22282**
Mogul Base Socket
 1500 Watts Max., 600 Volts
 Height - 2 5/8"
 4KV Pulse Rating



*** 22266**
70423
Two-Piece
Sign Receptacle
 Medium Base
 660 Watts Max., 250 Volts
 Height - 1 1/2"
 300° C Maximum Temp.

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com