

Pass & Seymour




Switches

Grounding Combination Switches


15 & 20A, 120/277VAC; 15A, 120/125VAC; 20A, 120VAC

Features

- Available in ten switch, receptacle and pilot light combinations.
- Easily accessible break-off for separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.



Standard Combination



Decorator Combination

NEMA
5-15RNEMA
5-20R

All devices listed on this page conform to NEMA WD-1 and WD-6.

| Catalog Number | Rating A. VAC | Color | NEMA Config. No. | 3rd Party Compliance | |
|--|------------------|--------------|---------------------|----------------------|-------|
| | | | | UL20 | UL498 |
| Standard: | | | | | |
| Two Single Pole Switches Side Wire, Grounding | | | | | |
| 690-IG | 15 120/277 | Ivory | | | • |
| 690-WG | 15 120/277 | White | | | • |
| 690-G | 15 120/277 | Brown | | | • |
| 690-LAG | 15 120/277 | Light Almond | | | • |
| 670-IG | 20 120/277 | Ivory | | | • |
| 670-WG | 20 120/277 | White | | | • |
| 670-G | 20 120/277 | Brown | | | • |
| 670-LAG | 20 120/277 | Light Almond | | | • |
| Single Pole & Three-Way Switch Side Wire, Grounding | | | | | |
| 696-IG | 15 120/277 | Ivory | | | • |
| 696-WG | 15 120/277 | White | | | • |
| 696-G | 15 120/277 | Brown | | | • |
| 696-LAG | 15 120/277 | Light Almond | | | • |
| Two Three-Way Switches Side Wire, Grounding | | | | | |
| 693-IG | 15 120/277 | Ivory | | | • |
| 693-WG | 15 120/277 | White | | | • |
| 693-G | 15 120/277 | Brown | | | • |
| 693-LAG | 15 120/277 | Light Almond | | | • |
| Single Pole Switch & Single Receptacle Side Wire, Grounding | | | | | |
| 691-I | 15 120/125 | Ivory | 5-15R | | • • |
| 691-W | 15 120/125 | White | 5-15R | | • • |
| 691 | 15 120/125 | Brown | 5-15R | | • • |
| 691-LA | 15 120/125 | Light Almond | 5-15R | | • • |
| 671-I | 20 120 | Ivory | 5-20R | | • • |
| 671-W | 20 120 | White | 5-20R | | • • |
| 671 | 20 120 | Brown | 5-20R | | • • |
| 671-LA | 20 120 | Light Almond | 5-20R | | • • |
| Single Pole Switch & Pilot Light Side Wire, Grounding | | | | | |
| 692-IG | 15 120/125 | Ivory | | | • |
| 692-WG | 15 120/125 | White | | | • |
| 692-G | 15 120/125 | Brown | | | • |
| 692-LAG | 15 120/125 | Light Almond | | | • |
| Three-Way Switch & Pilot Light Side Wire, Grounding | | | | | |
| 695-IG | 15 120/125 | Ivory | | | • |
| 695-WG | 15 120/125 | White | | | • |
| 695-G | 15 120/125 | Brown | | | • |
| 695-LAG | 15 120/125 | Light Almond | | | • |
| Decorator: | | | | | |
| Two Single Pole Switches Side Wire, Grounding | | | | | |
| 680-IG | 15 120/277 | Ivory | | | • |
| 680-WG | 15 120/277 | White | | | • |
| 680-LAG | 15 120/277 | Light Almond | | | • |
| Single Pole Switch & Single Receptacle Side Wire, Grounding | | | | | |
| 681-I | 15 120/125 | Ivory | 5-15R | | • • |
| 681-W | 15 120/125 | White | 5-15R | | • • |
| 681-LA | 15 120/125 | Light Almond | 5-15R | | • • |