

WIRE MANAGEMENT

Thin-Wall Tubing

Easy-Splice™

TWHS Series Cnt'd



SPECIFICATIONS

- UL Recognize.
- Temperature Rating: 125 °C. 600V Max.
- Black, White and colored thin-wall tubing meet MIL-DTL-23053/5, Class 1.
- Clear meets MIL-DTL-23053/5, Class 2 and is not flame retardant.

FEATURES

- Flexible flame-retardant, thin wall, general purpose heat-shrinkable polyolefin tubing has a 2:1 shrink ratio.
- Used for electrical insulation, wire harness bundling, wire jacket marking and color coding, it also splices and makes functional terminations.
- Standard packaging is either 6" lengths in blister boxes, or in economical 25' spools.

| CAT.NO. | EXPANDED I.D. | RECOVERED I.D. | NOMIINAL RECOVERED WALL THICKNESS | LENGTH (IN/FT) | STD. CTN. QTY. |
|---------------|---------------|----------------|-----------------------------------|----------------|----------------|
| TWHS-312-6 | 0.312 | 0.156 | 0.025 | 6" | 10 |
| TWHS-312-48 | 0.312 | 0.156 | 0.025 | 48" | 1 |
| TWHS-312 | 0.312 | 0.156 | 0.025 | 200' Spool | 1 |
| TWHS-375-6 | 0.375 | 0.187 | 0.025 | 6" | 9 |
| TWHS-375-48 | 0.375 | 0.187 | 0.025 | 48" | 1 |
| TWHS-375-25B | 0.375 | 0.187 | 0.025 | 25' Spool | 1 |
| TWHS-375 | 0.375 | 0.187 | 0.025 | 200' Spool | 1 |
| TWHS-500-6 | 0.500 | 0.250 | 0.025 | 6" | 8 |
| TWHS-500-48 | 0.500 | 0.250 | 0.025 | 48" | 1 |
| TWHS-500-25B | 0.500 | 0.250 | 0.025 | 25' Spool | 1 |
| TWHS-500 | 0.500 | 0.250 | 0.025 | 200' Spool | 1 |
| TWHS-750-6 | 0.750 | 0.375 | 0.030 | 6' | 6 |
| TWHS-750-48 | 0.750 | 0.375 | 0.030 | 48' | 1 |
| TWHS-750-25B | 0.750 | 0.375 | 0.030 | 25' Spool | 1 |
| TWHS-750-25W | 0.750 | 0.375 | 0.030 | 25' Spool | 1 |
| TWHS-750 | 0.750 | 0.375 | 0.030 | 100' Spool | 1 |
| TWHS-1000-6 | 1.000 | 0.500 | 0.035 | 6" | 4 |
| TWHS-1000-48 | 1.000 | 0.500 | 0.035 | 48" | 1 |
| TWHS-1000-25B | 1.000 | 0.500 | 0.035 | 25' Spool | 1 |
| TWHS-1000 | 1.000 | 0.500 | 0.035 | 100' Spool | 1 |
| TWHS-1500-48 | 1.500 | 0.750 | 0.040 | 48" | 1 |
| TWHS-1500-25B | 1.500 | 0.750 | 0.040 | 25' Spool | 1 |
| TWHS-2000-48 | 2.000 | 1.000 | 0.045 | 48" | 1 |
| TWHS-2000-25B | 2.000 | 1.000 | 0.045 | 25' Spool | 1 |