

MINITERMS
Butt Splices
B SERIES

FEATURES

VINYL:

Stripped wires are inserted from each end and "butt" in the center. A crimp at each end secures the connection.

Electro tin plated copper, vinyl (PVC) 300V, 75 °C.

UN-INSULATED:

Stripped wires are inserted from each end and "butt" in the center. A crimp at each end secures the connection.

Electro tin plated copper, 600V, 105 °C.

POLYOLEFIN HS:



Stripped wires are inserted from each end and "butt" in the center. A crimp at each end secures the connection.

Electro tin plated copper, Heat shrink, 600V, 105 °C, Shrink temp 150 °C.

NYLON:

Stripped wires are inserted from each end and "butt" in the center. A crimp at each end secures the connection.

Electro tin plated copper, Nylon, 600V, 105 °C.



INSULATION TYPE	WIRE RANGE	CERTIFICATION VARIANCE
Vinyl	22-18	
Vinyl	16-14	
Vinyl	12-10	
Vinyl	8	UL
Vinyl	6	UL
Un-insulated - Bare	22-18	
Un-insulated - Bare	16-14	
Un-insulated - Bare	12-10	UL
Un-insulated - Bare	8	
Polyolefin HS	22-18	
Polyolefin HS	16-14	
Polyolefin HS	12-10	
Nylon	22-18	
Nylon	16-14	
Nylon	12-10	



LENGTH (IN)	"S" PACKS		PRO PACKS		STD PACKS		BULK PACKS	
	CAT. NO.	QTY	CAT. NO.	QTY	CAT. NO.	QTY	CAT. NO.	QTY
1.024	B22-V-S	25	B22-V-P	70	B22-V	100	B22-V-BULK	1000
1.024	B16-V-S	20	B16-V-P	50	B16-V	100	B16-V-BULK	1000
1.024	B12-V-S	15	B12-V-P	30	B12-V	50	B12-V-BULK	500
1.398	–	–	B8-V-P	10	B8-V	50	B8-V-BULK	250
1.855	–	–	–	–	B6-V	50	B6-V-BULK	100
0.472	–	–	–	–	B22	100	B22-BULK	1000
0.591	–	–	–	–	B16	100	B16-BULK	1000
0.591	–	–	–	–	B12	50	B12-BULK	1000
0.827	–	–	–	–	B8	50	B8-BULK	1000
0.945	–	–	–	–	SB22	25	SB22-BULK	500
1.457	–	–	–	–	SB16	25	SB16-BULK	500
1.614	–	–	–	–	SB12	50	SB12-BULK	500
1.024	–	–	–	–	B22-N	100	B22-N-BULK	1000
1.024	–	–	–	–	B16-N	100	B16-N-BULK	1000
1.063	–	–	–	–	B12-N	50	B12-N-BULK	500