




HBL1221ILC




HBL1221PL



HBL1209



HBL1381



HBL1386I

Dimensions in Inches (mm)

HBL® Extra Heavy Duty Industrial Series, Illuminated Toggle Switches, Light ON with Load OFF

| Description | Toggle Color | Rating | Single Pole | Double Pole | Three Way |
|------------------------------------|--------------|-----------------|-------------------|-------------|-------------------|
| Nylon toggle, back and side wired. | Ivory | 15A 120/277V AC | HBL1201IL | — | HBL1203IL |
| | Ivory | 20A 120/277V AC | HBL1221IL | — | HBL1223IL |
| | Clear | | HBL1221ILC | — | HBL1223ILC |
| | Red | | HBL1221ILR | — | — |

HBL® Extra Heavy Duty Industrial Series, Pilot Light Switches, Light ON with Load ON

| Description | Toggle Color | Rating | Single Pole | Double Pole | Three Way |
|------------------------------------|--------------|-----------------|-------------------|------------------|-------------------|
| Nylon toggle, back and side wired. | Red | 15A 120/277V AC | HBL1201PL | — | HBL1203PL |
| | Red | 20A 120/277V AC | HBL1221PL | HBL1222PL | HBL1223PL |
| | Clear | | HBL1221PLC | — | HBL1223PLC |
| | Green | | HBL1221PLG | — | — |
| | Red | 30A 120/277V AC | HBL3031PL | HBL3032PL | — |

HBL® Extra Heavy Duty Industrial Series, Momentary Contact, Specification Grade, Three Position, Two Circuit, Center OFF

| Description | Toggle Color | 15A, 120/277V AC | 20A, 120/277V AC |
|------------------------------------|--------------|------------------|------------------|
| Nylon toggle, back and side wired. | Brown | HBL1556 | HBL1557 |
| | Gray | HBL1556GY | HBL1557GY |
| | Ivory | HBL1556I | HBL1557I |
| | Red | HBL1556R | — |
| | White | HBL1556W | HBL1557W |
| Key guide, back and side wired. | Black | HBL1556L | HBL1557L |
| | Gray | HBL1556LG | HBL1557LG |
| | Ivory | HBL1556LI | HBL1557LI |
| | White | HBL1556LW | HBL1557LW |
| Key for Locking switch. | | HBL1209 | |

HBL® Extra Heavy Duty Industrial Series, Maintained Contact, Specification Grade, Three Position, Two Circuit, Center OFF, Single Pole, Double Throw

| Description | Toggle Color | 15A 120/277V AC | 20A 120/277V AC | 30A 120/277V AC |
|------------------------------------|--------------|-----------------|-----------------|-----------------|
| Nylon toggle, back and side wired. | Brown | HBL1381 | HBL1385 | — |
| | Ivory | HBL1381I | HBL1385I | — |
| | White | — | HBL1385W | — |

Three Position, Two Circuit, Center OFF, Double Pole, Double Throw

| Description | Toggle Color | 15A 120/277V AC | 20A 120/277V AC | 30A 120/277V AC |
|------------------------------------|--------------|-----------------|-----------------|-----------------|
| Nylon toggle, back and side wired. | Brown | HBL1382 | HBL1386 | HBL1388 |
| | Ivory | HBL1382I | HBL1386I | HBL1388I |
| Locking. | | — | HBL1386L | — |
| Key for Locking switch. | | — | HBL1209 | — |

Note: Keys are supplied with each locking switch. For extra keys order HBL1209. See page D-15 for accessories and page D-16 for wallplates. See page D-22 for technical information.

HP Conversion Chart

| | 120V | 208V | 240V | 277V AC |
|-----|------|-------|------|---------|
| 15A | .5HP | 1.5HP | 2HP | 2HP |
| 20A | 1HP | 2HP | 2HP | 2HP |
| 30A | 2HP | 2HP | 2HP | 2HP |