

Features



Contactors



- Furnas style definite purpose contactors
- UL recognized
- Heavy duty silver contacts

Contactors

Catalog Number	IRP Product Number	Full Load Amps	Resistive Amps @ 600 V	Locked Rotor Amps @			Coil Voltage	Poles	Furnas/Siemens	Cutler Hammer/Eaton	Standard Pkg. Qty.	Item Wghts (lbs)
				240/277 V	480 V	600 V						
DP130120F	195-0030	30	40	180	150	120	120	1	45EG10AFA	C25CNB130A	50	0.507
DP130240F	195-0031	30	40	180	150	120	240	1	45EG10AGA	C25CNB130B	50	0.507
DP13024F	195-0032	30	40	180	150	120	24	1	45EG10AJA	C25CNB130	50	0.507
DP220120F	195-0033	20	30	120	100	80	120	2	45CG20AF	C25BNB220A	50	0.545
DP220240F	195-0034	20	30	120	100	80	240	2	45CG20AG	C25BNB220B	50	0.545
DP22024F	195-0035	20	30	120	100	80	24	2	45CG20AJ	C25BNB220T	50	0.545
DP225120F	195-0036	25	35	150	120	100	120	2	45DG20AF	C25BNB225A	50	0.545
DP230120F	195-0039	30	40	180	150	120	120	2	45EG20AF	C25BNB230A	50	0.545
DP230240F	195-0040	30	40	180	150	120	240	2	45EG20AG	C25BNB230B	50	0.545
DP23024F	195-0041	30	40	180	150	120	24	2	45EG20AJ	C25BNB230T	50	0.545
DP230277F	195-0042	30	40	180	150	120	277	2	45EG20AL	-	50	0.545
DP240120F	195-0043	40	50	240	200	160	120	2	45GG20AF	C25BNB240A	50	0.578
DP240240F	195-0044	40	50	240	200	160	240	2	45GG20AG	C25BNB240B	50	0.578
DP24024F	195-0045	40	50	240	200	160	24	2	45GG20AJ	C25BNB240T	50	0.578
DP330120F	195-0052	30	40	180	150	120	120	3	42BE35AFBBT	C25ENF440A	25	1.091
DP330240F	195-0053	30	40	180	150	120	240	3	42BF35AG(BBU)	C25DND330B	25	1.091
DP33024F	195-0054	30	40	180	150	120	24	3	42BF35AG(BBU)	C25DND330T	25	1.091
DP340120F	195-0055	40	50	240	200	160	120	3	42CF35AF(BBC)	C25DNF340A	25	1.091
DP340240F	195-0056	40	50	240	200	160	240	3	42CF35AG(BCD)	C25DNF340B	25	1.091
DP34024F	195-0057	40	50	240	200	160	24	3	42CF35AJ(BCE)	C25DNF340T	25	1.091
DP350120F	195-0058	50	65	300	250	200	120	3	42DF35AF(BCF)	C25DNJ350A	24	1.323
DP350240F	195-0059	50	65	300	250	200	240	3	42DF35AG(BCG)	C25DNJ350B	24	1.323
DP35024F	195-0060	50	65	300	250	200	24	3	42DF35AJ(BCH)	C25DNJ350T	24	1.323
DP360120F	195-0061	60	75	360	300	240	120	3	42EF35AF(BCI)	C25FNF360A	24	1.323
DP360240F	195-0062	60	75	360	300	240	240	3	42EF35AG(BCJ)	C25FNF360B	24	1.323
DP36024F	195-0063	60	75	360	300	240	24	3	42EF35AJ(BCK)	C25FNF360T	24	1.323
DP375120F	195-0064	75	90	450	375	300	120	3	42FE35AF(106)	C25FNF375A	12	3.252
DP375240F	195-0065	75	90	450	375	300	240	3	42FE35AG(106)	C25FNF375B	12	3.252
DP37524F	195-0066	75	90	450	375	300	24	3	42FE35AJ(106)	C25FNF375T	12	3.252
DP390120F	195-0067	90	120	540	450	360	120	3	42GE35AF(106)	C25GNF390A	12	3.252
DP390240F	195-0068	90	120	540	450	360	240	3	42GE35AG(106)	C25GNF390B	12	3.252
DP39024F	195-0069	90	120	540	450	360	24	3	42GE35AJ(106)	C25GNF390T	12	3.252
DP430120F	195-0085	30	40	180	150	120	120	4	42BF25AF(BBQ)	C25END430A	25	1.235
DP430240F	195-0086	30	40	180	150	120	240	4	42BF25AG(BBR)	C25END430B	25	1.235
DP43024F	195-0087	30	40	180	150	120	24	4	42BF25AJ(BBS)	C25END430T	25	1.235
DP440120F	195-0088	40	50	240	200	160	120	4	42CF25AF(BBZ)	C25ENF440A	25	1.312
DP440240F	195-0089	40	50	240	200	160	240	4	42CF25AG(BCA)	C25ENF440B	25	1.312
DP44024F	195-0090	40	50	240	200	160	24	4	42CF25AJ(BCB)	C25ENF440T	25	1.312
DP34024SF	195-0241	40	50	240	200	160	24	3	42CF35AJ(BCE)	C25DNF340T	25	1.058
DP23024LF	195-0242	30	40	180	150	120	24	2	45EG20AJL	CB25BN230T	50	0.578
DP14024F	195-0251	40	50	240	200	160	24	1	45GG10AJA	C25CNB140T	50	0.507
DP130277F	195-0250	30	40	180	150	120	277	1	45EG10ALA	C25CNA140H	50	0.536
DP230480F	195-0252	30	40	180	150	120	480	2	45EG20AHL	C25DNA240C	50	0.578
DP330277F	195-0253	30	40	180	150	120	277	3	-	C25DNA340H	25	1.091
DP330480F	195-0254	30	40	180	150	120	480	3	-	C25DNC340C	25	1.091
DP340277F	195-0255	40	50	240	200	160	277	3	-	C25DNA350H	25	1.091
DP340480F	195-0256	40	50	240	200	160	480	3	-	C25DNA350C	25	1.091
DP360480F	195-0257	60	75	360	300	240	480	3	-	C25FNE375C	24	1.323
1950236	195-0236	50 - 60	F Series Coil Only Replacement				120	3	Catalog#	IRP Number	Description	
1950237	195-0237	75 - 90	F Series Coil Only Replacement				120	3	Auxiliary Switches for F Series			
1950238	195-0238	75 - 90	F Series Coil Only Replacement				480	3	1950243	195-0243	Auxiliary switch for all 3 and 4 pole contactors below 75 AMPS	
1950239	195-0239	75 - 90	F Series Coil Only Replacement				208/240	3	1950244	195-0244	Auxiliary switch for all 3 pole contactors 75 to 120 AMPS	
1950240	195-0240	50 - 60	F Series Coil Only Replacement				480	3				

These contactors are electrically compatible with the models listed in the chart above. Some physical characteristics may differ

Features

- UL recognized
- Heavy duty silver contacts

Contactors

While Supplies Last (*except where noted)



Contactors & Accessories

Catalog Number	IRP Product Number	Full Load Amps	Resistive Amps @ 600 V	Lock Rotor Amps @			Coil Voltage	Poles	Furnas Part #	Cutler Hammer #	Standard Pkg. Qty.	Item Weights (lbs)
				240/277 V	480 V	600 V						
DP130120	190-0030	30	40	150	125	100	120	1 w/shunt	45EG10AFA		50	0.5
DP130240	190-0031	30	40	150	125	100	240	1 w/shunt	45EG10AGA	C25CNB130B	50	0.5
DP13024	190-0032	30	40	150	125	100	24	1 w/shunt	45EG10AJA	C25CNB130T	50	0.5
DP220120	190-0033	20	30	120	100	80	120	2	45CG20AF	C25BNB220A	50	0.6
DP220240	190-0034	20	30	120	100	80	240	2	45CG20AG	C25BNB220B	50	0.6
DP22024	190-0035	20	30	120	100	80	24	2	45CG20AJ	C25BNB220T	50	0.6
DP225120	190-0036	25	35	150	125	100	120	2	45DG20AF	C25BNB225A	50	0.6
DP230120	190-0039	30	40	150	125	100	120	2	45EG20AF	C25BNB230A	50	0.6
DP230240	190-0040	30	40	150	125	100	240	2	45EG20AG	C25BNB230B	50	0.6
DP23024	190-0041	30	40	150	125	100	24	2	45EG20AJ	C25BNB230T	50	0.6
DP230277	190-0042	30	40	150	125	100	277	2	45EG20AL	C25BNB230H	50	0.6
DP240120	190-0043	40	50	200	160	120	120	2	45GG20AF	C25BNB240A	50	0.6
DP240240	190-0044	40	50	200	160	120/120	240	2	45GG20AG	C25BNB240B	50	0.6
DP24024	190-0045	40	50	200	160	160	24	2	45GG20AJ	C25BNB240T	50	0.6
DP2X4024	190-0047	40	50	240	200	160	24	2 in 3 base	42CF15AJ	C25DNT240T	50	1
DP330120	190-0052	30	40	180	150	120	120	3	42BF35AF	C25DNF330A	25	1
DP330240	190-0053	30	40	180	150	120	240	3	42BF35AG	C25DNF330B	25	1
DP33024	190-0054	30	40	180	150	120	24	3	42BF35AJ	C25DNF330T	25	1
DP340120	190-0055	40	50	240	200	160	120	3	42CF35AF	C25DNF340A	25	1
DP340240	190-0056	40	50	240	200	160	240	3	42CF35AG	C25DNF340B	25	1
DP34024	190-0057	40	50	240	200	160	24	3	42CF35AJ	C25DNF340T	25	1
DP350120	190-0058	50	65	300	250	200	120	3	42DF35AF	C25DNJ350A	25	2
DP350240	190-0059	50	65	300	250	200	240	3	42DF35AG	C25DNJ350B	25	2
DP35024	190-0060	50	65	300	250	200	24	3	42DF35AJ	C25DNJ350T	25	2
DP360120	190-0061	60	75	360	300	240	120	3	42EF35AF	C25FNF360A	25	2
DP360240	190-0062	60	75	360	300	240	240	3	42EF35AG	C25FNF360B	25	2
DP36024	190-0063	60	75	360	300	240	24	3	42EF35AJ	C25FNF360T	25	2
DP375120	190-0064	75	90	450	375	300	120	3	42FE35AF	C25FNF375A	8	4
DP375240	190-0065	75	90	450	375	300	240	3	42FE35AG	C25FNF375B	8	4
DP37524	190-0066	75	90	450	375	300	24	3	42FE35AJ	C25FNF375C	8	4
DP390120	190-0067	90	120	540	450	360	120	3	42GE35AF	C25GNF390A	8	4
DP390240	190-0068	90	120	540	450	360	240	3	42GE35AG	C25GNF390B	8	4
DP39024	190-0069	90	120	540	450	360	24	3	42GE35AJ		8	4
DP3120120*	190-0070	120	120	720	600	480	120	3	42HF35AF	C25HNE3120A	8	4
DP3120240*	190-0071	120	120	720	600	480	240	3	42HF35AG	C25HNE3120B	8	4
DP312024*	190-0072	120	120	720	600	480	24	3	42HF35AJ		8	4
DP430120	190-0085	30	40	180	150	120	120	4	42BF25AF	C25END430A	25	1.25
DP430240	190-0086	30	40	180	150	120	240	4	42BF25AG		25	1.25
DP43024	190-0087	30	40	180	150	120	24	4	42BF25AJ		25	1.25
DP440120	190-0088	40	50	240	200	160	120	4	42CF25AF	C25ENF440A	25	1.25
DP440240	190-0089	40	50	240	200	160	240	4	42CF25AG		25	1.25
DP44024	190-0090	40	50	240	200	160	24	4	42CF25AJ	C25ENF440T	25	1.25

Catalog#	IRP Number	Description	Fits Contactor Series	Catalog#	IRP Number	Description	Fits Contactor Series
Auxiliary Switches							
1900092	190-0092	1 NO 75-120 FLA	DP375, 390, 312	1900230	190-0230	1 NO & 1 NC 25-60 FLA	DP330,340,430,440,350,360
1900093	190-0093	1 NC 75-120 FLA	DP375, 390, 312	1900232	190-0232	SPDT 75-90 FLA	DP375, 390 HCC Series
1900094	190-0094	1 NC 25-60 FLA	DP330,340,430,440,350,360	1900233	190-0233		
1900095	190-0095	1 NO 25-60 FLA	DP330,340,430, 40,350,360	1900234	190-0234	SPDT 75-120 FLA	DP375, 390, 312 HCD Series
1900096	190-0096	SPDT 25-60 FLA	DP330,340,430,440,350,360	1900235	190-0235		
1900097	190-0097	(2) SPDT 25-60 FLA	DP330,340,430,440,350,360				