





## RB General Purpose Batteries

Part No.	Voltage (V)	Capacity (AH)	Length		Width		Height*		Total Height* (Incl. Terminal)		Weight		Standard Terminal
			in	mm	in	mm	in.	mm	in.	mm	lbs	kgs	
RB445	4	4.50	1.89	48	2.09	53	3.70	94	3.86	98	1.30	0.59	F2
RBX446	4	4.60	1.86	47	1.90	48	4.00	101	4.20	106	1.30	0.59	F1
RB490	4	9.00	4.01	102	1.73	44	3.74	95	4.02	102	2.20	1.00	F2
RB4100	4	10.00	4.01	102	1.97	50	3.70	94	3.85	98	2.50	1.13	F1
RB610	6	1.10	2.0	51	1.65	42	2.0	51	2.20	56	0.44	0.20	F1
RB612	6	1.40	3.82	97	0.94	24	2.0	51	2.20	56	0.66	0.30	F1
RB623	6	2.30	1.69	43	1.45	37	2.99	76	2.99	76	0.75	0.34	F1 Side
RB630S	6	3.20	4.92	102	1.34	34	2.35	60	2.56	65	1.37	0.62	F1
RB630	6	3.50	5.28	134	1.34	34	2.35	60	2.56	65	1.37	0.62	F1
RB632	6	3.50	2.60	66	1.30	33	4.65	118	4.80	122	1.65	0.83	F1
RB640	6	4.50	2.76	70	1.86	47	3.94	100	4.25	108	1.60	0.73	F1
RB650LS	6	5.00	2.64	67	2.64	67	3.94	100	4.64	118	1.80	0.82	SP
RB650LF	6	5.00	2.64	67	2.64	67	3.94	100	4.64	118	1.80	0.82	F1
RB667	6	6.50	3.86	98	2.20	56	3.78	96	4.02	102	2.70	1.22	FP
RB670	6	7.00	5.95	151	1.34	34	3.70	94	3.94	100	2.42	1.10	F1
RB682	6	9.00	3.86	98	2.20	56	4.65	118	4.72	120	3.20	1.45	F1
RB6100	6	10.00	5.95	151	2.0	51	3.70	94	3.86	98	4.30	1.95	F1 or F2
RB6121	6	12.00	5.95	151	2.0	51	3.70	94	3.86	98	4.30	1.95	F1 or F2
RB6120	6	13.00	4.25	108	2.80	71	5.55	141	5.55	141	4.80	2.18	FP
RB6140	6	14.00	4.25	108	2.80	71	5.55	141	5.55	141	4.80	2.18	FP
RBX6180	6	18.00	3.60	91	3.34	84	6.49	164	6.70	170	6.80	3.08	F2
RB6200	6	20.00	6.18	157	3.27	83	4.92	125	4.92	125	7.10	3.22	NB1
RBX6330	6	33.00	6.25	158	3.35	85	6.50	165	6.75	171	12.20	5.53	F2
RB6360	6	36.00	6.25	159	3.35	85	6.50	165	6.93	176	12.10	5.49	F2 or NB1
RBX6500	6	58.00	7.24	183	4.40	111	7.42	188	8.32	211	21.50	9.75	NB4
RB832	8	3.20	5.29	134	1.42	36	2.49	63	2.70	69	1.58	0.72	F1
RB1208	12	0.80	3.78	96	0.98	25	2.44	62	2.44	62	0.77	0.35	wire&plug
RB1212	12	1.40	3.78	96	1.69	43	2.04	52	2.28	58	1.20	0.54	F1
RB1220	12	2.50	7.00	178	1.38	35	2.36	60	2.56	65	2.10	0.95	F1
RB1223	12	2.30	7.17	182	0.94	24	2.40	61	2.40	61	1.50	0.68	PC
RB1227	12	2.90	3.11	79	2.20	56	3.90	99	4.13	105	2.40	1.09	F1
RB1228	12	2.80	5.24	133	1.30	33	3.82	97	4.09	104	2.60	1.18	F1
RB1229	12	2.90	7.0	178	1.38	35	2.36	60	2.60	66	2.30	1.04	F1
RB1230	12	3.40	5.24	133	2.64	67	2.36	60	2.60	66	2.90	1.32	F1
RB1252	12	5.00	3.54	90	2.76	70	3.98	101	4.21	107	3.50	1.59	F1 or F2
RB1255RT	12	6.00	5.50	140	1.90	48	4.00	102	4.06	103	4.06	1.84	Recess FP
RB1270	12	7.50	5.95	151	2.56	65	3.70	94	3.86	98	4.80	2.18	F1 or F2
RB1290	12	9.00	5.95	151	2.56	65	3.70	94	3.86	98	6.00	2.72	F2 or NB1
RB12100	12	10.00	5.94	151	2.56	65	4.40	112	4.67	118	7.23	3.28	F2
RB12120	12	12.00	5.95	151	3.86	98	3.70	94	3.94	100	7.92	3.59	F2 or NB
RB12150	12	15.00	5.94	151	3.86	98	3.70	94	3.94	100	9.37	4.25	F1 or F2
RB12180	12	18.00	7.13	181	3.00	76	6.59	167	6.59	167	12.60	5.72	F2 or NB2
RBX12250	12	25.00	6.51	165	4.91	124	6.53	165	6.75	171	17.30	7.84	F2
RB12260	12	26.00	6.56	167	6.97	177	4.92	125	4.92	125	17.00	7.71	F2 or NB2
RB12280	12	28.00	6.50	165	4.92	125	6.97	177	6.97	177	20.10	9.14	NB1
RBX12330L	12	33.00	12.50	317	3.35	85	6.50	165	6.75	171	24.50	11.11	F2
RBX12330S	12	33.00	6.25	158	6.72	170	6.50	165	6.75	171	24.50	11.11	F2
RB12330	12	33.00	7.72	196	5.14	131	6.22	158	7.00	178	24.00	10.88	NB4
RB12400	12	40.00	7.76	197	6.50	165	6.69	170	6.69	170	29.10	13.20	NB4
RB12550	12	55.00	9.04	230	5.45	138	8.15	207	8.98	228	36.00	16.33	NB3
RB12750	12	75.00	10.25	260	6.60	168	8.15	207	8.98	228	50.60	22.95	NB3
RB121000	12	100.00	12.00	305	6.60	168	8.15	207	8.98	228	68.00	30.84	NB3

\*Height tolerances: (+/-) 0.4in (1mm) and (+/-) 0.08in (2mm) Actual product may vary from images shown

Call 800-245-4784 for additional battery types and sizes



## RBHR High Rate Discharge (UL94 VO flame retardant case and cover)

Part No.	Voltage (V)	Capacity (AH)	Length		Width		Height*		Total Height* (Incl. Terminal)		Weight		Standard Terminal
			in	mm	in	mm	in.	mm	in.	mm	lbs	kgs	
RBHR655-FR	6	5.5	2.76	70	1.85	47	3.94	100	4.17	106	2.10	0.95	F1
RBHR690-FR	6	9.0	5.95	151	1.34	34	3.70	94	3.94	100	3.09	1.40	F2
RBHR6121-FR	6	12.0	5.95	151	2.00	51	3.70	94	3.94	100	4.18	1.90	F2
RBHR1235-FR	12	3.5	5.24	133	2.64	67	2.36	60	2.60	66	2.99	1.36	F2
RBHR1255-FR	12	6.0	3.54	90	2.76	70	3.98	101	4.21	107	4.00	1.81	F2
RBHR1280-FR	12	8.5	5.94	151	2.56	65	3.70	94	3.86	98	6.00	2.72	F2
RBHR1290-FR	12	9.0	5.95	151	2.56	65	3.70	94	3.94	100	5.84	2.65	F2
RBHR12100-FR	12	10.5	5.94	151	2.56	65	4.37	111	4.61	117	7.00	3.18	F2
RBHR12120-FR	12	12.0	5.95	151	3.86	98	3.70	94	3.94	100	8.71	3.95	F2
RBHR12150-FR	12	15.0	5.95	151	3.86	98	3.70	94	3.94	100	10.10	4.60	F2
RBHR12180-FR	12	21.0	7.14	181	3.03	77	6.59	167	6.59	167	13.20	5.99	NB2



## RBLL High-Rate Long Life

Part No.	Voltage (V)	Watts/Cell @ 15-min (1.67 V/Cell)	Length		Width		Height*		Total Height* (Incl. Terminal)		Weight		Standard Terminal
			in	mm	in	mm	in.	mm	in.	mm	lbs	kgs	
RBLL6620	6	361	12.70	323	7.00	178	8.98	228	9.21	234	71.6	32.5	T11 20mm
RBLL12100	12	93	6.56	167	4.92	125	6.97	177	6.97	177	17.4	7.9	T12 12mm
RBLL12150	12	143	7.72	196	5.14	131	6.14	156	6.57	167	22.5	10.2	T6 16mm
RBLL12200	12	202	9.04	230	5.45	138	8.15	207	8.98	228	36.0	16.3	T6 16mm
RBLL12300	12	274	10.24	260	6.61	168	8.27	210	8.51	216	54.0	24.6	T6 16mm
RBLL12350	12	330	12.05	306	6.61	168	8.27	210	8.51	216	69.5	31.5	T6 16mm
RBLL12400	12	386	13.00	330	6.80	173	8.35	212	8.66	220	70.0	31.8	T11 20mm
RBLL12500	12	492	13.19	335	6.77	172	10.83	275	10.94	278	92.6	42.0	T11 20mm



## Hawker Cyclon Monobloc

Part No.	Voltage (V)	Capacity (AH)	Length		Width		Height*		Total Height* (Incl. Terminal)		Weight		Standard Terminal
			in	mm	in	mm	in.	mm	in.	mm	lbs	kgs	
0819-0010	4	2.50	3.13	80	1.81	46	2.75	70	2.75	70	0.80	0.36	F1
0809-0010	4	5.00	3.80	97	2.12	54	3.02	77	3.02	77	1.62	0.74	F2
0859-0010	4	8.00	3.81	97	2.13	54	4.00	102	4.00	102	2.11	0.96	F2
0819-0012	6	2.50	4.48	114	1.81	46	2.75	70	2.75	70	1.15	0.52	F1
0809-0012	6	5.00	5.48	139	2.12	54	3.02	77	3.02	77	2.16	0.98	F2
0859-0012	6	8.00	5.48	139	2.13	54	4.00	102	4.00	102	3.15	1.43	F2



## RBG Monobloc Alternative

Part No.	Voltage (V)	Capacity (AH)	Length		Width		Height*		Total Height* (Incl. Terminal)		Weight		Standard Terminal
			in	mm	in	mm	in.	mm	in.	mm	lbs	kgs	
RBG450	4	5.00	3.54	89	1.94	49	2.87	72	2.87	72	1.76	0.79	F2
RBG480	4	8.00	3.54	89	1.94	49	4.00	101	4.00	101	2.56	1.16	F2
RBG625	6	2.50	4.15	105	1.63	41	2.70	69	2.70	69	1.17	0.53	F1
RBG650	6	5.00	5.28	134	1.94	49	3.00	76	3.00	76	2.62	1.18	F2
RBG680	6	8.00	5.28	134	1.94	49	3.99	101	3.99	101	3.88	1.75	F2

\*Height tolerances: (+/-) 0.4in (1mm) and (+/-) 0.08in (2mm) Actual product may vary from images shown

Call 800-245-4784 for additional battery types and sizes



## GEL Series

Part No.	Voltage (V)	Capacity (AH)	Length		Width		Height*		Total Height* (Incl. Terminal)		Weight		Standard Terminal
			in	mm	in	mm	in.	mm	in.	mm	lbs	kgs	
GEL-GRP/U1	12	31.00	7.68	195	5.12	130	6.46	164	7.00	178	23.6	10.7	NB3 or T6
GEL-GRP/22	12	51.00	9.02	229	5.43	138	8.07	215	8.98	228	36.6	16.6	NB5 or T6
GEL-GRP/24	12	72.00	10.20	259	6.61	168	8.19	208	8.98	228	50.7	23.0	NB5 or T6
GEL-GRP/27	12	87.00	12.01	305	6.61	168	8.15	207	8.98	228	59.8	27.1	NB5 or T6
GEL-GRP/31	12	98.00	12.99	330	6.81	173	8.35	212	8.58	218	68.4	31.0	T11


## Custom NiCad & NiMH Packs



When ordering, please specify the part# as follows:

<b>NC</b>	-	<b>AA</b>	-	<b>5</b>	-	<b>D</b>	-	<b>WL</b>
NC = Ni-Cad NM = NiMH		Cell Size		# of Cells		Cell Configuration		Termination

### CELL CONFIGURATIONS



CELL SIZE +/- 0.02" (0.5mm)	AAA	1/3AA	1/2AA (2/3AA)	AA	1/3A	2/3A	4/5A	4/5SC	SC	5/4SC	1/2D	D	F
Height	1.70" 43.1mm	0.65" 16.4mm	1.14" 28.0mm	1.91" 48.5mm	0.65" 16.5mm	1.12" 28.5mm	1.69" 42.8mm	1.30" 33.1mm	1.67" 42.5mm	1.94" 49.3mm	1.40" 35.5mm	2.32" 58.9mm	3.52 89.3mm
Diameter	0.40" 10.2mm	0.56" 14.2mm	0.56" 14.2mm	0.56" 14.2mm	0.66" 16.8mm	0.66" 16.8mm	0.66" 16.8mm	0.88" 22.3mm	0.88" 22.3mm	0.88" 22.3mm	1.28" 32.4mm	1.28" 32.4mm	1.28" 32.4mm

## Standard Terminals

**WL** INSULATED WIRE LEADS

**PC** PRESSURE CONTACTS


**F1** **FASTON**  
0.187" x 0.032"  
quick disconnect tabs.

**F2** **FASTON**  
0.250" x 0.032"  
quick disconnect tabs


**F3/FP** **FASTON POLARIZED**  
Positive: "F2", Negative: "F1"

**SP** **SPRING TERMINALS**  
Fully collapsible positive  
and negative contacts


**T6** THREADED INSERT - 6mm STUD




**T12** THREADED INSERT - 5mm STUD




**NB3**




**T8** THREADED INSERT - 6mm STUD




**NB1**




**NB4**




**T11** THREADED INSERT - 8mm STUD



**NB2**



**NB5**



**Who We Are:** We are a team of battery professionals with over 100 years of combined experience in the battery industry dedicated to finding you battery solutions.

**What We Do:** We provide batteries for almost any application to both the OEM and replacement markets. We have multiple chemistries in stock and can build custom battery packs in as little as 24 hours. Our Customer Support Specialists are trained to properly identify the right battery for you and get it to you ASAP.

Distributed By:

