



Industrial grade 50A locking devices

Product description

2-pole, 3-wire grounding
 50A, 250V/AC
 Non-NEMA, California standard



CS8265



CS8277

California standard plugs & connectors

| Rating A | V/AC | Description | Cord diameter | Color | Plug catalog no. | Connector catalog no. | | |
|-------------|------|---------------------------------------|--------------------------|---------|-----------------------------------|-----------------------------------|---|---|
| 50 | 250 | Pro grip nylon California standard | 0.44-1.06" (11.1-26.0mm) | RD & BK | <input type="checkbox"/> CS8265EX | <input type="checkbox"/> CS8264EX | • | • |
| | | Armored California standard | 0.68-1.13" (17.3-28.6mm) | Steel | <input type="checkbox"/> CS8265 | <input type="checkbox"/> CS8264 | • | • |

California standard grade receptacles

| Rating A | V/AC | Description | Color | Single receptacle | | |
|-------------|------|---------------------------------|-------|---------------------------------|---|---|
| 50 | 250 | California standard receptacles | BK | <input type="checkbox"/> CS8269 | • | • |

California standard flanged inlets

| Rating A | V/AC | Description | Color | Flanged inlet | Flanged inlet w/ lid | | |
|-------------|------|------------------------------------|-------|---------------------------------|---------------------------------|---|---|
| 50 | 250 | California standard flanged inlets | Steel | <input type="checkbox"/> CS8275 | <input type="checkbox"/> CS8277 | • | • |

Accessories for 50A California standard locking devices

| Description | Color suffix | Catalog no. | | |
|----------------------------------------------------------|--------------|---------------------------------|---|---|
| Weather protective glass-filled nylon, w/ lift lid cover | BK, CR, GY | <input type="checkbox"/> 7788_ | • | • |
| Weather protective diecast aluminum, w/ lift lid cover | | <input type="checkbox"/> 7770 | • | |
| Weather protective boot for 50A armored plug | | <input type="checkbox"/> 7716 | • | |
| Weather protective boot for 50A armored connector | | <input type="checkbox"/> 7717 | • | |
| Weather protective boot for 50A pro grip plug | | <input type="checkbox"/> 7716EX | • | |
| Weather protective boot for 50A pro grip connector | | <input type="checkbox"/> 7717EX | • | |



7788CR
Corrosion resistant



7770



7716



7717



7716EX



7717EX

Dimensional information:
 C-80, C-81


Plug & connector specification information:
 50A: C-92

Receptacle specification information:
 50A: C-92

Flanged inlet & flanged outlet specification information:
 50A: C-92

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: BK (Black), GY (Gray), RD (Red), Y or CR (Yellow)



Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32