

# MINITERMS

## Vinyl Ring Terminals

R Series

### SPECIFICATIONS

- Vinyl: Electro tin plated copper, vinyl (PVC) 600V, 75 °C.

### FEATURES

- Vinyl Ring Terminal have Basic tongue type ring terminal. Safe and reliable connections, because it cannot be disconnected unless the screw is completely removed.




FIG. NO.	INSULATION TYPE	WIRE RANGE	STUD SIZE	RATINGS	LENGTH (L) (IN.)	WIDTH (W) (IN.)	SEAM TYPE	"S" PACKS		PRO PACKS		STD PACKS		BULK PACKS	
								CAT. NO.	QTY	CAT. NO.	QTY	CAT. NO.	QTY	CAT. NO.	QTY
1	Vinyl	22-18	1/4	cULus	1.055	0.456	Butted	—	—	—	—	R22-14V	100	R22-14V-BULK	1000
1	Vinyl	22-18	5/16	UL	1.085	0.464	Butted	—	—	—	—	R22-56V	100	R22-56V-BULK	1000
1	Vinyl	22-18	3/8	UL	1.306	0.534	Butted	—	—	—	—	R22-38V	100	R22-38V-BULK	1000
1	Vinyl	22-18	#10	cULus	0.826	0.314	Butted	R22-10V-S	25	R22-10V-P	100	R22-10V	100	R22-10V-BULK	1000
1	Vinyl	22-18	#6	cULus	0.826	0.314	Butted	R22-6V-S	25	—	—	R22-6V	100	R22-6V-BULK	1000
1	Vinyl	22-18	#8	cULus	0.826	0.314	Butted	R22-8V-S	25	R22-8V-P	100	R22-8V	100	R22-8V-BULK	1000
2	Vinyl	16-14	1/4	cULus	1.062	0.472	Butted	—	—	R16-14V-P	70	R16-14V	100	R16-14V-BULK	1000
2	Vinyl	16-14	5/16	cULus	1.062	0.472	Butted	—	—	—	—	R16-56V	100	R16-56V-BULK	1000
2	Vinyl	16-14	3/8	cULus	1.208	0.535	Butted	—	—	—	—	R16-38V	100	R16-38V-BULK	1000
2	Vinyl	16-14	1/2	—	1.348	0.745	Butted	—	—	—	—	R16-50V	100	R16-50V-BULK	1000
2	Vinyl	16-14	#10	cULus	0.866	0.334	Butted	R16-10V-S	25	R16-10V-P	90	R16-10V	100	R16-10V-BULK	1000
2	Vinyl	16-14	#6	cULus	0.767	0.259	Butted	R16-6V-S	25	R16-6V-P	90	R16-6V	100	R16-6V-BULK	1000
2	Vinyl	16-14	#8	cULus	0.866	0.334	Butted	R16-8V-S	25	R16-8V-P	90	R16-8V	100	R16-8V-BULK	1000
3	Vinyl	12-10	1/4	cULus	1.141	0.472	Butted	R12-14V-S	20	R12-14V-P	50	R12-14V	50	R12-14V-BULK	500
3	Vinyl	12-10	5/16	cULus	1.326	0.59	Butted	—	—	—	—	R12-56V	50	R12-56V-BULK	500
3	Vinyl	12-10	3/8	cULus	1.326	0.59	Butted	R12-38V-S	10	—	—	R12-38V	50	R12-38V-BULK	500
3	Vinyl	12-10	1/2	cULus	1.499	0.755	Butted	—	—	—	—	R12-50V	50	R12-50V-BULK	500
3	Vinyl	12-10	#10	cULus	1.003	0.374	Butted	R12-10V-S	10	R12-10V-P	50	R12-10V	50	R12-10V-BULK	500
3	Vinyl	12-10	#6	cULus	1.003	0.374	Butted	—	—	—	—	R12-6V	50	R12-6V-BULK	500
3	Vinyl	12-10	#8	cULus	1.003	0.374	Butted	R12-8V-S	15	R12-8V-P	50	R12-8V	50	R12-8V-BULK	500
4	Vinyl	8	1/4	UL	1.27	0.374	Butted	—	—	—	—	R8-14V	50	R8-14V-BULK	250
4	Vinyl	8	5/16	UL	1.31	0.328	Butted	—	—	—	—	R8-56V	50	R8-56V-BULK	250
4	Vinyl	8	3/8	UL	1.43	0.583	Butted	—	—	—	—	R8-38V	50	R8-38V-BULK	250
4	Vinyl	8	1/2	UL	1.73	0.81	Butted	—	—	—	—	R8-50V	50	R8-50V-BULK	250
4	Vinyl	8	#10	UL	1.27	0.374	Butted	—	—	—	—	R8-10V	50	R8-10V-BULK	250