

Pilot and Signaling Devices

Heavy-Duty 22.5 mm Watertight/Oiltight Selector Switches

C-2000

3-Position Knob Operated Selector Switches
Non-Illuminated
600 VAC Max., 300 VDC Max.
10 Amps Continuous AC, 2.5 Amps Continuous DC

Selection Process

Select operator below + Select contact block(s) from page 9-101 + Select nameplate, if required, from pages 9-103 to 9-105 = Complete Unit



Knob 3-Position

Position Type	Operator Style	Release Type	Cam Codes	Product Number	List Price GO-10GC
3-Position	Round Polished Chrome	Maintained	Z, E, L, U	P9CSM#0*	\$14.50
3-Position	Round Satin Chrome	Maintained	Z, E, L, U	P9MSM#0*	\$14.50
3-Position	Round Engineered Plastic	Maintained	Z, E, L, U	P9XSM#0*	\$14.50
3-Position	Square Engineered Plastic	Maintained	Z, E, L, U	P9SSM#0*	\$14.50
3-Position	Round Polished Chrome	Spring Return L → C	Z, E, L, U	P9CSM#1*	\$16.50
3-Position	Round Satin Chrome	Spring Return L → C	Z, E, L, U	P9MSM#1*	\$16.50
3-Position	Round Engineered Plastic	Spring Return L → C	Z, E, L, U	P9XSM#1*	\$16.50
3-Position	Square Engineered Plastic	Spring Return L → C	Z, E, L, U	P9SSM#1*	\$16.50
3-Position	Round Polished Chrome	Spring Return C ← R	Z, E, L, U	P9CSM#5*	\$16.50
3-Position	Round Satin Chrome	Spring Return C ← R	Z, E, L, U	P9MSM#5*	\$16.50
3-Position	Round Engineered Plastic	Spring Return C ← R	Z, E, L, U	P9XSM#5*	\$16.50
3-Position	Square Engineered Plastic	Spring Return C ← R	Z, E, L, U	P9SSM#5*	\$16.50
3-Position	Round Polished Chrome	Spring Return L → C ← R	Z, E, L, U	P9CSM#3*	\$16.50
3-Position	Round Satin Chrome	Spring Return L → C ← R	Z, E, L, U	P9MSM#3*	\$16.50
3-Position	Round Engineered Plastic	Spring Return L → C ← R	Z, E, L, U	P9XSM#3*	\$16.50
3-Position	Square Engineered Plastic	Spring Return L → C ← R	Z, E, L, U	P9SSM#3*	\$16.50


3-Position Selector Switches

Replace double dagger (§) in product number with cam code from cams table below.


Cams

Choose desired cam. Note selection and position of contact block(s).

§Cam Code				Screw Terminal Contact Block				Quick-Connect Terminal Contact Block	
				Position 1	Position 2	Position 1	Position 2		
Z	0	0	X	P9B10VN	—	P9B10FN	—	—	
	X	0	0	—	P9B10VN	—	P9B10FN	—	
	X	X	0	P9B01VN	—	P9B01FN	—	—	
	0	X	X	—	P9B01VN	—	P9B01FN	—	
	0	0	X	P9B11VN	—	—	—	—	
	X	X	0	—	—	—	—	—	
	0	X	X	—	P9B11VN	—	—	—	
E	0	0	X	—	P9B01VN	—	P9B01FN	—	
	0	X	0	P9B10VN	—	P9B10FN	—	—	
	0	0	X	P9B11VN	—	—	—	—	
L	0	0	X	—	P9B01VN	—	P9B01FN	—	
	0	X	0	P9B01VN	—	P9B01FN	—	—	
	X	0	0	P9B11VN	—	—	—	—	
	0	X	0	—	—	—	—	—	
U	0	0	X	P9B11VN	—	—	—	—	
	0	X	0	—	—	—	—	—	
	0	0	X	—	P9B11VN	—	—	—	
	X	0	0	—	—	—	—		



Operator Positions



Contact Block Positions (viewed from rear)

Replace asterisk (*) in product number with color code from colors table below.

*Colors

Colors	Black	Red	Green	Yellow	Blue	No Knob ¹
*Color code	N	R	V	G	L	0

¹Subtract \$3.00 from List Price, GO-10GC, for selector switches ordered without knobs. Color knobs are listed separately on page 9-111.

