

Temp Light Fixtures



BLITE-105CFL



BLITE-400PS



BLITE-400PS-277



BLITE-105CFL

- Easy installation units comes fully assembled
- 105w CFL equal to 300w incandescent lamp
- 1ft Daisy Chain or Power Tool Option
- Low to medium bay lighting applications
- Bright Temp Lighting at a Low Cost!



BLITE-400PS

- Labor saving units comes fully assembled
- Multi-Tap ballast: 120v, 208v, 240v, 277v (factory wired 120v)
- 400w, clear MH Pulse Start lamp (included) meets OSHA1926.56 for minimum illumination of work areas (minimum of 5 foot-candles for general construction area lighting)



BLITE-400PS-277

- Labor saving units comes fully assembled
- Multi-Tap ballast: 120v, 208v, 240v, 277v (factory wired 277v)
- 400w, clear MH Pulse Start lamp (included) meets OSHA1926.56 for minimum illumination of work areas (minimum of 5 foot-candles for general construction area lighting)



Overall Features

- Snap-Lock Hook
- Open-Close Cage
- Lamp Included
- Full Color Packaging



Packaging Great For Counter Area Displays

