

DESCRIPTION			LUMENS	POWER USED	REPLACES	BASE	CCT			DIMENSIONS
LED-8033E 38W POST TOP SITE LIGHTING	LED-8033E30	LED-8033E30C	3889	38W	175W	E26 Edison	3000K	✓		9.53" x 3.15"
	LED-8033E42	LED-8033E42C	4367	38W	175W	E26 Edison	4200K	✓		9.53" x 3.15"
	LED-8033E57	LED-8033E57C	4275	38W	175W	E26 Edison	5700K	✓		9.53" x 3.15"
LED-8024E 45W POST TOP SITE LIGHTING	LED-8024E30	LED-8024E30C	4969	45W	175W	E26 Edison	3000K	✓		9.22" x 3.15"
	LED-8024E42	LED-8024E42C	5361	45W	175W	E26 Edison	4200K	✓		9.22" x 3.15"
	LED-8024E57	LED-8024E57C	5037	45W	175W	E26 Edison	5700K	✓		9.22" x 3.15"
LED-8024M 45W POST TOP SITE LIGHTING	LED-8024M30	LED-8024M30C	5107	45W	175W	E39 Mogul	3000K	✓	✓	9.75" x 3.25"
	LED-8024M42	LED-8024M42C	5146	45W	175W	E39 Mogul	4200K	✓	✓	9.75" x 3.25"
	LED-8024M57	LED-8024M57C	5297	45W	175W	E39 Mogul	5700K	✓	✓	9.75" x 3.25"
LED-8046M 65W POST TOP SITE LIGHTING	LED-8046M30	LED-8046M30C	5850	65W	250W	E39 Mogul	3000K	✓	✓	11.22" x 3.98"
	LED-8046M42	LED-8046M42C	6350	65W	250W	E39 Mogul	4200K	✓	✓	11.22" x 3.98"
	LED-8046M57	LED-8046M57C	6497	65W	250W	E39 Mogul	5700K	✓	✓	11.22" x 3.98"
LED-8027M 100W POST TOP SITE LIGHTING	LED-8027M30	LED-8027M30C	10603	100W	400W	E39 Mogul	3000K	✓	✓	11.9" x 4.9"
	LED-8027M42	LED-8027M42C	10669	100W	400W	E39 Mogul	4200K	✓	✓	11.9" x 4.9"
	LED-8027M57	LED-8027M57C	10083	100W	400W	E39 Mogul	5700K	✓	✓	11.9" x 4.9"
LED-8083E 30W POST TOP w/External Driver DIMMABLE	LED-8083E30	NA	3300	30W	100W	E26 Edison	3000K	✓		6.02" x 2.76"
	LED-8083E40	NA	3300	30W	100W	E26 Edison	4000K	✓		6.02" x 2.76"
	LED-8083E57	NA	3300	30W	100W	E26 Edison	5700K	✓		6.02" x 2.76"
LED-8084M 45W POST TOP w/External Driver DIMMABLE	LED-8084M42	NA	4273	45W	175W	E39 Mogul	4200K	✓	✓	10.5" x 3.93"
	LED-8084M57	NA	4509	45W	175W	E39 Mogul	5700K	✓	✓	10.5" x 3.93"
LED-8085M 60W POST TOP w/External Driver DIMMABLE	LED-8085M42	NA	5807	60W	250W	E39 Mogul	4200K	✓	✓	10.5" x 3.93"
	LED-8085M57	NA	6130	60W	250W	E39 Mogul	5700K	✓	✓	10.5" x 3.93"

VOLTAGE:  120-277VAC  120-347VAC • >80 CRI • 50,000 HOUR RATED LIFE • 5 YEAR WARRANTY