



Night Scene[®]

BY PROGRESS LIGHTING

FIRST IMPRESSIONS COUNT.

Professional outdoor lighting can dramatically improve the appearance of your home while providing additional safety and security. Night Scene can highlight the architectural elements of your home or turn your beautiful garden into a night-time treasure.

People choose landscape lighting to display the beauty of their residence and surroundings. Lighting can extend the daylight hours, and add safety and security.



FOUR BASIC STEPS IN LANDSCAPE LIGHTING

STEP 1. WHAT TO LIGHT



STEP 2. CHOOSING A LIGHTING SYSTEM



Examine your home and its surroundings. Ask yourself: what favorite landscape features need accent lighting? Decide what you would like to illuminate (architectural features of the house, flowers, shrubs, trees, sculpture, deck, path or general areas). Determine if you want these elements to be focused upon with accent lighting, or to be provided with general illumination from background lighting.

120-VOLT LINE-VOLTAGE SYSTEM

A 120-volt system—standard in most American homes—is usually recommended if the lighted subject is larger than 25 ft. or positioned more than 30 ft. from the fixture.

12-VOLT LOW-VOLTAGE SYSTEM

12-volts is preferable for less-permanent lighting fixtures that can be moved to accommodate plant growth or changing needs.




STEP 3. LANDSCAPE LIGHTING TECHNIQUES



There are many different techniques for lighting areas or objects. These techniques are path lighting, spread lighting, spot lighting in an upward direction or downward direction, grazing, cross lighting, shadowing and silhouetting. See the Night Scene Catalog for more detailed information.

STEP 4. LANDSCAPE LIGHTING PLANS



It will help to draw a plan, in scale as if looking down on the house or grounds. This will help you determine what areas you want to accent or provide general illumination. Consider where your transformer will be installed if a 12 volt system is selected. Placement of your fixtures will help determine cable lengths and size required.

MODULAR BOLLARDS

P5286-86, P5287-86*



P5289-30, P5290-30*



P8679-86 SHOWN WITH P5286-86 TOP



All modular bollards shown with P8680 post section. (Mounting post not included)

P5286-71, P5287-71*



P5289-20, P5290-20*



P8679-86

P8680-86



P5286-71 Gilded Iron
P5286-86 Burnished Chestnut
 120V line voltage. 8 panel with white art glass.
 SIZE: 6-7/8" W., 10-3/4" ht.
 LAMP: One medium base 100w max.

P5289-20 Antique Bronze
P5289-30 White with Copper Roof
 120V line voltage. Path light with arched window and white art glass.
 SIZE: 6-7/8" W., 10" ht.
 LAMP: One medium base 100w max.

P8679-20 Antique Bronze
P8679-30 White
P8679-71 Gilded Iron
P8679-86 Burnished Chestnut
 Extruded aluminum pier mount with cast aluminum flange for mounting to cement, wood or directly to J-box.†
 SIZE: 6" W., 4-7/8" ht.

P5287-71 Gilded Iron
P5287-86 Burnished Chestnut
 12V low voltage. 8 panel with white art glass.
 SIZE: 6-7/8" W., 10-3/4" ht.
 LAMP: One 50w 12V MR16.
 Bi-pin socket.

P5290-20 Antique Bronze
P5290-30 White with Copper Roof
 12V low voltage. Path light with arched window and white art glass.
 SIZE: 6-7/8" W., 10" ht.
 LAMP: One 50w 12V MR16. Bi-pin socket.

P8680-20 Antique Bronze
P8680-30 White
P8680-71 Gilded Iron
P8680-86 Burnished Chestnut
 Extruded aluminum post with cast aluminum flange for mounting to cement, wood or directly to J-box.†
 SIZE: 6" W., 25-1/2" ht.

 Low Voltage

* All low voltage fixtures include 1/2 NPS threaded adapter, connector (P8651), mounting stake (P8618-31), and lamp. All low voltage units must be connected to a 12v transformer.

† Stake included for anchoring into ground for low voltage applications. For use with modular bollards. Includes J-bolts and pattern for concrete mounting. Base includes 1/2" IP threaded opening for mounting to conduit.

PATH / SPREAD LIGHTS

P5260-20*



P5218-20*



P5271-20*




P5255-20*



P5217-33*



P5276-71*



P5217-33 Cobblestone 
Gazing ball path light with clear optic glass. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 6" dia., 25" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

P5218-20 Antique Bronze 
Tiffany turtle path light. Cast aluminum construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 6" dia., 25" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

P5255-20 Antique Bronze 
Tiffany art glass panels suspended from a shepherd's crook. Solid brass construction. Stem, 1/2 NPS thread adapter, mounting stake included.
SIZE: 4" sq., 27" ht., 7-1/2" depth
LAMP: One 18w 12-volt T5 wedge base (included).


P5260-20 Antique Bronze 
Tree style path light with acorn patterned green glass and opalescent glass leaf accents. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 4 3/4" dia., 21-1/2" ht., 16" depth
LAMP: One 18w 12-volt T5 wedge base (included).

P5271-20 Antique Bronze 
Green Tiffany art glass shade suspended from detailed arm. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 7" dia., 23" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

P5276-71 Gilded Iron 
Cranbrook path light. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 6-1/4" dia., 25" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

PATH / SPREAD LIGHTS

P5250-33*



P5250-31*



P5275-31*



P5272-46*



P5294-50*



P5273-33



P5250-31 Black 
P5250-33 Cobblestone 
 Ashmore Collection path light with water seeded glass. Cast aluminum construction. Square stem with 1/2 NPS thread adapter, connector, mounting stake and lamp included.
 SIZE: 6-1/2" W., 25-1/2" ht.
 LAMP: One 18w 12-volt T5 wedge base (included).

P5272-46 Weathered Bronze 
 Arts & Crafts path light with light honey art glass panels. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
 SIZE: 5-1/2" W., 28-3/4" ht., 6-1/2" depth
 LAMP: One 18w 12-volt T5 wedge base (included).

P5273-33 Cobblestone
 Mission style path light with light honey art glass. Solid brass construction. Square stem included with 1/2 NPS thread.
 SIZE: 6-1/2" sq., 30" ht.
 LAMP: One medium base A-19 lamp, 60w max.

P5275-31 Black 
 Coventry path light with water seeded glass. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
 SIZE: 5-3/4" dia., 25" ht.
 LAMP: One 18w 12-volt T5 wedge base (included).

P5294-50 Golden Baroque 
P5294-71 Gilded Iron 
 Tiffany Collection path light with etched and water patterned glass. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
 SIZE: 5" W., 22" ht., 6-3/4" depth
 LAMP: One 18w 12-volt T5 wedge base (included).

P5253-33*



P5253-44*



P5261-33*



P5277-71*



P5277-50*



P5257-20*



P5253-33 Cobblestone 
P5253-44 Oxford Silver 
 Cast aluminum shade and wire guard with etched glass enclosure. Solid brass stem. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
 SIZE: 6" W., 25" ht.,
 LAMP: One 18w 12-volt T5 wedge base (included).

P5257-20 Antique Bronze 
 Path light with clear optic seeded glass. Solid brass or copper construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included. (Copper finish will age over time to a natural patina.)
 SIZE: 7-3/4" dia., 26" ht., 10" depth
 LAMP: One 18w 12-volt T5 wedge base (included).

P5277-50 Golden Baroque 
P5277-71 Gilded Iron 
 Cape Cod Collection cast aluminum path light with etched water glass closure. Solid brass stem. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
 SIZE: 6" dia., 25" ht., 7-1/2" depth
 LAMP: One 18w 12-volt T5 wedge base (included).

P5261-33 Cobblestone 
 Mission style path light with light honey art glass. Solid brass construction. Square stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
 SIZE: 6-1/2" sq., 19-3/8" ht.
 LAMP: One 18w 12-volt T5 wedge base (included).

 Low Voltage

* All low voltage fixtures include 1/2 NPS threaded adapter, connector (P8651), mounting stake (P8618-31), and lamp. All low voltage units must be connected to a 12v transformer.

PATH / SPREAD LIGHTS

P5252-40*



P5231-20*



P5231-25*



P5232-20*



P5232-25*



P5215-25*



P5215-25 Acid Verde 
 Dome path light with clear glass shade. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 5" dia., 7" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

P5231-20 Antique Bronze 
P5231-25 Acid Verde 
 Square path light with beveled glass panels suspended from shepherd's crook arm. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 5" sq., 6-1/8" ht., Overall ht. 28".
LAMP: One 18w 12-volt T5 wedge base (included).

P5252-40 Millstone 
 Renaissance Collection path light with scroll arms and white washed alabaster style glass. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 7-5/8" dia., 27-1/2" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

P5232-20 Antique Bronze 
P5232-25 Acid Verde 
 Square path light with glass panels. Solid brass construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 4-1/4" sq., 6-1/8" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

 Low Voltage

* All low voltage fixtures include 1/2 NPS threaded adapter, connector (P8651), mounting stake (P8618-31), and lamp. All low voltage units must be connected to a 12v transformer.

P5208-43*



P5243-25*



P5242-31*



P5268-31



P5238-25WB*



P5265-31



P5208-20 Antique Bronze 
P5208-43 Colonial Silver 
Aberdeen path light with clear water seeded glass. Includes mounting stake and quick-connector.
SIZE: 5" sq., 22" ht.
LAMP: One 18w 12-volt halogen T5 wedge base lamp (included).

P5238-25WB Verde 
P5238-31WB Black 
20w bi-pin halogen cast aluminum spread light. Twist off cover for easy relamping. Stake, stem and lamp included.
SIZE: 6-1/2" dia., 11-1/2" ht.
LAMP: One 20w 12-volt halogen bi-pin (included).

P5242-31 Black 
Adjustable path/flood. Die cast aluminum construction. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 7" W., 27" ht., Extends 13"
LAMP: One 18w 12-volt T5 wedge base (included).

P5243-25 Verde 
Tulip style path light. Cast aluminum construction. Stem with 1/2 NPS thread included. Stem, 1/2 NPS thread adapter, connector, mounting stake and lamp included.
SIZE: 4" dia., 24-3/4" ht.
LAMP: One 18w 12-volt T5 wedge base (included).

P5265-31 Black
Aluminum dome. White innerlined shade for maximum light output. Stem and 1/2 NPS thread included.
SIZE: 9" dia., 26-3/4" ht.
LAMP: One medium base A-19 lamp, 100w max.

P5268-31 Black
Pagoda style white innerlined shades and white glass diffuser. Cast aluminum construction. For direct burial only. 1/2 NPS thread. Stem included.
SIZE: 10" dia., 37" ht.
LAMP: One 100w medium base.



PATH / BORDER LIGHTS

P5204-38



P5209-38



P5219-31*



P5204-31 Black
P5204-38 Green
 Cast aluminum. Clear glass liner.
 1/2 NPS threaded fitting for
 permanent or P5233 installation.
 SIZE: 6" dia., 7" ht.
 LAMP: One medium base lamp,
 100w max.

P5209-31 Black
P5209-38 Green
 Polypropylene. Clear ribbed liner.
 1/2 NPS threaded fitting for permanent
 or P5233 installation. NPF Ballast.
 SIZE: 6-1/4" dia., 8-3/4" ht.
 LAMP: One 7w twin 2-pin compact
 fluorescent.

P5219-31 Black 
P5219-38 Green 
 Cast aluminum. Clear glass liner.
 1/2 NPS threaded fitting for P8667
 or P8618 installation. Stem, 1/2 NPS
 thread adapter, connector, mounting
 stake and lamp included.
 SIZE: 6" dia., 7" ht.
 LAMP: One 18w 12-volt T5 wedge
 base (included).



P5233-31 Black
 7" Cast aluminum spike for portable
 installation. 15' SIT cord with plug.
 Accommodates 1/2 NPS threaded fitting.

P5205-31



P5313-31



P5210-31



P5312-31



P5205-31 Black
Etched glass. 1/2 NPS threaded fitting for permanent or P5233 installation.
SIZE: 5" dia., 7-1/4" ht.
LAMP: One medium base lamp, 60w max.

P5210-31 Black
Cast aluminum path and driveway light. Clear glass liner. 1/2 NPS threaded fitting for permanent or P5233 installation.
SIZE: 10" dia., 9-1/2" ht.
LAMP: One medium base lamp, 100w max.

P5312-31 Black
Bollard shown with P5210-31 light (order each separately).
SIZE: 3-7/8" dia., 28-3/8" ht. (Less P5210)
LAMP: Accepts P5210-31.

P5313-31 Black
Bollard shown with P5205-31 light (order each separately).
SIZE: 4-3/4" dia., 28-3/8" ht. (Less P5205)
LAMP: Accepts P5205-31.

 Low Voltage

- * All low voltage fixtures include 1/2 NPS threaded adapter, connector (P8651), mounting stake (P8618-31), and lamp. All low voltage units must be connected to a 12v transformer.

ACCENT LIGHTS

P5230-31*



P5240-25WB*



P5278-31*



P5279-25*



P5230-31 Black 
Miniature low voltage spot light.
Black powder coat finish over die cast aluminum.
Locking vertical adjustment. Mounting stake included.
SIZE: 3" dia., 5" long.
LAMP: One 50w 12-volt MR16.

P5278-25 Verde 
P5278-31 Black 
12V composite spot light. Non-metallic construction and stainless hardware prevent corrosion.
SIZE: 3" dia., 5-5/8" ht.
LAMP: One MR16, GU5.3 base, 35w max.

P5240-25WB Verde 
P5240-31WB Black 
Die cast aluminum construction.
Sealed clear lens cover. Locking vertical adjustment. Mounting stake included.
SIZE: 2" dia., 6" ht.
LAMP: One 20w 12-volt MR11 (included).

P5279-25 Verde 
P5279-31 Black 
12V composite spot light.
Non-metallic construction and stainless hardware prevent corrosion.
SIZE: 4-1/4" dia., 8-3/4" ht.
LAMP: One MR16, GU5.3 base, 50w max.

P5234-31



P5235-31



P5236-31*



P5237-31*



P5234-31 Black
Black powder-coat painted cast aluminum resists chipping and fading. Clear lens. Locking vertical adjustment.
SIZE: 4-1/2" dia., 6-5/8" long.
LAMP: One PAR 20 50w max.

P5235-31 Black
Black powder-coat painted aluminum resists chipping and fading. Clear lens. Locking vertical adjustment.
SIZE: 5-1/4" dia., 8-1/4" long.
LAMP: One 150w PAR 38.

P5236-31 Black 
Black powder-coat painted aluminum resists chipping and fading. Locking vertical adjustment. Mounting stake included. Shown with P8612-31 light shield (order separately).
SIZE: 4-1/2" dia., 6-5/8" long.
LAMP: One 50w 12-volt D.C. bayonet halogen reflector.

P5237-31 Black 
Black powder-coat painted aluminum resists chipping and fading. Locking vertical adjustment.
SIZE: 5-1/4 dia., 5-1/4" length.
LAMP: One 50w 12-volt PAR-36.

 Low Voltage

* All low voltage units must be connected to a 12v transformer.



P5280-11*



ACCENT LIGHTS

P5241-31



P5281-31*



P5241-31 Black
 Black powder-coat painted cast aluminum resists chipping and fading. Clear lens. Locking vertical adjustment.
 SIZE: 4-3/4" dia., 6-5/8" long.
 LAMP: One PAR 30 75w max.

P5280-11 Brass 
 Brass accent fixture. Heavy-duty die-cast brass construction.
 SIZE: 5-3/4" L., (14" L including mounting stake) 3" dia.
 LAMP: One MR-16 lamp, 50w max.

P5281-31 Black 
 Aluminum accent fixture. Cast aluminum construction.
 SIZE: 6-7/8" L., (15-5/8" L including mounting stake) 3" dia.
 LAMP: One MR-16 lamp, 50w max.

 Low Voltage

* All low voltage units must be connected to a 12v transformer.

LINEAR PATH LIGHT

P5200-20*



ACCENT LIGHT KIT

P5230-31KIT*



P5200-20 Antique Bronze 
Linear path light. Cast bronze.
Furnished with stake. Patent pending.
SIZE: 7" W., 1-7/8" ht.
LAMP: One 18w 12-volt T5 wedge
base (included).

P5230-31KIT Black 
Miniature low voltage spot light kit.
Packed in units of 24.
SIZE: 3" dia., 5" long.
LAMP: 50w 12-volt MR16 lamps
(included).
INCLUDED: 24-P5230-31 spot,
24-P8618-31 stake, and 24-MR-16 lamp



POND LIGHT

P5227-31*



HANGING ACCENT LIGHTS

P5244-25*



P5230-31 Black 
Black powder-coat painted
aluminum resists chipping and fading.
Clear lens. Locking vertical adjustment.
SIZE: 4-1/2" dia., 6-5/8" long.
LAMP: One 50w PAR 20.

P5227-31 Black 
Non-metallic pond light. Base accepts
gravel for weighting. Maximum depth 24"
SIZE: 4" W., 6" ht.
LAMP: One 20w 12-volt MR16.

P5244-25 Verde 
P5244-31 Black 
Tulip hanging light. Die cast aluminum.
Unique floral shaped housing. 72"
of nylon coated stainless steel cable
supplied for mounting.
SIZE: 4" dia., 4-1/2" ht.
LAMP: One 18w 12-volt T5 wedge base
(included).

WELL LIGHTS

P5228-31*



FLOOD LIGHTS

P5221-31 WITH P8610-31



P5229-31* w/ P8613-31



P5239-31WB*



P5228-31 Black

Cast aluminum adjustable well light. Clear glass lens. Twist off cover for easy relamping. Internal gimbal ring adjusts 45° max.

SIZE: 3-1/2" dia., 8-1/2" ht.

LAMP: One 20w 12-volt MR-16.

P5229-31 Black

Adjustable well light. Well sleeve is 1/4" thick PVC pipe and installs flush or reversed provides lamp shielding.

SIZE: 6-5/8" dia., 13-1/4" ht.

LAMP: One 50w 12-volt PAR-36.

P5221-31 Black

Offers an intense white illumination for or strong accent lighting and more faithful color fidelity floral displays.

SIZE: 10" W., 10-1/2" ht., 5-1/8" depth

LAMP: One Q300w T3, RSC.

Quartz halogen.

P5239-31WB Black

Adjustable hinge door for easy relamping. Includes stake.

SIZE: 5-1/4" W., 6" ht., 3-1/2" depth

LAMP: One 50w 12-volt halogen bi-pin lamp (included).

P8610-31 Black

Metal visor provides glare and beam control.

DECK / RAIL LIGHTS

P5223-54WB*



P5224-31WB*



P5216-46*



P5251-31WB*



P5262-33*



P5216-46WB Weathered Bronze 
Arts & Crafts deck light with light honey glass. Includes quick-connector.
SIZE: 4" sq., 6" ht.
LAMP: One 18w 12-volt T5 wedge base lamp (included).

P5223-31WB Black 
P5223-54WB Natural 
Durable cast aluminum. Black finish is powder-coat painted to resist chipping, fading and the effects of salt air.
SIZE: 3-1/8" W., 2" ht., extends 1-3/8".
LAMP: One 13w T5 wedge base lamp (included) #912.

P5224-31WB Black 
Durable cast aluminum is powder-coat painted for superior resistance to chipping, fading and the effects of salt air.
SIZE: 3" W., 1-3/4" ht., extends 1-3/8".
LAMP: One 13w T5 wedge base lamp (included) #912.

P5251-31WB Black 
Mini-cylinder deck light. Cast aluminum. Twist off housing for easy relamping.
SIZE: 2" dia., 2-1/2" ht.
LAMP: One 13w T5 wedge base lamp (included) #912.

P5262-33 Cobblestone 
Mission rail mount or post lantern. Fits 4" x 4" post or flush mount.
SIZE: 6-1/2" W., 7-1/2" ht.
LAMP: One 18w T5 wedge base (included).

 Low Voltage

* All low voltage units must be connected to a 12v transformer.

ADDRESS LIGHTS

P5971-20WB*



P5971-31WB*



P5971-33WB*



P5972-30



Shown with numbers



P5971-20WB Bronze 

P5971-31WB Black 

P5971-33WB Cobblestone 

Stake mount address lights. 12V 5w Xenon lamps included. Adjustable to four different heights (10", 16", 22", 28"). Includes stake, Quick-connect and lamps. Requires a 12V transformer (not included).

SIZE: 12-1/2" W., 28" max. ht.

LAMPS: 2 5w Xenon, wedge base (incl.) (see catalog 127 for information on numbers/letters)

P8684-68 Clear

Tempered glass cover for added lamp protection for P5229-31.

P8613-31 Black

Cube cell louver for glare control for P5229-31.

P5972-30 White 

Compact fluorescent address light. Includes stick-on gold address numbers.

SIZE: 4-3/4" W., 9-7/8" ht.

Extends 2-3/8"


LAMP: One 13w 2 pin twin compact fluorescent lamp.

 Low Voltage



* All low voltage units must be connected to a 12v transformer.

STEP LIGHTS



P6802-31





P6817-16



P6803-30



P6819-16



P6802-31 Black

Cast aluminum housing with black metal louver. For wood, brick, masonry, and poured concrete installations. IC Rated.

SIZE: Refer to diagram.

LAMP: One 7w 2-pin twin compact fluorescent lamp.

P6803-31 Black

P6803-30 White

Cast aluminum housing with metal louver. For wood, brick, masonry, and poured concrete installations.

With Thermo-Gard protection.

SIZE: Refer to diagram.

LAMP: One 25w 120-volt T6-1/2, intermediate base.

P6817-16 Satin Aluminum

P6817-31 Black

Cast aluminum, tempered glass with louver faceplate. Two 1/2" I.P. for conduit entry. For poured concrete and masonry installations.

SIZE: Refer to diagram.

LAMP: 25w max. T6-1/2.

P6819-16 Satin Aluminum

Cast aluminum, tempered glass with louver faceplate. Two 1/2" I.P. for conduit entry. For poured concrete and masonry installations.

SIZE: Refer to diagram.

LAMP: 75w max. T6-1/2.

PAR LAMPHOLDERS - ALUMINUM

P5202-30



P5203-20



P5207-30



PAR LAMPHOLDERS - NON-METALLIC

P5211-31



P5212-30



P5214-31



P5202-20 Bronze
P5202-30 White
P5202-31 Black
Single painted adjustable swivel floodlight. Aluminum construction. Locking adjustment.
SIZE: 5-7/8" dia., 9" height
LAMP: One 150w max. PAR20, PAR30 or PAR38.

P5203-20 Bronze
P5203-30 White
P5203-31 Black
Two painted adjustable swivel floodlights with lamp shroud. Aluminum construction.
SIZE: 6-1/4" dia., 9" ht.
LAMPS: Two 150w max. PAR20, PAR30 or PAR38.

P5207-20 Bronze
P5207-30 White
P5207-31 Black
Two painted adjustable swivel floodlights. Aluminum construction. Locking adjustment.
SIZE: 4-3/4" dia., 5-3/4" ht.
LAMPS: Two 150w max. PAR20, PAR30 or PAR38.

P5211-20 Bronze
P5211-30 White
P5211-31 Black
Single non-metallic PAR lamp holder.
SIZE: 4-5/8" dia., 7" ht.
LAMP: One 120w max. PAR 38.

P5212-20 Bronze
P5212-30 White
P5212-31 Black
Double non-metallic PAR lampholder.
SIZE: 11" W., 4-5/8" ht. Extends 5".
LAMP: One 120w max. PAR 38.

P5214-20 Bronze
P5214-30 White
P5214-31 Black
Non-metallic PAR lampholder shroud. Fits P5211 and P5212.
Size: 6-5/8" dia., 5-1/8" ht.

OUTDOOR MOTION SENSORS

P8682-30



P6036-30



P6037-30



P8682-20 Bronze
P8682-30 White
P8682-31 Black
180 Degree detection zone economy motion sensor accessory for Par Lampholders. Adjustable range up to approx. 60 feet (varies with ambient temperature).
SIZE: 5-1/2" L, 3-1/8" W, 2" ht.

P6036-20 Bronze
P6036-30 White
P6036-31 Black
180 Degree detection zone motion sensor accessory for Par Lampholders. Adjustable range up to approx. 70 feet (varies with ambient temperature).
SIZE: 3-3/4" L, 3-3/8" W, 3" ht.

P6037-20 Bronze
P6037-30 White
P6037-31 Black
240 Degree detection zone with Dual-level brightness technology motion sensor accessory for Par Lampholders. Adjustable range up to approx. 100 feet (varies with ambient temperature).
SIZE: 3-3/4" L, 3-3/8" W, 3" ht.



TRANSFORMERS

PLUG-IN COMPATIBLE TRANSFORMERS

P8519-01 P8520-01 P8522-31 P8523-31



P8521-01



with photocell

with timer

with photocell
and timer

PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8519-01	300	300w stainless steel	5-3/8" x 17" x 5-3/8"
P8520-01	600	(2) 300w circuits, stainless steel	6-5/8" x 17" x 5-5/8"
P8521-01	900	(3) 300w circuits, stainless steel	6-5/8" x 19" x 5-7/8"
P8522-31	300	300w	5" x 17" x 5-5/8"
P8523-31	600	(2) 300w circuits	5" x 17" x 5-5/8"

PLUG-IN COMPATIBLE TRANSFORMER ACCESSORIES



P8524-01 Two-prong plug-in timer. Allows multiple settings. (To be used with plug-in compatible transformers.)
SIZE: 2-3/4" W., 3-1/4" ht.



P8525-31 Direct mount photo-cell. Turns transformer on at dusk and off when ambient light appears. (To be used with plug-in compatible transformers.)
SIZE: 1-3/8" dia., 3/4" length.



P8526-31 Remote mount photo-cell. Turns on transformer at dusk and off when ambient light appears. Includes 10 ft. of cord. (To be used with plug-in compatible transformers.)
PHOTOCELL SIZE: 1-3/8" dia., 5-1/4" length



P8531-01 Digital timer. Allows multiple settings. (To be used with plug-in compatible transformers.)
SIZE: 3"w, 4-1/8" ht, extends 1-5/8"

MANUAL TRANSFORMERS

P8590-31, P8591-31, P8592-31



These transformers have all the features shown at left except plug-in capability. Powder coated for outdoor use. UL listed, CUL listed

PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8590-31	150	150w manual	3-1/2" x 8-3/4" x 3"
P8591-31	300	300w manual	4" x 10" x 5"
P8592-31	600	(2) 300w circuits manual	4" x 12" x 4-1/2"

ELECTRONIC TRANSFORMERS

P8517-31 P8518-31



PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8517-31	100	100w electronic	3-5/8" x 6-1/2" x 2-3/8"
P8518-31	300	300w electronic	5-1/8" x 7-1/4" x 3"

ACCESSORIES

ACCENT LIGHT ACCESSORIES



P8611-31 Black
45° cube cell louvers fits under supplied glass lens.
SIZE: 3-1/2" cube cell for P5234-31 & P5236-31.



P8612-31 Black
Light shields adjust to desired length on cowling of light fixture. Rotate bias-cut end to adjust cutoff angle.
SIZE: 5-3/4" long for P5234-31 & P5236-31

P8613-31 Black
45° cube cell louvers fits under supplied glass lens.
SIZE: 4-3/4" cube cell for P5235-31 & P5237-31

P8614-31 Black
Light shields adjust to desired length on cowling of light fixture. Rotate bias-cut end to adjust cutoff angle.
SIZE: 7-1/4" long for P5235-31 & P5237-31

ACCESSORIES FOR INSTALLATION



P8527-01 Direct burial in-ground 12-Volt electronic transformer. Stainless steel housing. Internal and external fittings provided. 100w capacity.
SIZE: 3-5/8" W., 8-5/8" length, 3-3/8" ht.



12-Volt Cable 2 conductor. Black. UL listed.
P8635-31 10-gauge 300 ft.
P8628-31 12-gauge 100 ft.
P8699-31 12-gauge 200 ft.



P8672-31 Black
Miniature pedestal mount. Powder-coat painted cast metal. Flanged base for surface mounting. 1/2 NPS thread.
SIZE: 1-1/2" dia., 1" ht.



P8659-01 Adjustable mounting bracket for low voltage installations. Flexible, stainless steel band adjusts to wrap around tree limbs, poles, etc. from 2" to 6" diameter. Includes "L" bracket and 1/2" stem nut. Wire nuts included.



P8671-31 Black
Polycarbonate canopy for tree trunks and walls. 1/2 NPS thread.
SIZE: 4-1/8" dia. Extends 1-3/16".



MOUNTING STEMS 1/2 NPS THREADS
16" STEM **P8666-31** Black
P8666-38 Green
8-1/2" STEM **P8667-31** Black
P8667-38 Green



P8673-31R Black
For more permanent burial connection. 120 or 12-volt gel-filled direct burial. UL listed. Accepts 10ga to 18ga awg wires.



P8618-31 Black
Ground stake, 8-3/4" ABS movable stake for direct mounting of 12v landscape lights. 1/2 NPS thread.



P8708-01 Silicone filled Underground direct burial wire connectors. #20-#10 gauge. 10 per pack (1 standard pack = 10 pieces). Size: 1-3/4" L., 5/8" dia.



P8562-31 Black
Quick-mount landscape post for 120v or 12v PVC. SIZE: 3" dia., 20" length with stabilizing grid and post, 1/2 NPS threaded hole. Wet location UL listed.



P8651-01 Black
Low voltage Quick-connector. Allows #10 or #12 gauge outdoor low voltage cable to connect to an 18 gauge wire from fixture.
SIZE: 1-5/8" W., 5/8" ht.

LAMPS



PRODUCT	WATT	BEAM SPREAD
P8663-01	20w	25°
P8665-01	50w	25°

Halogen Reflector Lamps for P5236-31 Spotlight D.C. bayonet base.



P7801-01 Lamp
18w T5 wedge base lamp

PROGRESS LIGHTING

MAILING ADDRESS

Post Office Box 6701
Greenville, South Carolina 29606

STREET ADDRESS

701 Millennium Boulevard
Greenville, SC 29607

IN CANADA

1616 Auto Route 440 West
Laval, Quebec
Canada H7S 2E7

www.progresslighting.com
REV (5/07)

Night Scene[®]

BY PROGRESS LIGHTING

Night Scene Landscape Lighting Catalog.

Our full line catalog has helpful information to aid in your entire landscape installation.



Hubbell Lighting, Inc.