



## NMLT Non-Metallic Liquid-Tight

Part Number	Internal Diameter		External Diameter		Lengths (FT)	Weight lbs per 100 ft.
	Min (inch)	Max (inch)	Min (inch)	Max (inch)		
NMLT-3/8	0.484	0.504	0.690	0.710	100 FT.	12.8
NMLT-1/2	0.622	0.640	0.820	0.840	1000 FT.	13.3
NMLT-3/4	0.820	0.840	1.030	1.050	100 FT.	16.3
NMLT-1	1.041	1.066	1.290	1.315	100 FT.	25.9
NMLT-1-1/4	1.380	1.410	1.635	1.660	50 FT.	33.9
NMLT-1-1/2	1.575	1.600	1.865	1.900	50 FT.	44.6
NMLT-2	2.020	2.045	2.340	2.375	50 FT.	61.7

All values are nominal and subject to correction.

**Application:** NMLT is designed for liquid tight applications which are subject to vibration, movement, oil, and corrosives. Suitable for indoor and outdoor use such as indoor lighting, water treatment systems, and HVAC equipment.

**Construction:** One-piece construction of rigid, non-metallic reinforcement embedded in flexible PVC wall for exceptional crush and corrosion resistance. Durable, sunlight resistant and flame retardant thermoplastic PVC that resists heat, oil and chemical breakdown. Convenient markings in feet for easy measurement.

**Standards:** UL listed for direct burial applications  
 UL listed per UL Standard for safety 1660; UL File Number E211327  
 Conforms to the provisions of Article 351 of the NEC  
 Sunlight resistant UL compound PVC Jacket  
 Temperature range: 80°C dry and 60°C, wet to -34°C +70°C. Oil resistant  
 Can be used for lengths of over 6 feet per 1993 NEC

**1-800-945-5542**