

Temporary Lighting Solutions



400 Watt Temporary High Bay Fixture

17400HB

Save time and money with Topaz's fully assembled 400-Watt Temporary High Bay Fixture. Lighting the way with its energy efficient clear Metal Halide Pulse Start lamp, this assembly is housed in a corrosion resistant steel white powder coat finish fixture and protected by a welded steel safety cage. Operating at a reduce temperature with its vented Multi-Tap Pulse Start Ballast, overheating is a non-issue for those extended run periods. And with a built in easy to carry handle and pre-wired for 120V (re-configurable for 208V, 240V & 277V), this temporary fixture can quickly be mounted and meets OSHA requirements for minimum illumination of work areas when properly installed. Combine its improved efficacy (up to 45% more lumens per watt), approved use for damp locations and cold weather starting performance, you'll find the Topaz Temporary High Bay Fixture is an ideal temporary lighting solution for parking garages, mezzanines, outdoors and construction sites.



Temporary Lighting Solutions


400 Watt Temporary High Bay Fixture

Features

- Fully assembled to save time and labor costs
- Labor saving unit comes fully assembled.
- Multi-Tap ballast: 120V, 208V, 240V, 277V (Factory wired 120V)
- 400W, clear MH pulse start lamp included.
- Corrosion resistant welded steel safety cage included. (Replacement cages can also be purchased separately)

Applications

- For use in "High Bay" applications only. Topaz Electric defines High Bay applications greater than 25 feet from the floor.
- Meets OSHA requirements for minimum illumination of work areas when properly installed.



UL and cUL Listed for Damp locations



Meets EISA 2007 for energy efficiency.
Meets NEC 2005 and 2008 requirements.

Order info

| Catalog Number | UPC | Description | Ship Case | Weight/Case |
|----------------|-------|--------------------------------------|-----------|-------------|
| 17400HB | 86898 | 400 Watt Temporary High Bay Fixture | 1 | 24 |
| 17400CG | 86901 | Replacement Safety Cage, 10" Opening | 6 | 17 |

SS-EL-001-B1116



www.topaz-usa.com

NY Headquarters
925 Waverly Avenue
Holtsville, NY 11742
800.666.2852 | Fax: 631.654.1261

CA Office
225 Parkside Drive
San Fernando, CA 91340
888.551.2852 | Fax: 888.690.2852

FL Office
3850 20th Street, Suite 600
Vero Beach, FL 32960
800.338.2852 | Fax: 772.778.5386