

EZ FLOODS



- **New 2" Integra Hood for Friendly Lighting reduces light trespass and glare when properly aimed**
- **Hinged lens frame is captive during relamping**
- **Hydroformed reflector provides field adjustable lamp positions**
- **EZ Grip locknut matches fixture finish and adjusts with fingers, pliers or a screwdriver**
- **Long Life Lamp Included**



Patents:
The design of the EZ Flood is protected by Canada patent D128,348, Mexico patent 29648 and patents pending in the U.S., China and Taiwan

Now with Integra Hood

OPTICS

Easy to Open



Easy to rotate lamp position



ACCESSORIES

Guard



GDEZW

Extra Large Hood



EZH6 & EZH6W

CATALOG NUMBERS

		Bronze	White	Description
High Pressure Sodium Lamp supplied with fixture	35	EZSH35	EZSH35W	35W HPS, HPF, 120V, Bronze or White
	50	EZSH50	EZSH50W	50W HPS, HPF, 120V, Bronze or White
	70	EZSH70	EZSH70W	70W HPS, HPF, 120V, Bronze or White
	70	EZSH70QT	EZSH70QTW	70W HPS, HPF, QT, Bronze or White
	100	EZSH100	EZSH100W	100W HPS, HPF, 120V, Bronze or White
	100	EZSH100QT	EZSH100QTW	100W HPS, HPF, QT, Bronze or White
	150	EZSH150	EZSH150W	150W HPS, HPF, 120V, Bronze or White
	150	EZSH150QT	EZSH150QTW	150W HPS, HPF, QT, Bronze or White

PULSE★START High Efficiency Metal Halide

				Description
Metal Halide Lamp supplied with fixture PS★ = Pulse Start PSQ & QT=Quad Tap=120 / 208 / 240 / 277 volts	PS★ 50	EZHH50QT	EZHH50QTW	50W MH, HPF, QT, Bronze or White
	PS★ 70	EZHH70QT	EZHH70QTW	70W MH, HPF, QT, Bronze or White
	PS★ 100	EZHH100QT	EZHH100QTW	100W MH, HPF, QT, Bronze or White
	PS★ 125	EZHH125PSQ	EZHH125PSQW	125W MH, HPF, PSQ, Bronze or White
	150	EZHH150QT	EZHH150QTW	150W MH, HPF, QT, Bronze or White
	PS★ 150	EZHH150PSQ	EZHH150PSQW	150W MH, HPF, PSQ, Bronze or White

For factory installed options, see RAB catalog