



1595SWTTRWCC4

Straight Blade Receptacles Decorator Combination Tamper-Resistant Switch/GFCI Receptacles

15A, 125VAC

Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Up-down switching.
- 15 Amp single pole switch rated for 1/2 HP motor loads – perfect for bath or kitchen vents and garbage disposals.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

| Catalog Number | Switch Rating A. VAC | Receptacle Rating A. VAC | Color | NEMA Config. No. | 3rd Party Compliance | | |
|--|-------------------------|-----------------------------|--------------|------------------|---------------------------|--------------------------|--------------------------|
| | | | | | UL943 C22.2 No. 144 | UL498 C22.2 No. 42 | UL20 C22.2 No. 111 |
| NEW Combination Tamper-Resistant Single Pole Switch/GFCI | | | | | | | |
| 1595SWTTRICC4 | 15 120 | 15 125 | Ivory | 5-15R | • | • | • |
| 1595SWTTRWCC4 | 15 120 | 15 125 | White | 5-15R | • | • | • |
| 1595SWTTRBKCC4 | 15 120 | 15 125 | Black | 5-15R | • | • | • |
| 1595SWTTRLACC4 | 15 120 | 15 125 | Light Almond | 5-15R | • | • | • |



NEMA
5-15R