



The first plug and play LED replacement for CFLs.

These modest beauties tuck away quietly in recessed fixtures,  
but surprise everyone with beautiful natural light and huge savings.






The 5W Helen Lamp GX23 delivers up to 70% power savings compared to 13W CFLs while eliminating up to 5 replacement maintenance cycles.

This lamp extends the successful Helen Lamp family to GX23 series sockets. While continuing with the retrofit-simplicity of ballast-driven plug-and-play through Lunera's BallastLED™ technology, the Helen Lamp GX23 can also be directly 120V/277V line driven.



### Helen Lamp GX23 Highlights

<b>Input Voltage</b>	Driven by CFL ballast or 120V/277V Line Driven	<b>Color Temp</b>	2700K, 3000K, 3500K, 4000K
<b>Power</b>	5W	<b>Life</b>	50,000 hours life (L70)
<b>CRI</b>	>80	<b>Warranty</b>	5 years
<b>Delivered Lumens</b>	Up to 535lm	<b>Compatibility</b>	Fixtures with GX23 series 2-pin CFL sockets. Single or dual lamp. May be dimmed. Non-lensed or fully-enclosed.



REV 0926