

## Remote and Wall Mount Control Systems

See Control Systems Compatibility Guide for correct controller.




**337001 WH** White  
Basic Hand Held Control System

- 3-Speed Motor Control and Off
- Manual Reverse
- Light On/Off with Full Range Dimming
- Operational Radius of 30 Feet or Less
- Includes Transmitter & Canopy Mounted Receiver
- Includes 9-Volt Battery
- Includes Wall Bracket and all Mounting Hardware



**337010 WH** White  
**337010 IV** Ivory  
**337010 ALM** Almond  
Fan/Light Dual Slider Control

- 4-Speed Fan Control
- Full Range Dimming Light Control
- Face Plate Included
- Controls One Fan and Light
- For Use with Most Ceiling Fans
- Max. 1.25 AMP
- Requires 3 Wire + Ground Installation



**370012 MUL** White/Ivory/Almond  
Wall Mount Transmitter  
(Full Function)

- 3-Speed Motor Control and Off
- Remote Forward and Reverse
- Light On/Off with Full Range Dimming & Intelligent Return
- Controls Multiple Fans
- Includes White, Ivory & Almond Switch & Wall Cover Plates
- Includes all Necessary Mounting Hardware & Battery
- Includes Transmitter Only, Works in Conjunction with our CoolTouch™ Control Systems
- NOT compatible with any DC Control System



**337011 WH** White  
**337011 IV** Ivory  
**337011 ALM** Almond  
Light Dimmer Slide Control

- Full Range Light Dimmer
- Face Plate Included
- Controls One Fan Light or Light Fixture
- For Use with Most Ceiling Fans
- 600-W. Max.

## Remote and Wall Mount Control Systems



**370014 MUL** White/Ivory/Almond  
Wall Mount Transmitter  
(Limited Function)

- 3 Speed Motor Control and Off
- Manual Reverse
- Light On/Off with Full Range Dimming and Intelligent Return
- Controls Multiple Fans
- Includes White, Ivory & Almond Switch & Wall Cover Plates
- Includes all Necessary Mounting Hardware & Battery
- Includes Transmitter Only, Works in Conjunction with our CoolTouch™ Control Systems
- NOT compatible with any DC Control System



**337012 WH** White  
**337012 IV** Ivory  
**337012 ALM** Almond  
4 Speed Fan Slide Control

- 4-Speed Fan Control
- Face Plate Included
- Controls One Fan
- For Use with Most Ceiling Fans
- Max. 1.25 AMP



**337214** (Standard White Finish)  
Universal CoolTouch™ Control System  
CoolTouch™ Control Systems: Looks permanent, but goes wherever you go!

- Designed SPECIFICALLY for Incandescent OR Fluorescent operation
- 3 Speed Motor Control and Off
- Manual Forward and Reverse Operation
- Down Light Control: On/Off with Dimming (Incandescent) or On/Off ONLY (Fluorescent)
- Wireless (Radio Frequency) Operation
- Operational Radius of 30 Feet or Less
- Retrofits most Pull Chain Fans
- No Wires to Run, No Holes to Cut
- Replaces Any Single Wall Switch or Mounts on Any Flat Surface
- Receiver Designed for Wet Locations. Mount Transmitter in Dry or Indoor Location ONLY
- Includes all necessary Mounting Hardware
- Includes Replaceable Long Life Lithium Batteries
- Includes Wall Pocket, Transmitter & Canopy Mounted Receiver
- Comes in Standard White Finish, see accessory color options on page 224
- Compatible with MOST Ceiling Fan Brands
- U.S. Patent Pending

Our Control System Ordering Guide on page 225 will step you through the simple process of converting your ceiling fan to Remote Control Operation. Please see our Control Systems Compatibility Guide on page 226-227 to identify all the ceiling fans that are compatible with this CoolTouch™ Control System.