



CE Series

- Universal Face
- Damp Location Listed
- NiCad Battery

- 120/277 VAC
- Thermoplastic Housing



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93043113	CER	856143001448	Red Letters, White Housing	•	•	•	•	2.00 lbs	6	
93053081	CERB	782520867126	Red Letters, Black Housing	•			•	2.00 lbs	6	
93043116	CERRC	856143001462	Red Letters, Remote Capacity, White Housing	•	•	•	•	2.00 lbs	6	
93053083	CERRCB	782520867140	Red Letters, Remote Capacity, Black Housing	•			•	2.00 lbs	6	
93043114	CEG	856143001455	Green Letters, White Housing	•	•	•	•	2.00 lbs	6	
93053082	CEGB	782520867133	Green Letters, Black Housing	•			•	2.00 lbs	6	
93043117	CEGRC	856143001479	Green Letters, Remote Capacity White Housing	•			•	2.00 lbs	6	



CC Series

- Combination LED Exit/Unit
- Damp Location Listed
- LED Lamp-Heads
- NiCad Battery



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93043109	CCR	856143001400	Red Letters, White Housing Single/Double Face	•	•	•	•	2.5 lbs	6	
93053078	CCRB	782520867096	Red Letters, Black Housing Single/Double Face	•			•	2.5 lbs	6	
93043110	CCG	856143001417	Green Letters, White Housing Single/Double Face	•			•	2.5 lbs	6	
93053079	CCGB	782520867102	Green Letters, Black Housing Single/Double Face	•			•	2.5 lbs	6	
93043111	CCRRC	856143001424	Red Letters, White Housing Single/Double Face, Remote Capacity	•	•	•	•	2.5 lbs	6	
93053080	CCRCB	782520867119	Red Letters, Black Housing Single/Double Face, Remote Capacity	•			•	2.5 lbs	6	
93043112	CCGRC	856143001431	Green Letters, White Housing Single/Double Face, Remote Capacity	•			•	2.5 lbs	6	



CEL Series

- Commercial LED Edge-Lit Exit Sign
- Brushed Aluminum Housing with Battery
- 120/277 VAC



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93043118	CELS1RNE	856143001547	Red Letters, Single Face, Surface Mount	•			•	3.23 lbs	6	
93043119	CELS1GNE	856143001554	Green Letters, Single Face, Surface Mount	•				3.23 lbs	6	
93043120	CELS2RNE	856143001561	Red Letters, Double Face, Surface Mount	•			•	3.23 lbs	6	
93043121	CELS2GNE	856143001578	Green Letters, Double Face, Surface Mount	•				3.23 lbs	6	
93043122	CELR1RNE	856143001585	Red Letters, Single Face, Recessed Mount	•			•	6.14 lbs	3	
93043123	CELR1GNE	856143001592	Green Letters, Single Face, Recessed Mount	•				6.14 lbs	3	
93043124	CELR2RNE	856143001608	Red Letters, Double Face, Recessed Mount	•			•	6.14 lbs	3	
93043125	CELR2GNE	856143001615	Green Letters, Double Face, Recessed Mount	•				6.14 lbs	3	



CEW Series

- NiCad Battery
- 120/277VAC Input
- Green or Red LED with Battery
- Impact Resistant Polycarbonate Housing and Face-Plate
- Wet Location Listed



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93047782	CEWSRE	856143001646	Red Letters, Single Face	•	•	•	•	4.3 lbs	6	
93047783	CEWDRE	856143001653	Red Letters, Double Face	•	•	•	•	4.3 lbs.	6	
93047784	CEWSGE	856143001660	Green Letters, Single Face	•				4.3 lbs	6	
93047785	CEWDGE	856143001677	Green Letters, Double Face	•				4.3 lbs.	6	



CSR Series

- 120 or 220-240VAC
- 50/60 Hz Input
- White Thermoplastic Housing
- Universal Face



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93058260	CSRIV	856143001783	International Voltage SALIDA LED Sign, AC only	•			•	2.00 lbs.	6	
93056261	CSREIV	856143001790	International Voltage SALIDA LED Sign, Emergency with NiCad battery	•			•	2.00 lbs.	6	



CCE Series

- Thin Die-Cast LED Exit Sign
- 120/277 VAC Input
- AC or Emergency
- Top, End or Ceiling Mount



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93047786	CCESRE	856143001684	Red Letters, Single Face, NiCad Battery	•			•	2.80 lbs	8	
93047787	CCEDRE	856143001691	Red Letters, Double Face, NiCad Battery	•			•	2.80 lbs	8	
93047788	CCESGE	856143001707	Green Letters, Single Face, NiCad Battery	•				2.80 lbs	8	
93047789	CCEDGE	856143001714	Green Letters, Double Face, NiCad Battery	•				2.80 lbs	8	
93047790	CCESR	856143001721	Red Letters, Single Face, AC Only	•			•	2.80 lbs	8	
93047791	CCEDR	856143001738	Red Letters, Double Face, AC Only	•			•	2.80 lbs	8	
93047792	CCESG	856143001745	Green Letters, Single Face, AC Only	•				2.80 lbs	8	
93047793	CCEDG	856143001752	Green Letters, Double Face, AC Only	•				2.80 lbs	8	



CWC

- Wet Location Combination Exit/Emergency Light
- UL924 Wet Location Listed
- Fully adjustable LED lamp-heads



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty
93063664	CWC1RW	856143001837	White Housing, Single Face, Red Letters	•			•	8.00 lbs	4
93063665	CWC2RW	856143001844	White Housing, Double Face, Red Letters	•			•	8.00 lbs	4
93063666	CWC1GW	856143001851	White Housing, Single Face, Green Letters	•				8.00 lbs	4
93063667	CWC2GW	856143001868	White Housing, Double Face, Green Letters	•				8.00 lbs	4
93063668	CWC1RW-CT	856143001875	White Housing, Single Face, Red Letters, Cold Temperature Operation	•			•	8.00 lbs	4
93063669	CWC2RW-CT	856143001882	White Housing, Double Face, Red Letters, Cold Temperature Operation	•			•	8.00 lbs	4
93063670	CWC1GW-CT	856143001899	White Housing, Single Face, Green Letters, Cold Temperature Operation	•				8.00 lbs	4
93063671	CWC2GW-CT	856143001905	White Housing, Double Face, Green Letters, Cold Temperature Operation	•				8.00 lbs	4



CU2 Series

- 2 Double Head LED Emergency Light
- Dual-Input 120/277 VAC
- NiCad Battery
- Damp Location Listed

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93043107	CU2	856143001486	White Hosing	•	•	•	•	1.00 lbs	12	
93053076	CU2B	782520867072	Black Hosing	•			•	1.00 lbs	12	
93043108	CU2RC	856143001493	White Housing, Remote Capacity	•			•	1.00 lbs.	12	
93053077	CU2RCB	782520867089	Black Housing, Remote Capacity	•			•	1.00 lbs	12	



CUW Series

- Decorative LED AC/Emergency Light
- Durable die-cast aluminum housing
- Wet Location Listed
- Normally On and Emergency Operation

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93063364	CUWZ-PC	856143001806	Die-Cast, 0° to 50°C, with Photo-Control, Dark Bronze Finish	•			•	4.00 lbs.	6	
93063366	CUWZ-HTR-PC	856143001820	Die-Cast, -20° to 40°C, with HTR and Photo-Control, Dark Bronze Finish	•			•	4.00 lbs.	6	



CIR Series

- Indoor LED Remote Heads
- Remote Heads Powered From CU, CE or CC Only

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93043126	CIRS	856143001509	LED Single Head with Mounting Plate	•		•	•	1.00 lbs	20	
93043127	CIRD	856143001516	LED Double Head with Mounting Plate	•		•	•	1.2 lbs	12	



COR Series

- Outdoor LED Remote Heads
- Remote Head Powered From CU, CE or CC Only

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93043128	CORS	856143001523	Outdoor LED Single Head Remote	•	•	•	•	1.00 lbs	20	
93043129	CORD	856143001530	Outdoor LED Double Head Remote		•	•	•	1.2 lbs	12	



CSWEU2

- 120/277 VAC
- Dual Adjustable Heads
- Wet Location Listed

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
CSWEU2	CSWEU2	856143001399	6V 14W, White Housing, Clear Polycarbonate Cover	•			•	5.00 lbs.	6	



CU2W Series

- 120/277 VAC
- 9.6VDC NiCad Battery
- Grey or Black Housing
- 2 Head LED
- Wet Location Listed

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93047780	CU2WG	856143001622	2 Head Adjustable Wet Location LED Emergency Light, Grey Housing	•	•	•	•	7.50 lbs.	4	
93047781	CU2WB	856143001639	2 Head Adjustable Wet Location LED Emergency Light, Black Housing	•			•	7.50 lbs.	4	



CWR Series

- Matching Outdoor Remotes for use with CU2W
- Remote Heads Powered From CU2W Only



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty	Price
93048687	CWRS	856143001776	Outdoor LED Single Head, Grey Finish, with Mounting Plate	•			•	2.00 lbs.	12	
93048688	CWRD	856143001769	Outdoor LED Double Head, Grey Finish, with Mounting Plate	•	•	•	•	3.00 lbs.	12	



CJB

- J-Box Mounted Emergency Light
- Passive Infra-Red Sensor
- Provides 90 minutes of emergency lighting



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	Wt. each	Ctn. Qty
93065066	CJBLWE	856143001837	Low level, white finish with battery	•	•	•	•	1 lb.	12
93065067	CJBLWEP	856143001844	Low level, white finish, battery, PIR sensor	•	•	•	•	1 lb.	12
93065068	CJBLBE	856143001851	Low level, black finish with battery	•			•	1 lb.	12
93065069	CJBLBEP	856143001868	Low level, black finish, battery, PIR sensor	•			•	1 lb.	12
93065070	CJBWE	856143001875	Adjustable angle, white finish with battery	•	•	•	•	1 lb.	12
93065071	CJBWEP	856143001882	Adj. angle, white finish, battery, PIR sensor	•	•	•	•	1 lb.	12
93065072	CJBBE	856143001899	Adjustable angle, black finish with battery	•			•	1 lb.	12
93065073	CJBBEP	856143001905	Adj. angle, black finish, battery, PIR sensor	•			•	1 lb.	12