

APPLAUSE



P4036-09

Individuals demonstrate appreciation and praise for elements that are worthy of acclaim. A collection deserving of recognition, Applause is comprised of etched parchment glass paired with an Antique Bronze finish and etched glass with a Brushed Nickel finish.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO AVAILABLE IN

Bath & Vanity
Close-to-Ceiling

PAIR WITH

Assembly Hall



P4037-09



P3507-09

WALL BRACKET
P2095-09 Brushed Nickel
7" W., 9-1/8" ht.
Extends 7-7/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3507-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
15-3/4" dia., 12" ht.
Overall ht. w/chain 51"; wire 10'.
Two medium base lamps,
each 100w max.



P4035-09

INVERTED PENDANT
P3560-09 Brushed Nickel
19-5/8" dia., 21-3/8" ht.
Overall ht. w/stem 96-1/2"; wire 15'.
Three medium base lamps,
each 100w max.



P4654-09

THREE-LIGHT CHANDELIER
P4035-09 Brushed Nickel
20" dia., 15-3/4" ht.
Overall ht. w/chain 91"; wire 15'.
Three medium base lamps,
each 100w max.



P5010-09

FIVE-LIGHT CHANDELIER
P4036-09 Brushed Nickel
24-1/2" dia., 24-5/8" ht.
Overall ht. w/chain 99"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4037-09 Brushed Nickel
Two-tier.
29-1/4" dia., 31-3/4" ht.
Overall ht. w/chain 145-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.



P2095-09

TWO-LIGHT LINEAR CHANDELIER
P4321-09 Brushed Nickel
36" L., 14" W., 18-1/4" ht.
Overall ht. w/chain 93"; wire 15'.
Two medium base lamps,
each 100w max.



P4321-09



P3560-09

TWELVE-LIGHT CHANDELIER
P4654-09 Brushed Nickel
Three-tier.
42" dia., 38" ht.
Overall ht. w/chain 161"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT
P5010-09 Brushed Nickel
7" dia., 6-1/2" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp,
100w max.



P4036-20



P4037-20

P3507-20

P4035-20

P4654-20

P5010-20

P2095-20

P4321-20

P3560-20

APPLAUSE

WALL BRACKET

P2095-20 Antique Bronze
7" W., 9-1/8" ht.
Extends 7-7/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3507-20 Antique Bronze
Hanging and ceiling mount
hardware included.
15-3/4" dia., 12" ht.
Overall ht. w/chain 51"; wire 10'.
Two medium base lamps,
each 100w max.

INVERTED PENDANT

P3560-20 Antique Bronze
19-5/8" dia., 21-3/8" ht.
Overall ht. w/stem 96-1/2"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P4035-20 Antique Bronze
20" dia., 15-3/4" ht.
Overall ht. w/chain 91"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4036-20 Antique Bronze
24-1/2" dia., 24-5/8" ht.
Overall ht. w/chain 99"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4037-20 Antique Bronze
Two-tier.
29-1/4" dia., 31-3/4" ht.
Overall ht. w/chain 145-1/2"; wire 15'.
Nine medium base lamps, each
100w max.

TWO-LIGHT LINEAR CHANDELIER

P4321-20 Antique Bronze
36" L., 14" W., 18-1/4" ht.
Overall ht. w/chain 93"; wire 15'.
Two medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4654-20 Antique Bronze
Three-tier.
42" dia., 38" ht.
Overall ht. w/chain 161"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT

P5010-20 Antique Bronze
7" dia., 6-1/2" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp,
100w max.

APPLAUSE



P2095-20

P2096-20



P2097-20



P2105-20



P2095-09

P2096-09



P2097-09



P2105-09



Applause is comprised of etched natural parchment glass paired with a classic iron form with Antique Bronze finish and etched parchment glass with Brushed Nickel finish.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO AVAILABLE IN

Fixture Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2095-09 Brushed Nickel
P2095-20 Antique Bronze
7" W., 9-1/8" ht.
Extends 7-7/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2096-09 Brushed Nickel
P2096-20 Antique Bronze
16-1/4" W., 8-1/2" ht. Extends 9".
H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2097-09 Brushed Nickel
P2097-20 Antique Bronze
24" W., 8-1/2" ht. Extends 9".
H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2105-09 Brushed Nickel
P2105-20 Antique Bronze
34" W., 8-1/2" ht. Extends 9".
H/CTR 6".
Four medium base lamps,
each 100w max.

APPLAUSE

Tinted patterned glass on Antique Bronze finish and etched white glass on Brushed Nickel finish.

SEMI-FLUSH CONVERTIBLE

P3507-09 Brushed Nickel

P3507-20 Antique Bronze
Hanging and ceiling mount hardware included.

15-3/4" dia., 12" ht.

Overall ht. w/chain 51"; wire 10'.

Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT

P3617-09 Brushed Nickel

P3617-20 Antique Bronze
14" dia., 9" ht.

Two medium base lamps, each 60w max.



P3507-20



P3507-09



P3617-20



P3617-09