

# PENN



P4769-137

Penn offers a modern take on vintage design. Turnkey details clear glass globes are enhanced by a Polished Nickel or Natural Brass finish.

**FINISHES**

- Polished Nickel - 104
- Natural Brass - 137

**PAIR WITH**

- Elevate
- Mod
- Harmony



P4769-104



P5328-104



P5067-104



P5070-104



P4769-137



P5328-137



P5067-137



P5070-137

**THREE-LIGHT CHANDELIER**

**P4769-104** Polished Nickel  
**P4769-137** Natural Brass  
 22" dia., 17-3/4" ht.  
 Overall ht. w/stem 84", wire 15'.  
 Three medium base lamps  
 each, 100w max.

**MINI-PENDANT**

**P5067-104** Polished Nickel  
**P5067-137** Natural Brass  
 6-7/8" dia., 9-1/2" ht.  
 Overall ht. w/stem 76"; wire 15'.  
 One medium base lamp,  
 100w max.

**PENDANT**

**P5070-104** Polished Nickel  
**P5070-137** Natural Brass  
 9-3/4" dia., 12-3/4" ht.  
 Overall ht. w/stem 79"; wire 15'.  
 One medium base lamp,  
 100w max.

**LARGE PENDANT**

**P5328-104** Polished Nickel  
**P5328-137** Natural Brass  
 12" dia., 15" ht.  
 Overall ht. w/stem 81", wire 10'.  
 One medium base lamp,  
 100w max.

*Fixtures shown with P7825-01  
 vintage lamps.*