

## 30 Amp, 480 and 600 Volts AC 2 Pole, 3 Wire, Grounding

**IP20**  
SUITABILITY



30A 240V AC  
NEMA L25-30P

30A 480V AC  
NEMA L8-30P  
5 HP

30A 600V AC  
NEMA L9-30P

### Plugs

| Description            | Cord Dia.                | Catalog Number                               |
|------------------------|--------------------------|--|
| Black and white nylon. | .325"-.930"<br>(8.25-24) | <b>HBL2601</b> <b>HBL2641</b> <b>HBL2651</b> |

Note: See page B-52 for accessories.



**HBL2651**

### Flanged Inlets

| Description               | Catalog Number                               |
|---------------------------|--|
| Nylon casing, back wired. | <b>HBL2605</b> <b>HBL2645</b> <b>HBL2655</b> |

Note: See page B-52 for accessories.



**HBL2655**

**IP20**  
SUITABILITY



30A 240V AC  
NEMA L25-30R

30A 480V AC  
NEMA L8-30R  
5 HP

30A 600V AC  
NEMA L9-30R

### Connector Bodies

| Description            | Cord Dia.                | Catalog Number                               |
|------------------------|--------------------------|--|
| Black and white nylon. | .325"-.930"<br>(8.25-24) | <b>HBL2603</b> <b>HBL2643</b> <b>HBL2653</b> |

Note: See page B-52 for accessories.



**HBL2653**

### Single Flush Receptacles

| Description                            | Catalog Number                               |
|--|--|
| Black nylon face, back and side wired. | <b>HBL2600</b> <b>HBL2640</b> <b>HBL2650</b> |


Note: See page B-52 for accessories.

### Flanged Receptacles

| Description               | Catalog Number                  |
|---------------------------|---------------------------------|
| Nylon casing, back wired. | - <b>HBL2646</b> <b>HBL2656</b> |

Note: See page B-52 for accessories.

See page B-69 for technical information on Twist-Lock devices.



**HBL2650**



**HBL2656**

Dimensions in Inches (mm)