



HEAVY-DUTY SDS HAMMER ACCESSORIES



PREMIUM SDS HAMMER BITS

44 MAGNUM™ CARBIDE



TIP — AGGRESSIVE GEOMETRY

- Centering point - allows more accurate starting of holes.
- Unique edge design - allows cutting mesh and small diameter re-bar with less likelihood of tip breakage.
- Unique face design - directs concrete dust into the flute's pick up area quickly for faster drilling.
- Chisel design - a distinctive chisel shape can be seen. It efficiently penetrates concrete, which also improves drilling speed.

FLUTES — MORE RIGID - BETTER DUST EXTRACTING MULTI-FLUTED SPIRAL EXECUTION

- Four fluted spiral removes concrete dust faster.
- Shaft strength is improved for less bending / breakage.
- Drilling is smoother due to less vibration.
- More energy of the hammer blow is transmitted to the tip to improve drilling speed.



5-PIECE 44 MAGNUM™ CARBIDE-TIPPED BIT SET

48-20-7490 Set includes one each of: 48-20-7410, 48-20-7431, 48-20-7441, 48-20-7451 and 48-20-7471.

DESCRIPTION (INCHES) DIA. x U.L. x O.L.	2-CUTTER SINGLE	BULK QTY	2-CUTTER	MONSTER QTY	2-CUTTER
5/32 x 2 x 4-1/2	48-20-7400	25	48-20-7500	-	-
5/32 x 4 x 6	48-20-7401	25	48-20-7501	-	-
3/16 x 2 x 4-1/2	48-20-7410	25	48-20-7510	200	48-20-7810
3/16 x 4 x 6	48-20-7411	25	48-20-7511	200	48-20-7811
3/16 x 6 x 8	48-20-7412	25	48-20-7512	-	-
3/16 x 8 x 10	48-20-7413	25	48-20-7513	-	-
3/16 x 10 x 12	48-20-7414	25	48-20-7514	-	-
3/16 x 12 x 14	48-20-7415	25	48-20-7515	-	-
3/16 x 14 x 16	48-20-7416	25	48-20-7516	-	-
7/32 x 4 x 6	48-20-7421	25	48-20-7521	-	-
7/32 x 6 x 8	48-20-7422	25	48-20-7522	-	-
7/32 x 9 x 11	48-20-7424	25	48-20-7524	-	-
7/32 x 12 x 14	48-20-7425	25	48-20-7525	-	-
7/32 x 14 x 16	48-20-7426	25	48-20-7526	-	-
1/4 x 2 x 4-1/2	48-20-7430	25	48-20-7530	200	48-20-7830
1/4 x 4 x 6	48-20-7431	25	48-20-7531	200	48-20-7831
1/4 x 6 x 8	48-20-7432	25	48-20-7532	-	-
1/4 x 9 x 11	48-20-7434	25	48-20-7534	-	-
1/4 x 12 x 14	48-20-7435	25	48-20-7535	-	-
1/4 x 14 x 16	48-20-7436	25	48-20-7536	-	-
1/4 x 18 x 20	48-20-7438	-	-	-	-
5/16 x 4 x 6	48-20-7441	25	48-20-7541	150	48-20-7841
5/16 x 10 x 12	48-20-7444	-	-	-	-
3/8 x 4 x 6	48-20-7451	20	48-20-7551	125	48-20-7851
3/8 x 6 x 8	48-20-7452	-	-	-	-
3/8 x 8 x 10	48-20-7453	-	-	-	-
3/8 x 10 x 12	48-20-7454	20	48-20-7554	-	-
3/8 x 16 x 18	48-20-7457	-	-	-	-
3/8 x 22 x 24	48-20-7459	-	-	-	-
7/16 x 4 x 6	48-20-7461	-	-	-	-
7/16 x 10 x 12-1/2	48-20-7464	-	-	-	-
7/16 x 16 x 18	48-20-7467	-	-	-	-
1/2 x 4 x 6	48-20-7471	15	48-20-7571	100	48-20-7871
1/2 x 8 x 10	48-20-7473	-	-	-	-
1/2 x 10 x 12	48-20-7474	15	48-20-7574	-	-
1/2 x 16 x 18	48-20-7477	-	-	-	-
1/2 x 22 x 24	48-20-7479	-	-	-	-
9/16 x 4 x 6-1/2	48-20-7481	-	-	-	-
9/16 x 10 x 12-1/2	48-20-7484	-	-	-	-
9/16 x 16 x 18	48-20-7487	-	-	-	-
5/8 x 4 x 6	48-20-7601	-	-	-	-
5/8 x 6 x 8	48-20-7602	10	48-20-7702	-	-
5/8 x 10 x 12	48-20-7604	-	-	-	-
5/8 x 16 x 18	48-20-7607	-	-	-	-
5/8 x 22 x 24	48-20-7609	-	-	-	-