

HID

HALOGEN

CFL

FL

BALLAST

GERMICIDAL



## LINEAR FLUORESCENT

### CONTENTS

- 90 - Linear Fluorescent Lamps - T5 (TCLP Compliant)
- 91 - Linear Fluorescent Lamps - T8



T5 Mini Bi-Pin Base



T8 Med Bi-Pin Base



How to  
read  
the  
table



HID

HALOGEN

CFL

FL

BALLAST

GERMICIDAL

HID

HALOGEN

CFL

FL

BALLAST

GERMICIDAL

# FLUORESCENT LAMPS

## Linear Fluorescent Lamps - T5 (TCLP Compliant) ■■■

\*Items only available for special orders

Product Information							Photometric Characteristics					
Watts	Bulb	Base	Item#	Description	Case Qty.	MOL (in)	Initial Lumens (lm)	Mean Lumens (lm)	Avg. Life (Hrs)	Color Temp (K)	CRI	UPC
<b>Fluorescent Lamps</b>												
14	T5	Mini Bi-Pin	4100	FL14/T5/830	25	21.61	1350	1269	20000	3000	85	844366041006
			4101	FL14/T5/835	25	21.61	1350	1269	20000	3500	85	844366041013
			4102	FL14/T5/841	25	21.61	1350	1269	20000	4100	85	844366041020
			4103	FL14/T5/850	25	21.61	1350	1269	20000	5000	85	844366041037
			4104	FL14/T5/865	25	21.61	1350	1269	20000	6500	85	844366041044
21	T5	Mini Bi-Pin	4105	FL21/T5/830	25	33.39	2100	1974	20000	3000	85	844366041051
			4106	FL21/T5/835	25	33.39	2100	1974	20000	3500	85	844366041068
			4107	FL21/T5/841	25	33.39	2100	1974	20000	4100	85	844366041075
			4108	FL21/T5/850	25	33.39	2100	1974	20000	5000	85	844366041082
			4109	FL21/T5/865	25	33.39	2100	1974	20000	6500	85	844366041099
28	T5	Mini Bi-Pin	4110	FL28/T5/830	25	45.2	2900	2726	20000	3000	85	844366041105
			4111	FL28/T5/835	25	45.2	2900	2726	20000	3500	85	844366041112
			4112	FL28/T5/841	25	45.2	2900	2726	20000	4100	85	844366041129
			4113	FL28/T5/850	25	45.2	2900	2726	20000	5000	85	844366041136
			4114	FL28/T5/865	25	45.2	2900	2726	20000	6500	85	844366041143
35	T5	Mini Bi-Pin	4130	* FL35/T5/830	25	57.09	3650	3431	20000	3000	85	844366041303
			4131	* FL35/T5/835	25	57.09	3650	3431	20000	3500	85	844366041310
			4132	* FL35/T5/841	25	57.09	3650	3431	20000	4100	85	844366041327
			4133	* FL35/T5/850	25	57.09	3650	3431	20000	5000	85	844366041334
			4134	* FL35/T5/865	25	57.09	3650	3431	20000	6500	85	844366041341

HID

HALOGEN

CFL

FL

BALLAST

GERMICIDAL

Product Information							Photometric Characteristics					
Watts	Bulb	Base	Item#	Description	Case Qty.	MOL (in)	Initial Lumens (lm)	Mean Lumens (lm)	Avg. Life (Hrs)	Color Temp (K)	CRI	UPC
<b>Fluorescent Lamps - High Output (T5)</b>												
<b>24</b>	T5	Mini Bi-Pin	4115	FL24/T5/830/H0	25	21.61	2000	1880	20000	3000	85	844366041150
			4116	FL24/T5/835/H0	25	21.61	2000	1880	20000	3500	85	844366041167
			4117	FL24/T5/841/H0	25	21.61	2000	1880	20000	4100	85	844366041174
			4118	FL24/T5/850/H0	25	21.61	2000	1880	20000	5000	85	844366041181
			4119	FL24/T5/865/H0	25	21.61	2000	1880	20000	6500	85	844366041198
<b>39</b>	T5	Mini Bi-Pin	4120	FL39/T5/830/H0	25	33.39	4900	4606	20000	3000	85	844366041204
			4121	FL39/T5/835/H0	25	33.39	4900	4606	20000	3500	85	844366041211
			4122	FL39/T5/841/H0	25	33.39	4900	4606	20000	4100	85	844366041228
			4123	FL39/T5/850/H0	25	33.39	4900	4606	20000	5000	85	844366041235
			4124	FL39/T5/865/H0	25	33.39	4900	4606	20000	6500	85	844366041242
<b>54</b>	T5	Mini Bi-Pin	4125	FL54/T5/830/H0	25	45.2	5000	4700	20000	3000	85	844366041259
			4126	FL54/T5/835/H0	25	45.2	5000	4700	20000	3500	85	844366041266
			4127	FL54/T5/841/H0	25	45.2	5000	4700	20000	4100	85	844366041273
			4128	FL54/T5/850/H0	25	45.2	5000	4700	20000	5000	85	844366041280
			4129	FL54/T5/865/H0	25	45.2	5000	4700	20000	6500	85	844366041297
<b>80</b>	T5	Mini Bi-Pin	4135	*FL80/T5/830/H0	25	57.09	7000	6580	20000	3000	85	844366041358
			4136	*FL80/T5/835/H0	25	57.09	7000	6580	20000	3500	85	844366041365
			4137	*FL80/T5/841/H0	25	57.09	7000	6580	20000	4100	85	844366041372
			4138	*FL80/T5/850/H0	25	57.09	7000	6580	20000	5000	85	844366041389
			4139	*FL80/T5/865/H0	25	57.09	7000	6580	20000	6500	85	844366041396

# FLUORESCENT LAMPS

Linear Fluorescent Lamps - T8 ■■■

\*Items only available for special orders

Product Information							Photometric Characteristics					
Watts	Bulb	Base	Item#	Description	Case Qty.	MOL (in)	Initial Lumens (lm)	Mean Lumens (lm)	Avg. Life (Hrs)	Color Temp (K)	CRI	UPC
<b>T8 700 Series</b>												
32	T8	Med Bi-Pin	4183	* FL32T8/741/ECO	25	37.66	2850	2750	20000	4100	75	844366041839
32	T8	Med Bi-Pin	4184	* FL32T8/750/ECO	25	37.66	2750	2690	20000	5000	75	844366041846
<b>T8 800 Series</b>												
32	T8	Med Bi-Pin	4180	* FL32T8/835/ECO	25	37.66	3000	2850	20000	3500	82	844366041808
32	T8	Med Bi-Pin	4181	* FL32T8/841/ECO	25	37.66	3000	2850	20000	4100	82	844366041815
32	T8	Med Bi-Pin	4182	* FL32T8/850/ECO	25	37.66	3000	2850	20000	5000	82	844366041822
32	T8	Med Bi-Pin	4185	* FL32T8/865/ECO	25	37.66	3000	2850	20000	6000	82	844366041853
32	T8	Med Bi-Pin	4187	* FL32T8/835/HO/ECO	25	37.66	3200	3050	20000	3500	82	844366041877
32	T8	Med Bi-Pin	4188	* FL32T8/841/HO/ECO	25	37.66	3200	3050	20000	4100	82	844366041884
32	T8	Med Bi-Pin	4189	* FL32T8/850/HO/ECO	25	37.66	3200	3050	20000	5000	82	844366041891
<b>T8 800 Energy Saving</b>												
28	T8	Med Bi-Pin	4191	* FL28T8/835/ES/ECO	25	37.66	2700	2565	20000	3500	82	844366041914
28	T8	Med Bi-Pin	4192	* FL28T8/841/ES/ECO	25	37.66	2675	2550	20000	4100	82	844366041921
28	T8	Med Bi-Pin	4193	* FL28T8/850/ES/ECO	25	37.66	2650	2520	20000	5000	82	844366041938
28	T8	Med Bi-Pin	4190	* FL28T8/865/ES/ECO	25	37.66	2650	2520	20000	6000	82	844366041907

HID

HALOGEN

CFL

FL

BALLAST

GERMICIDAL