



MASONRY BOXES WITH CONCENTRIC KNOCKOUTS (CKO) 2-1/2" DEEP


Cat. No.	No. of Gangs	Knockouts			Dimension W x H	Cu. Inch	Std. Pkg.
		Ends	Bottom	Sides			
MSBG-1	1, Gangable	2	1	4	1-7/8" x 3-3/4"	16.1	25
MSB-1	1	2	1	4	1-7/8" x 3-3/4"	16.1	25
MSB-2	2	4	2	4	3-3/4" x 3-3/4"	31.9	10
MSB-3	3	6	3	4	5-1/2" x 3-3/4"	47.9	10
MSB-4	4	8	4	4	7-3/8" x 3-3/4"	63.6	10
MSB-5	5	10	5	4	9-1/8" x 3-3/4"	79.6	10
MSB-6	6	12	6	4	11" x 3-3/4"	95.3	1




MSBG-1




MSB-1



MSB-2




MSB-3




MSB-6

MASONRY BOXES WITH CONCENTRIC KNOCKOUTS (CKO) 3-1/2" DEEP


Cat. No.	No. of Gangs	Knockouts			Dimension W x H	Cu. Inch	Std. Pkg.
		Ends	Bottom	Sides			
MBG-1	1, Gangable	4	1	4	1-7/8" x 3-3/4"	23.5	25
MB-1	1	4	1	4	1-7/8" x 3-3/4"	23.5	25
MB-2	2	8	2	4	3-3/4" x 3-3/4"	46.9	10
MB-3	3	12	3	4	5-1/2" x 3-3/4"	69.3	10
MB-4	4	16	4	4	7-3/8" x 3-3/4"	92.1	10
MB-5	5	20	5	4	9-1/8" x 3-3/4"	116.1	10
MB-6	6	24	6	4	11" x 3-3/4"	139.0	1




MBG-1




MB-1



MB-2



MB-3



MB-6

MASONRY BOX PARTITION

Cat. No.	Description	Dimension W x H	Std. Pkg.
MB-D	2-1/2" / 3-1/2" Partition for MSB and MB Boxes	3-1/4" x 3-1/2"	25

Features:

- Fits 2-1/2" & 3-1/2" Masonry Boxes



MB-D

- 600V** CKO's suitable for bonding without any additional bonding means up to 600V
- Visit www.ul.com or QCIT Guide on page W1 for more information